

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925395

Luminaire Tested: DFN2DIP-SQ2F0-070D040US950-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925395  
REPORT IS A COMBINATION OF REPORTS P901312 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-070D040US950-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9454.1 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 97.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925395  
CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P925395  
 CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60			
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	57	56	52			
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44			
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42	38			
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37	33			
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32	29			
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	32	29	26			
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26	23			
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23	21			
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21	19			
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6069	6069	6069
5°	6068	5959	6002
10°	5998	5829	5799
15°	5904	5624	5489
20°	5785	5346	5112
25°	5662	5037	4748
30°	5501	4721	4289
35°	5342	4384	3886
40°	5181	4035	3426
45°	4994	3651	3009
50°	4800	3263	2603
55°	4596	2851	2213
60°	4360	2423	1814
65°	4087	1989	1623
70°	3757	1584	1456
75°	3340	1371	1308
80°	2744	1113	1109
85°	1785	691	789

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4994 cd/sqm



TEST NUMBER: P925395

CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.7	2.7
10°-20°	710.1	7.5
20°-30°	997.0	10.5
30°-40°	1086.8	11.5
40°-50°	998.8	10.6
50°-60°	784.4	8.3
60°-70°	510.6	5.4
70°-80°	262.8	2.8
80°-90°	69.4	0.7
90°-100°	42.5	0.4
100°-110°	158.3	1.7
110°-120°	419.9	4.4
120°-130°	696.4	7.4
130°-140°	739.7	7.8
140°-150°	687.5	7.3
150°-160°	552.7	5.8
160°-170°	356.1	3.8
170°-180°	122.6	1.3
0°-30°	1965.7	20.8
0°-40°	3052.5	32.3
0°-60°	4835.8	51.1
0°-90°	5678.5	60.1
90°-120°	620.6	6.6
90°-150°	2744.1	29.0
90°-180°	3776.0	39.9
0°-180°	9454.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2760	2760	2760	2760	2760	
5°	2760	2748	2715	2738	2730	262
15°	2625	2598	2513	2465	2440	740
25°	2383	2303	2138	2036	1998	1096
35°	2053	1926	1706	1549	1494	1285
45°	1679	1511	1249	1071	1012	1296
55°	1276	1082	812	662	615	1140
65°	862	659	435	350	342	854
75°	460	285	200	182	180	486
85°	107	55	47	47	47	123
90°	1	11	19	23	25	9
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	



TEST NUMBER: P925395

CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2760.0	2760.0	2760.0	2760.0	2760.0
2.5°	2772.4	2760.0	2732.4	2757.6	2752.6
5°	2760.0	2747.5	2715.0	2737.5	2730.1
7.5°	2737.5	2722.6	2687.7	2697.4	2685.0
10°	2707.5	2690.1	2640.2	2632.6	2617.7
12.5°	2670.2	2647.6	2580.1	2565.2	2537.6
15°	2625.1	2597.6	2512.7	2465.3	2440.4
17.5°	2572.7	2532.7	2427.7	2372.8	2332.8
20°	2512.7	2462.7	2337.9	2275.6	2220.4
22.5°	2447.9	2390.3	2245.3	2160.5	2123.2
25°	2382.9	2302.9	2138.0	2035.7	1998.2
27.5°	2305.5	2220.4	2038.1	1920.8	1863.3
30°	2223.1	2128.0	1928.1	1801.0	1733.4
32.5°	2143.1	2028.1	1823.5	1673.5	1610.9
35°	2053.2	1925.7	1706.1	1548.7	1493.6
37.5°	1965.8	1828.2	1596.1	1423.6	1361.4
40°	1873.3	1723.6	1481.1	1303.8	1238.9
42.5°	1778.4	1618.7	1366.3	1181.3	1119.1
45°	1678.6	1511.0	1249.0	1071.4	1011.5
47.5°	1583.6	1406.4	1136.6	959.1	904.2
50°	1478.7	1301.4	1026.6	854.1	801.9
52.5°	1376.1	1188.8	921.7	756.8	709.4
55°	1276.3	1081.5	811.7	662.0	614.6
57.5°	1174.0	974.1	714.5	574.5	534.5
60°	1069.1	869.2	611.9	484.7	444.7
62.5°	966.7	766.9	524.4	404.7	384.7
65°	861.7	659.3	434.6	349.8	342.1
67.5°	761.9	559.4	349.8	307.1	299.7
70°	656.9	462.1	289.6	264.7	254.6
72.5°	557.0	372.1	242.2	222.4	217.3
75°	459.5	284.6	199.8	182.3	179.9
77.5°	362.2	202.2	157.4	147.3	142.3
80°	272.2	144.9	119.8	110.0	110.0
82.5°	189.8	97.5	82.4	77.4	77.4
85°	107.3	54.9	47.4	47.4	47.4
87.5°	40.0	19.8	19.8	17.5	17.5
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6



TEST NUMBER: P925395

CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9



TEST NUMBER: P925395  
 CATALOG NUMBER: DFN2DIP-SQ2F0-070D040US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.19	15.11	15.06	16.00	17.12	10.15	11.07	11.02	11.96	13.08
	3H	15.85	16.68	16.74	17.57	18.72	11.33	12.15	12.21	13.05	14.20
	4H	16.45	17.23	17.35	18.13	19.29	11.77	12.54	12.67	13.45	14.61
	6H	16.86	17.58	17.78	18.49	19.66	12.08	12.79	12.99	13.70	14.87
	8H	16.98	17.66	17.90	18.59	19.76	12.16	12.84	13.08	13.77	14.94
	12H	17.04	17.69	17.97	18.61	19.80	12.20	12.85	13.12	13.77	14.96
4H	2H	14.21	14.99	15.12	15.89	17.05	10.74	11.52	11.65	12.42	13.58
	3H	16.03	16.67	16.94	17.61	18.78	12.08	12.73	13.00	13.66	14.84
	4H	16.71	17.29	17.63	18.23	19.42	12.62	13.20	13.54	14.14	15.33
	6H	17.21	17.71	18.15	18.67	19.87	13.02	13.53	13.96	14.48	15.68
	8H	17.37	17.85	18.32	18.80	20.01	13.14	13.61	14.09	14.56	15.78
	12H	17.46	17.89	18.42	18.85	20.07	13.20	13.63	14.16	14.59	15.81
8H	4H	16.68	17.15	17.62	18.10	19.31	12.89	13.36	13.84	14.31	15.53
	6H	17.22	17.61	18.19	18.61	19.82	13.39	13.78	14.36	14.77	15.98
	8H	17.43	17.77	18.41	18.75	19.98	13.57	13.91	14.55	14.89	16.12
	12H	17.56	17.86	18.54	18.83	20.11	13.67	13.98	14.66	14.95	16.23
12H	4H	16.63	17.06	17.59	18.02	19.24	12.90	13.32	13.86	14.29	15.51
	6H	17.20	17.54	18.18	18.52	19.75	13.43	13.78	14.41	14.76	15.99
	8H	17.41	17.71	18.39	18.69	19.96	13.63	13.94	14.61	14.91	16.19