

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911775

Luminaire Tested: DFN2DIP-SQ2F0-080D030US850-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P911775  
REPORT IS A COMBINATION OF REPORTS P901302 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-080D030US850-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10834.9 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 101.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P911775  
CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P911775

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	59	57	55	55	55	55	51
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	48	44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	32	29	29	29	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8063	8063	8063
5°	8062	7917	7974
10°	7968	7745	7704
15°	7844	7472	7292
20°	7685	7103	6791
25°	7522	6692	6308
30°	7308	6273	5698
35°	7098	5824	5163
40°	6883	5361	4552
45°	6635	4850	3998
50°	6377	4336	3458
55°	6106	3788	2940
60°	5792	3219	2410
65°	5431	2642	2156
70°	4991	2104	1935
75°	4438	1821	1738
80°	3644	1479	1473
85°	2372	918	1048

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6635 cd/sqm



TEST NUMBER: P911775  
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	343.7	3.2
10°-20°	943.4	8.7
20°-30°	1324.5	12.2
30°-40°	1443.8	13.3
40°-50°	1327.0	12.2
50°-60°	1042.1	9.6
60°-70°	678.3	6.3
70°-80°	349.2	3.2
80°-90°	91.1	0.8
90°-100°	37.0	0.3
100°-110°	138.0	1.3
110°-120°	366.1	3.4
120°-130°	607.1	5.6
130°-140°	644.9	6.0
140°-150°	599.4	5.5
150°-160°	481.9	4.4
160°-170°	310.5	2.9
170°-180°	106.9	1.0
0°-30°	2611.6	24.1
0°-40°	4055.4	37.4
0°-60°	6424.5	59.3
0°-90°	7543.2	69.6
90°-120°	541.1	5.0
90°-150°	2392.5	22.1
90°-180°	3292.0	30.4
0°-180°	10834.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	1	10	16	20	22	10
95°	53	26	32	36	35	63
105°	247	271	50	58	62	264
115°	467	481	501	125	67	460
125°	660	671	687	692	695	589
135°	817	830	838	846	844	631
145°	948	947	961	967	963	593
155°	1044	1037	1046	1051	1045	481
165°	1100	1095	1098	1103	1098	311
175°	1125	1120	1121	1127	1119	107
180°	1123	1123	1123	1123	1123	



TEST NUMBER: P911775

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	0.8	9.8	16.2	20.4	21.8
92.5°	20.4	17.1	19.5	21.2	21.8
95°	52.8	26.0	31.6	35.8	34.9
97.5°	95.0	28.5	41.4	43.9	44.7
100°	143.8	32.5	46.4	52.8	54.5
102.5°	197.4	195.8	47.9	56.8	59.3
105°	247.0	271.4	49.6	58.4	61.8
107.5°	304.6	324.9	51.2	60.1	63.4
110°	360.0	376.9	142.2	61.0	64.2



TEST NUMBER: P911775

CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	412.0	426.5	412.8	62.5	65.0
115°	467.1	481.0	501.3	125.1	66.7
117.5°	515.1	531.3	545.2	429.0	216.1
120°	568.7	580.9	595.5	605.3	495.6
122.5°	614.2	627.3	643.6	648.3	649.2
125°	660.5	671.1	686.6	692.2	694.7
127.5°	702.8	714.1	726.4	734.5	735.3
130°	742.6	755.7	764.5	773.4	772.8
132.5°	783.2	793.8	802.7	810.0	809.2
135°	817.3	830.4	837.6	845.8	844.2
137.5°	853.0	862.8	871.0	879.1	876.7
140°	888.0	894.5	903.4	910.7	906.7
142.5°	917.4	923.0	933.6	940.0	936.0
145°	948.2	947.3	961.2	966.8	962.7
147.5°	974.9	972.5	986.3	990.3	987.1
150°	1001.0	995.3	1008.3	1013.1	1009.1
152.5°	1022.8	1016.4	1028.6	1033.5	1027.8
155°	1044.0	1036.8	1046.5	1051.3	1044.9
157.5°	1061.1	1054.7	1062.0	1067.6	1061.1
160°	1075.7	1070.9	1075.7	1080.6	1074.8
162.5°	1088.7	1083.8	1087.9	1093.6	1086.3
165°	1100.0	1095.2	1097.7	1103.3	1097.7
167.5°	1109.0	1104.1	1106.6	1112.3	1105.0
170°	1116.3	1111.4	1113.1	1118.8	1111.4
172.5°	1121.2	1116.3	1118.0	1123.6	1116.3
175°	1125.2	1119.5	1121.2	1126.9	1118.8
177.5°	1126.9	1121.2	1122.1	1127.7	1120.4
180°	1122.9	1122.9	1122.9	1122.9	1122.9



TEST NUMBER: P911775  
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D030US850-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.95	16.97	16.72	17.76	18.72	11.91	12.93	12.68	13.72	14.68
	3H	17.62	18.53	18.41	19.34	20.33	13.09	14.01	13.88	14.81	15.80
	4H	18.22	19.08	19.03	19.90	20.90	13.54	14.40	14.35	15.21	16.22
	6H	18.64	19.43	19.46	20.25	21.27	13.85	14.65	14.67	15.47	16.48
	8H	18.76	19.52	19.59	20.35	21.37	13.94	14.69	14.77	15.53	16.55
	12H	18.82	19.54	19.66	20.37	21.42	13.98	14.70	14.82	15.53	16.58
4H	2H	15.98	16.84	16.79	17.65	18.66	12.52	13.38	13.33	14.19	15.19
	3H	17.81	18.52	18.63	19.37	20.39	13.86	14.58	14.68	15.42	16.44
	4H	18.49	19.14	19.33	19.98	21.03	14.40	15.05	15.24	15.89	16.94
	6H	19.00	19.56	19.85	20.43	21.48	14.81	15.37	15.66	16.24	17.29
	8H	19.17	19.69	20.02	20.55	21.62	14.93	15.46	15.79	16.32	17.38
	12H	19.26	19.73	20.13	20.61	21.68	15.00	15.47	15.87	16.35	17.42
8H	4H	18.47	18.99	19.32	19.85	20.92	14.68	15.21	15.54	16.07	17.14
	6H	19.02	19.45	19.90	20.36	21.42	15.18	15.62	16.07	16.52	17.59
	8H	19.22	19.61	20.12	20.51	21.59	15.36	15.75	16.26	16.64	17.73
	12H	19.36	19.70	20.25	20.59	21.72	15.47	15.81	16.37	16.70	17.84
12H	4H	18.43	18.90	19.30	19.78	20.85	14.69	15.16	15.57	16.05	17.12
	6H	18.99	19.38	19.89	20.28	21.36	15.23	15.61	16.12	16.51	17.59
	8H	19.21	19.55	20.10	20.44	21.57	15.43	15.77	16.33	16.66	17.80