

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914410

Luminaire Tested: DFN2DIP-SQ2F0-040D040US927-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914410  
REPORT IS A COMBINATION OF REPORTS P899786 AND P896659  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-040D040US927-RLLFLL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5497.7 lumens  
Efficiency: N/A  
Efficacy: 87.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 63.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914410  
CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P914410  
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2880	2880	2880
5°	2879	2828	2848
10°	2846	2766	2751
15°	2802	2669	2605
20°	2745	2537	2426
25°	2687	2390	2253
30°	2610	2240	2035
35°	2535	2080	1844
40°	2458	1915	1626
45°	2370	1732	1428
50°	2277	1548	1235
55°	2181	1353	1050
60°	2069	1149	861
65°	1940	944	770
70°	1783	751	691
75°	1585	650	621
80°	1301	528	526
85°	847	328	374

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2370 cd/sqm



TEST NUMBER: P914410

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.7	2.2
10°-20°	336.9	6.1
20°-30°	473.1	8.6
30°-40°	515.7	9.4
40°-50°	473.9	8.6
50°-60°	372.2	6.8
60°-70°	242.3	4.4
70°-80°	124.7	2.3
80°-90°	34.7	0.6
90°-100°	62.0	1.1
100°-110°	197.0	3.6
110°-120°	337.2	6.1
120°-130°	443.5	8.1
130°-140°	497.8	9.1
140°-150°	488.1	8.9
150°-160°	409.5	7.4
160°-170°	271.5	4.9
170°-180°	94.9	1.7
0°-30°	932.7	17.0
0°-40°	1448.4	26.3
0°-60°	2294.6	41.7
0°-90°	2696.2	49.0
90°-120°	596.2	10.8
90°-150°	2025.6	36.8
90°-180°	2801.0	50.9
0°-180°	5497.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	11	30	28	29	5
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P914410

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P914410

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P914410  
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US927-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.61	11.44	11.59	12.42	13.71	6.58	7.40	7.55	8.38	9.67
	3H	12.27	13.01	13.26	14.00	15.31	7.75	8.48	8.73	9.47	10.78
	4H	12.87	13.56	13.86	14.56	15.88	8.18	8.88	9.18	9.87	11.19
	6H	13.27	13.91	14.28	14.91	16.24	8.49	9.13	9.49	10.13	11.46
	8H	13.39	14.00	14.40	15.01	16.34	8.57	9.18	9.58	10.19	11.52
	12H	13.44	14.02	14.46	15.03	16.38	8.60	9.18	9.62	10.19	11.54
4H	2H	10.63	11.32	11.63	12.32	13.63	7.16	7.85	8.16	8.85	10.17
	3H	12.43	13.01	13.44	14.03	15.37	8.49	9.07	9.50	10.09	11.42
	4H	13.11	13.64	14.13	14.65	16.01	9.02	9.55	10.04	10.56	11.92
	6H	13.61	14.06	14.64	15.10	16.45	9.42	9.87	10.45	10.91	12.26
	8H	13.77	14.19	14.80	15.23	16.59	9.54	9.96	10.57	10.99	12.36
	12H	13.85	14.24	14.90	15.28	16.65	9.59	9.97	10.64	11.02	12.39
8H	4H	13.07	13.50	14.10	14.53	15.89	9.29	9.71	10.32	10.74	12.11
	6H	13.62	13.97	14.67	15.04	16.40	9.78	10.13	10.84	11.20	12.57
	8H	13.82	14.13	14.88	15.19	16.57	9.96	10.27	11.02	11.32	12.71
	12H	13.95	14.22	15.01	15.27	16.69	10.06	10.33	11.13	11.39	12.81
12H	4H	13.02	13.41	14.07	14.45	15.82	9.29	9.67	10.34	10.72	12.09
	6H	13.59	13.90	14.65	14.96	16.34	9.82	10.13	10.89	11.19	12.57
	8H	13.80	14.07	14.86	15.12	16.55	10.02	10.29	11.08	11.34	12.77