

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903637

Luminaire Tested: DFN2DIP-SQ3F0-040D100US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903637
REPORT IS A COMBINATION OF REPORTS P901489 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D100US830-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13063.6 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 109.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903637
CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P903637

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29			
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24			
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26	20			
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17			
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19	15			
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16	13			
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14	11			
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13	10			
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11	9			
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8			
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1681	1681	1681
5°	1683	1656	1668
10°	1668	1633	1645
15°	1642	1605	1609
20°	1608	1567	1572
25°	1574	1521	1530
30°	1531	1478	1477
35°	1491	1428	1420
40°	1442	1377	1366
45°	1392	1326	1310
50°	1338	1273	1246
55°	1282	1211	1188
60°	1218	1138	1120
65°	1148	1062	1040
70°	1058	969	954
75°	935	858	874
80°	786	715	723
85°	553	473	473

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2177 cd/sqm



TEST NUMBER: P903637

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.1
10°-20°	388.5	3.0
20°-30°	570.9	4.4
30°-40°	663.1	5.1
40°-50°	662.3	5.1
50°-60°	577.5	4.4
60°-70°	426.9	3.3
70°-80°	241.5	1.8
80°-90°	69.3	0.5
90°-100°	104.9	0.8
100°-110°	391.0	3.0
110°-120°	1037.0	7.9
120°-130°	1720.0	13.2
130°-140°	1827.0	14.0
140°-150°	1698.0	13.0
150°-160°	1365.2	10.5
160°-170°	879.7	6.7
170°-180°	302.8	2.3
0°-30°	1097.5	8.4
0°-40°	1760.6	13.5
0°-60°	3000.3	23.0
0°-90°	3738.1	28.6
90°-120°	1532.9	11.7
90°-150°	6778.0	51.9
90°-180°	9326.0	71.4
0°-180°	13063.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	28	46	58	62	12
95°	150	74	90	101	99	177
105°	700	769	140	166	175	748
115°	1323	1362	1420	354	189	1303
125°	1871	1901	1945	1961	1968	1669
135°	2316	2352	2373	2396	2392	1789
145°	2686	2684	2723	2739	2728	1680
155°	2958	2937	2965	2978	2960	1363
165°	3116	3103	3110	3126	3110	880
175°	3188	3172	3176	3192	3170	303
180°	3181	3181	3181	3181	3181	



TEST NUMBER: P903637

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	2.2	27.6	45.9	57.7	62.0
92.5°	57.7	48.4	55.2	59.9	62.0
95°	149.5	73.5	89.6	101.4	99.0
97.5°	269.2	80.6	117.3	124.3	126.6
100°	407.6	92.1	131.2	149.5	154.2
102.5°	559.2	554.9	135.8	161.0	168.1
105°	699.7	768.8	140.5	165.6	174.9
107.5°	863.2	920.6	145.2	170.3	179.6
110°	1019.7	1067.9	402.8	172.8	181.7



TEST NUMBER: P903637

CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1167.1	1208.3	1169.3	177.1	184.3
115°	1323.4	1362.5	1420.2	354.5	188.9
117.5°	1459.2	1505.2	1544.5	1215.2	612.3
120°	1611.3	1645.7	1687.2	1714.9	1404.1
122.5°	1740.0	1776.9	1823.1	1836.7	1839.2
125°	1871.2	1901.3	1945.0	1961.1	1967.9
127.5°	1990.9	2023.2	2057.9	2080.9	2083.0
130°	2103.8	2140.7	2165.9	2191.2	2189.1
132.5°	2218.8	2248.9	2274.1	2294.8	2292.6
135°	2315.6	2352.5	2373.0	2396.2	2391.6
137.5°	2416.8	2444.4	2467.6	2490.6	2483.7
140°	2515.6	2534.3	2559.4	2580.2	2568.7
142.5°	2598.8	2614.9	2644.7	2663.0	2651.6
145°	2686.2	2683.8	2722.9	2739.0	2727.5
147.5°	2761.9	2755.1	2794.2	2805.7	2796.7
150°	2835.7	2819.6	2856.6	2870.2	2858.7
152.5°	2897.8	2879.5	2914.0	2927.8	2911.7
155°	2957.7	2937.2	2964.8	2978.4	2960.1
157.5°	3006.1	2987.8	3008.5	3024.6	3006.1
160°	3047.6	3033.7	3047.6	3061.3	3045.2
162.5°	3084.2	3070.5	3082.0	3098.1	3077.4
165°	3116.4	3102.8	3109.6	3125.8	3109.6
167.5°	3141.9	3127.9	3135.1	3151.2	3130.4
170°	3162.6	3148.8	3153.4	3169.5	3148.8
172.5°	3176.3	3162.6	3167.3	3183.4	3162.6
175°	3187.8	3171.7	3176.3	3192.5	3169.5
177.5°	3192.5	3176.3	3178.8	3194.9	3174.1
180°	3181.0	3181.0	3181.0	3181.0	3181.0



TEST NUMBER: P903637
 CATALOG NUMBER: DFN2DIP-SQ3F0-040D100US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.64	7.33	7.76	8.45	9.99	6.19	6.89	7.31	8.00	9.55
	3H	8.28	8.90	9.41	10.03	11.59	7.79	8.41	8.92	9.54	11.10
	4H	8.86	9.45	9.99	10.57	12.14	8.36	8.95	9.50	10.08	11.65
	6H	9.24	9.79	10.39	10.92	12.50	8.74	9.29	9.89	10.42	12.00
	8H	9.34	9.86	10.49	11.00	12.57	8.84	9.36	9.99	10.50	12.07
	12H	9.38	9.88	10.54	11.01	12.61	8.87	9.37	10.03	10.50	12.10
4H	2H	7.07	7.67	8.22	8.79	10.36	6.72	7.31	7.86	8.43	10.00
	3H	8.92	9.41	10.07	10.56	12.14	8.51	9.00	9.66	10.15	11.74
	4H	9.62	10.08	10.78	11.22	12.82	9.20	9.65	10.35	10.79	12.39
	6H	10.12	10.51	11.28	11.67	13.26	9.69	10.08	10.85	11.24	12.83
	8H	10.27	10.63	11.43	11.78	13.39	9.83	10.19	10.99	11.35	12.95
	12H	10.33	10.66	11.51	11.82	13.44	9.88	10.21	11.06	11.37	12.99
8H	4H	9.80	10.16	10.96	11.32	12.92	9.42	9.79	10.58	10.94	12.55
	6H	10.42	10.72	11.60	11.91	13.52	10.03	10.34	11.21	11.53	13.13
	8H	10.63	10.90	11.82	12.07	13.69	10.24	10.50	11.43	11.68	13.30
	12H	10.76	10.99	11.94	12.16	13.81	10.34	10.57	11.53	11.75	13.40
12H	4H	9.78	10.11	10.95	11.27	12.88	9.41	9.74	10.58	10.90	12.52
	6H	10.45	10.71	11.63	11.88	13.51	10.07	10.34	11.26	11.51	13.13
	8H	10.68	10.91	11.86	12.08	13.73	10.30	10.53	11.48	11.70	13.35