

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914429

Luminaire Tested: DFN2DIP-SQ2F0-050D030US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914429
REPORT IS A COMBINATION OF REPORTS P901295 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D030US927-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6274.1 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3389	3389	3389
5°	3388	3334	3359
10°	3355	3282	3309
15°	3300	3221	3233
20°	3227	3138	3156
25°	3155	3041	3067
30°	3066	2950	2956
35°	2981	2845	2838
40°	2878	2737	2726
45°	2774	2629	2610
50°	2660	2516	2477
55°	2541	2384	2354
60°	2405	2230	2213
65°	2257	2068	2046
70°	2068	1872	1865
75°	1809	1636	1692
80°	1495	1336	1374
85°	1010	843	863

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2774 cd/sqm

TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	2.3
10°-20°	408.1	6.5
20°-30°	599.8	9.6
30°-40°	696.6	11.1
40°-50°	695.8	11.1
50°-60°	606.7	9.7
60°-70°	448.5	7.1
70°-80°	253.7	4.0
80°-90°	68.4	1.1
90°-100°	26.5	0.4
100°-110°	98.6	1.6
110°-120°	261.5	4.2
120°-130°	433.7	6.9
130°-140°	460.7	7.3
140°-150°	428.1	6.8
150°-160°	344.2	5.5
160°-170°	221.8	3.5
170°-180°	76.3	1.2
0°-30°	1153.0	18.4
0°-40°	1849.6	29.5
0°-60°	3152.1	50.2
0°-90°	3922.7	62.5
90°-120°	386.5	6.2
90°-150°	1709.0	27.2
90°-180°	2351.0	37.5
0°-180°	6274.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1531	1528	146
15°	1467	1458	1439	1445	1438	413
25°	1328	1316	1291	1294	1291	611
35°	1146	1131	1107	1098	1091	715
45°	932	922	900	883	877	719
55°	706	697	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	7	12	15	16	6
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.2	1541.2	1541.2	1541.2	1541.2
2.5°	1550.1	1542.8	1526.5	1541.2	1538.4
5°	1541.2	1535.4	1519.0	1530.8	1528.0
7.5°	1530.8	1522.0	1505.7	1517.7	1514.7
10°	1514.7	1504.3	1486.5	1498.3	1493.9
12.5°	1492.3	1483.5	1465.8	1473.1	1470.1
15°	1467.1	1458.3	1439.0	1445.0	1437.6
17.5°	1436.0	1427.2	1407.9	1415.2	1407.9
20°	1401.9	1393.1	1372.4	1376.7	1370.9
22.5°	1367.9	1354.6	1335.2	1335.2	1332.2
25°	1327.9	1316.1	1290.9	1293.7	1290.9
27.5°	1283.3	1273.0	1253.8	1249.3	1242.0
30°	1239.0	1227.1	1204.9	1200.5	1194.5
32.5°	1191.5	1182.7	1159.0	1150.0	1144.1
35°	1145.6	1130.8	1107.1	1098.1	1090.8
37.5°	1093.7	1080.4	1056.6	1046.2	1038.9
40°	1040.5	1028.5	1004.7	991.5	985.6
42.5°	988.6	976.6	953.0	938.0	929.2
45°	932.2	921.9	899.5	883.4	877.3
47.5°	877.3	867.0	843.3	826.9	818.1
50°	819.5	812.1	791.4	770.6	763.2
52.5°	763.2	752.8	733.6	717.3	706.9
55°	705.5	696.6	678.7	661.0	653.6
57.5°	647.6	640.2	620.9	603.2	597.1
60°	589.8	584.0	563.2	546.8	542.5
62.5°	533.5	523.2	508.3	493.5	487.6
65°	475.8	466.8	452.0	438.7	431.3
67.5°	416.5	409.0	395.8	385.4	379.4
70°	361.6	355.7	342.3	331.9	326.1
72.5°	305.4	299.4	292.0	281.6	277.2
75°	248.9	246.1	238.5	229.7	232.7
77.5°	198.6	192.6	189.6	185.2	180.9
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.8	100.8	99.3	93.4	93.4
85°	60.7	59.3	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9

TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P914429

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	13.46	13.32	14.33	15.41	12.03	13.02	12.88	13.88	14.97
	3H	14.13	15.01	14.98	15.89	17.00	13.64	14.52	14.49	15.40	16.51
	4H	14.71	15.55	15.58	16.43	17.54	14.22	15.05	15.09	15.93	17.05
	6H	15.10	15.87	15.98	16.76	17.89	14.60	15.37	15.48	16.26	17.39
	8H	15.20	15.94	16.09	16.84	17.97	14.70	15.44	15.59	16.34	17.47
	12H	15.25	15.95	16.14	16.85	18.00	14.74	15.44	15.64	16.34	17.49
4H	2H	12.94	13.78	13.82	14.66	15.78	12.59	13.43	13.46	14.31	15.42
	3H	14.80	15.50	15.68	16.41	17.54	14.39	15.09	15.28	16.00	17.13
	4H	15.50	16.14	16.40	17.05	18.21	15.08	15.71	15.98	16.62	17.78
	6H	16.01	16.56	16.92	17.49	18.65	15.57	16.12	16.49	17.06	18.22
	8H	16.15	16.66	17.06	17.59	18.76	15.71	16.23	16.63	17.15	18.33
	12H	16.22	16.68	17.15	17.63	18.81	15.77	16.23	16.71	17.18	18.36
8H	4H	15.70	16.21	16.61	17.14	18.31	15.32	15.83	16.23	16.76	17.93
	6H	16.31	16.74	17.25	17.70	18.88	15.92	16.35	16.87	17.32	18.49
	8H	16.52	16.90	17.47	17.85	19.05	16.13	16.50	17.08	17.46	18.65
	12H	16.64	16.97	17.60	17.93	19.17	16.23	16.56	17.19	17.52	18.76
12H	4H	15.69	16.15	16.62	17.09	18.27	15.32	15.78	16.25	16.72	17.90
	6H	16.34	16.71	17.29	17.67	18.86	15.96	16.34	16.91	17.30	18.49
	8H	16.57	16.90	17.52	17.85	19.09	16.19	16.52	17.14	17.47	18.71

END OF REPORT