

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914508

Luminaire Tested: DFN2DIP-SQ2F0-080D050US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914508
REPORT IS A COMBINATION OF REPORTS P899805 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D050US927-FLLFLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9779.5 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914508
CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P914508
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58	54		
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45		
3	84	74	67	61	79	70	63	58	62	57	52	55	50	47	48	45	42	38		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33		
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18		
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5422	5422	5422
5°	5422	5335	5375
10°	5368	5251	5295
15°	5280	5153	5174
20°	5164	5021	5050
25°	5048	4866	4908
30°	4905	4721	4729
35°	4769	4551	4541
40°	4604	4380	4361
45°	4438	4207	4177
50°	4256	4025	3964
55°	4065	3815	3766
60°	3848	3568	3540
65°	3611	3310	3273
70°	3309	2995	2984
75°	2895	2618	2706
80°	2392	2138	2198
85°	1615	1350	1381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4438 cd/sqm



TEST NUMBER: P914508

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.1	2.4
10°-20°	653.0	6.7
20°-30°	959.7	9.8
30°-40°	1114.6	11.4
40°-50°	1113.2	11.4
50°-60°	970.7	9.9
60°-70°	717.6	7.3
70°-80°	406.0	4.2
80°-90°	110.7	1.1
90°-100°	77.5	0.8
100°-110°	246.3	2.5
110°-120°	421.5	4.3
120°-130°	554.3	5.7
130°-140°	622.2	6.4
140°-150°	610.1	6.2
150°-160°	511.8	5.2
160°-170°	339.4	3.5
170°-180°	118.6	1.2
0°-30°	1844.8	18.9
0°-40°	2959.4	30.3
0°-60°	5043.4	51.6
0°-90°	6277.6	64.2
90°-120°	745.3	7.6
90°-150°	2532.0	25.9
90°-180°	3502.0	35.8
0°-180°	9779.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2466	2466	2466	2466	2466	
5°	2466	2457	2430	2449	2445	234
15°	2348	2333	2302	2312	2300	661
25°	2125	2106	2066	2070	2066	978
35°	1833	1809	1771	1757	1745	1145
45°	1492	1475	1439	1413	1404	1151
55°	1129	1114	1086	1058	1046	1009
65°	761	747	723	702	690	753
75°	398	394	382	368	372	425
85°	97	95	93	85	83	108
90°	1	14	37	35	36	9
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P914508

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.9	2465.9	2465.9	2465.9	2465.9
2.5°	2480.2	2468.4	2442.3	2465.9	2461.4
5°	2465.9	2456.6	2430.5	2449.3	2444.8
7.5°	2449.3	2435.2	2409.1	2428.2	2423.4
10°	2423.4	2406.8	2378.4	2397.2	2390.2
12.5°	2387.7	2373.6	2345.2	2357.0	2352.2
15°	2347.5	2333.4	2302.4	2312.0	2300.2
17.5°	2297.6	2283.5	2252.6	2264.4	2252.6
20°	2243.1	2229.0	2195.8	2202.8	2193.5
22.5°	2188.7	2167.3	2136.4	2136.4	2131.6
25°	2124.6	2105.7	2065.5	2070.0	2065.5
27.5°	2053.3	2036.8	2006.0	1999.0	1987.2
30°	1982.4	1963.3	1927.9	1920.8	1911.2
32.5°	1906.5	1892.4	1854.3	1840.0	1830.5
35°	1832.9	1809.3	1771.3	1757.0	1745.2
37.5°	1749.9	1728.5	1690.6	1674.0	1662.2
40°	1664.7	1645.5	1607.6	1586.4	1576.8
42.5°	1581.7	1562.5	1524.8	1500.9	1486.8
45°	1491.6	1475.0	1439.2	1413.3	1403.8
47.5°	1403.8	1387.2	1349.2	1323.0	1308.9
50°	1311.2	1299.4	1266.1	1233.0	1221.1
52.5°	1221.1	1204.5	1173.9	1147.7	1131.1
55°	1128.8	1114.4	1086.1	1057.6	1045.8
57.5°	1036.3	1024.4	993.5	965.0	955.4
60°	943.6	934.4	901.1	875.0	867.9
62.5°	853.6	837.0	813.3	789.7	780.1
65°	761.3	746.9	723.3	701.9	690.1
67.5°	666.4	654.3	633.2	616.6	607.0
70°	578.6	569.0	547.7	531.1	521.7
72.5°	488.5	479.0	467.1	450.6	443.5
75°	398.2	393.7	381.7	367.6	372.3
77.5°	317.7	308.2	303.4	296.4	289.3
80°	237.3	234.7	230.0	222.9	218.1
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5



TEST NUMBER: P914508

CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P914508
 CATALOG NUMBER: DFN2DIP-SQ2F0-080D050US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.25	15.25	15.07	16.10	17.15	13.80	14.81	14.63	15.65	16.71
	3H	15.90	16.80	16.73	17.66	18.74	15.41	16.31	16.24	17.17	18.25
	4H	16.48	17.33	17.33	18.19	19.29	15.98	16.84	16.84	17.70	18.79
	6H	16.87	17.66	17.74	18.53	19.63	16.37	17.16	17.24	18.03	19.13
	8H	16.97	17.72	17.85	18.61	19.71	16.47	17.22	17.34	18.11	19.21
	12H	17.02	17.73	17.90	18.61	19.75	16.51	17.22	17.39	18.11	19.24
4H	2H	14.71	15.57	15.57	16.43	17.52	14.36	15.21	15.22	16.07	17.16
	3H	16.57	17.28	17.44	18.18	19.28	16.16	16.87	17.03	17.77	18.88
	4H	17.27	17.92	18.16	18.81	19.95	16.85	17.50	17.73	18.39	19.52
	6H	17.78	18.34	18.68	19.26	20.39	17.35	17.91	18.24	18.82	19.96
	8H	17.92	18.45	18.82	19.36	20.51	17.48	18.01	18.38	18.92	20.07
	12H	17.99	18.46	18.91	19.40	20.55	17.54	18.02	18.46	18.95	20.10
8H	4H	17.47	17.99	18.37	18.91	20.05	17.09	17.62	17.99	18.53	19.68
	6H	18.08	18.52	19.01	19.47	20.62	17.70	18.13	18.63	19.09	20.23
	8H	18.29	18.68	19.23	19.62	20.79	17.90	18.28	18.84	19.23	20.39
	12H	18.42	18.76	19.36	19.69	20.91	18.01	18.35	18.95	19.28	20.50
12H	4H	17.46	17.93	18.38	18.86	20.02	17.09	17.56	18.01	18.49	19.65
	6H	18.11	18.49	19.05	19.44	20.61	17.74	18.12	18.67	19.07	20.23
	8H	18.34	18.68	19.28	19.62	20.84	17.96	18.30	18.90	19.24	20.45