

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903667

Luminaire Tested: DFN2DIP-SQ3F0-050D080US830-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903667  
REPORT IS A COMBINATION OF REPORTS P901456 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-050D080US830-RLLONL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11470.8 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 102.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903667  
CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P903667  
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36	30				30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26				26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22				22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19				19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21	17				17
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14				14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12				12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11				11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2232	2232	2232
5°	2234	2195	2210
10°	2210	2150	2137
15°	2179	2078	2025
20°	2137	1978	1888
25°	2094	1867	1756
30°	2037	1754	1588
35°	1982	1631	1441
40°	1925	1505	1273
45°	1859	1365	1120
50°	1791	1224	971
55°	1719	1074	828
60°	1636	916	681
65°	1541	757	612
70°	1425	608	552
75°	1280	533	501
80°	1070	442	432
85°	726	288	321

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1859 cd/sqm



TEST NUMBER: P903667

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.5	1.6
10°-20°	501.1	4.4
20°-30°	703.6	6.1
30°-40°	766.9	6.7
40°-50°	704.9	6.1
50°-60°	553.6	4.8
60°-70°	360.3	3.1
70°-80°	185.5	1.6
80°-90°	51.8	0.5
90°-100°	83.9	0.7
100°-110°	312.8	2.7
110°-120°	829.6	7.2
120°-130°	1376.0	12.0
130°-140°	1461.6	12.7
140°-150°	1358.4	11.8
150°-160°	1092.1	9.5
160°-170°	703.7	6.1
170°-180°	242.2	2.1
0°-30°	1387.2	12.1
0°-40°	2154.2	18.8
0°-60°	3412.7	29.8
0°-90°	4010.3	35.0
90°-120°	1226.4	10.7
90°-150°	5422.4	47.3
90°-180°	7460.0	65.0
0°-180°	11470.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	22	37	46	50	11
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P903667

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P903667

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8



TEST NUMBER: P903667  
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-RLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.31	9.03	9.39	10.11	11.58	4.27	4.99	5.35	6.07	7.54
	3H	9.98	10.62	11.07	11.71	13.20	5.45	6.09	6.54	7.18	8.67
	4H	10.58	11.19	11.68	12.27	13.77	5.89	6.50	6.99	7.58	9.08
	6H	10.99	11.55	12.10	12.64	14.15	6.20	6.76	7.31	7.85	9.36
	8H	11.11	11.64	12.22	12.75	14.25	6.28	6.81	7.39	7.92	9.42
	12H	11.17	11.67	12.28	12.77	14.30	6.32	6.82	7.43	7.92	9.45
4H	2H	8.31	8.92	9.42	10.01	11.51	4.85	5.46	5.96	6.55	8.05
	3H	10.13	10.64	11.24	11.75	13.26	6.18	6.69	7.30	7.81	9.32
	4H	10.81	11.28	11.93	12.38	13.91	6.72	7.19	7.84	8.29	9.82
	6H	11.32	11.72	12.44	12.84	14.37	7.13	7.53	8.25	8.66	10.18
	8H	11.49	11.86	12.61	12.98	14.52	7.25	7.62	8.38	8.74	10.28
	12H	11.57	11.91	12.72	13.04	14.59	7.31	7.64	8.45	8.78	10.32
8H	4H	10.77	11.14	11.89	12.26	13.80	6.99	7.36	8.12	8.48	10.02
	6H	11.33	11.63	12.47	12.80	14.33	7.50	7.80	8.64	8.97	10.50
	8H	11.54	11.81	12.69	12.95	14.50	7.68	7.95	8.83	9.09	10.65
	12H	11.67	11.91	12.82	13.04	14.63	7.79	8.03	8.95	9.17	10.76
12H	4H	10.72	11.05	11.86	12.19	13.73	6.99	7.33	8.13	8.46	10.00
	6H	11.30	11.57	12.45	12.71	14.27	7.54	7.81	8.70	8.95	10.51
	8H	11.51	11.75	12.67	12.89	14.48	7.74	7.98	8.90	9.12	10.71