

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917135

Luminaire Tested: DFN2DIP-SQ2F0-040D030US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917135
REPORT IS A COMBINATION OF REPORTS P901294 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D030US930-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5193.5 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 56.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917135
CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P917135
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53		
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46		
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39		
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34		
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	30		
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26		
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23		
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21		
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19		
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17		
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2964	2964	2964
5°	2963	2910	2931
10°	2929	2847	2832
15°	2883	2746	2681
20°	2825	2611	2496
25°	2765	2460	2318
30°	2687	2306	2095
35°	2609	2141	1898
40°	2530	1971	1673
45°	2439	1783	1470
50°	2344	1593	1271
55°	2245	1393	1081
60°	2129	1183	886
65°	1996	971	793
70°	1835	774	711
75°	1631	669	639
80°	1340	544	541
85°	872	338	386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2439 cd/sqm



TEST NUMBER: P917135
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.4
10°-20°	346.8	6.7
20°-30°	486.9	9.4
30°-40°	530.7	10.2
40°-50°	487.8	9.4
50°-60°	383.1	7.4
60°-70°	249.3	4.8
70°-80°	128.4	2.5
80°-90°	34.2	0.7
90°-100°	27.2	0.5
100°-110°	101.5	2.0
110°-120°	269.1	5.2
120°-130°	446.3	8.6
130°-140°	474.1	9.1
140°-150°	440.6	8.5
150°-160°	354.3	6.8
160°-170°	228.3	4.4
170°-180°	78.6	1.5
0°-30°	960.0	18.5
0°-40°	1490.7	28.7
0°-60°	2361.5	45.5
0°-90°	2773.5	53.4
90°-120°	397.8	7.7
90°-150°	1758.9	33.9
90°-180°	2420.0	46.6
0°-180°	5193.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	1	7	12	15	16	5
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	



TEST NUMBER: P917135

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2



TEST NUMBER: P917135

CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5



TEST NUMBER: P917135
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D030US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.12	11.98	12.05	12.92	14.15	7.08	7.94	8.01	8.88	10.11
	3H	12.78	13.55	13.73	14.50	15.75	8.25	9.02	9.20	9.98	11.22
	4H	13.38	14.10	14.34	15.06	16.32	8.69	9.42	9.65	10.38	11.63
	6H	13.78	14.45	14.75	15.42	16.69	9.00	9.67	9.97	10.63	11.90
	8H	13.90	14.54	14.88	15.52	16.79	9.08	9.71	10.06	10.70	11.96
	12H	13.96	14.56	14.94	15.54	16.83	9.12	9.72	10.10	10.70	11.99
4H	2H	11.14	11.86	12.10	12.82	14.08	7.67	8.39	8.63	9.35	10.61
	3H	12.95	13.55	13.92	14.54	15.81	9.00	9.60	9.97	10.59	11.86
	4H	13.62	14.17	14.61	15.16	16.45	9.53	10.08	10.52	11.07	12.36
	6H	14.12	14.59	15.12	15.60	16.90	9.93	10.41	10.93	11.42	12.71
	8H	14.29	14.73	15.28	15.73	17.04	10.05	10.49	11.05	11.50	12.80
	12H	14.37	14.77	15.39	15.79	17.10	10.11	10.51	11.12	11.52	12.84
8H	4H	13.59	14.03	14.59	15.03	16.34	9.80	10.25	10.80	11.25	12.55
	6H	14.13	14.50	15.16	15.54	16.85	10.30	10.66	11.32	11.71	13.01
	8H	14.34	14.66	15.37	15.69	17.01	10.48	10.80	11.51	11.83	13.15
	12H	14.46	14.75	15.50	15.77	17.14	10.58	10.86	11.61	11.89	13.26
12H	4H	13.54	13.94	14.56	14.96	16.27	9.81	10.20	10.82	11.22	12.53
	6H	14.11	14.43	15.14	15.46	16.78	10.34	10.66	11.37	11.69	13.02
	8H	14.32	14.60	15.35	15.62	16.99	10.54	10.82	11.57	11.84	13.21