

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917157

Luminaire Tested: DFN2DIP-SQ2F0-050D030US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917157
REPORT IS A COMBINATION OF REPORTS P901295 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D030US930-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6457.2 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3488	3488	3488
5°	3487	3431	3458
10°	3453	3378	3406
15°	3396	3315	3328
20°	3322	3230	3248
25°	3247	3130	3157
30°	3155	3037	3042
35°	3068	2928	2921
40°	2961	2817	2805
45°	2854	2706	2686
50°	2738	2589	2550
55°	2615	2454	2423
60°	2476	2295	2277
65°	2323	2129	2105
70°	2129	1927	1920
75°	1862	1684	1741
80°	1538	1375	1414
85°	1040	867	888

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2854 cd/sqm

TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.3	2.3
10°-20°	420.0	6.5
20°-30°	617.3	9.6
30°-40°	717.0	11.1
40°-50°	716.1	11.1
50°-60°	624.4	9.7
60°-70°	461.6	7.1
70°-80°	261.1	4.0
80°-90°	70.4	1.1
90°-100°	27.2	0.4
100°-110°	101.5	1.6
110°-120°	269.1	4.2
120°-130°	446.3	6.9
130°-140°	474.1	7.3
140°-150°	440.6	6.8
150°-160°	354.3	5.5
160°-170°	228.3	3.5
170°-180°	78.6	1.2
0°-30°	1186.6	18.4
0°-40°	1903.6	29.5
0°-60°	3244.1	50.2
0°-90°	4037.2	62.5
90°-120°	397.8	6.2
90°-150°	1758.9	27.2
90°-180°	2420.0	37.5
0°-180°	6457.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1576	1573	151
15°	1510	1501	1481	1487	1480	425
25°	1367	1354	1328	1332	1328	629
35°	1179	1164	1139	1130	1123	736
45°	959	949	926	909	903	740
55°	726	717	698	680	673	649
65°	490	480	465	452	444	484
75°	256	253	246	236	240	273
85°	62	61	60	55	53	70
90°	1	7	12	15	16	6
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	

TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1586.2	1586.2	1586.2	1586.2	1586.2
2.5°	1595.4	1587.8	1571.0	1586.2	1583.3
5°	1586.2	1580.2	1563.3	1575.5	1572.6
7.5°	1575.5	1566.4	1549.6	1561.9	1558.9
10°	1558.9	1548.2	1529.9	1542.0	1537.5
12.5°	1535.9	1526.8	1508.5	1516.1	1513.0
15°	1509.9	1500.9	1481.0	1487.2	1479.5
17.5°	1477.9	1468.8	1448.9	1456.5	1448.9
20°	1442.8	1433.8	1412.4	1416.9	1411.0
22.5°	1407.9	1394.1	1374.2	1374.2	1371.1
25°	1366.6	1354.5	1328.5	1331.5	1328.5
27.5°	1320.8	1310.1	1290.4	1285.8	1278.2
30°	1275.1	1262.9	1240.1	1235.5	1229.4
32.5°	1226.3	1217.2	1192.8	1183.6	1177.5
35°	1179.0	1163.8	1139.4	1130.2	1122.6
37.5°	1125.6	1111.9	1087.4	1076.8	1069.2
40°	1070.8	1058.5	1034.0	1020.4	1014.3
42.5°	1017.4	1005.1	980.8	965.4	956.3
45°	959.4	948.8	925.8	909.1	902.9
47.5°	902.9	892.3	867.9	851.0	842.0
50°	843.4	835.8	814.5	793.1	785.5
52.5°	785.5	774.8	755.0	738.3	727.6
55°	726.1	716.9	698.5	680.3	672.7
57.5°	666.5	658.9	639.0	620.8	614.6
60°	607.0	601.0	579.7	562.8	558.3
62.5°	549.1	538.4	523.2	507.9	501.8
65°	489.7	480.5	465.2	451.5	443.8
67.5°	428.7	420.9	407.3	396.6	390.4
70°	372.2	366.1	352.3	341.6	335.7
72.5°	314.3	308.1	300.5	289.8	285.3
75°	256.2	253.2	245.5	236.4	239.5
77.5°	204.4	198.2	195.2	190.6	186.1
80°	152.6	151.0	147.9	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.5	61.0	59.5	54.9	53.4
87.5°	27.5	24.5	21.4	16.8	15.2
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2

TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5

TEST NUMBER: P917157

CATALOG NUMBER: DFN2DIP-SQ2F0-050D030US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.58	13.56	13.42	14.43	15.51	12.13	13.12	12.98	13.98	15.07
	3H	14.23	15.11	15.08	15.99	17.10	13.74	14.62	14.59	15.50	16.61
	4H	14.81	15.65	15.68	16.53	17.64	14.32	15.15	15.19	16.03	17.15
	6H	15.20	15.97	16.08	16.86	17.99	14.70	15.47	15.58	16.36	17.49
	8H	15.30	16.04	16.19	16.94	18.07	14.80	15.54	15.69	16.44	17.57
	12H	15.35	16.05	16.24	16.95	18.10	14.84	15.54	15.74	16.44	17.59
4H	2H	13.04	13.88	13.92	14.76	15.88	12.69	13.53	13.56	14.41	15.52
	3H	14.90	15.60	15.78	16.51	17.64	14.49	15.19	15.38	16.10	17.23
	4H	15.60	16.24	16.50	17.15	18.31	15.18	15.81	16.08	16.72	17.88
	6H	16.11	16.66	17.02	17.59	18.75	15.67	16.22	16.59	17.16	18.32
	8H	16.25	16.76	17.16	17.69	18.86	15.81	16.33	16.73	17.25	18.43
	12H	16.32	16.78	17.25	17.73	18.91	15.87	16.33	16.81	17.28	18.46
8H	4H	15.80	16.31	16.71	17.24	18.41	15.42	15.93	16.33	16.86	18.03
	6H	16.41	16.84	17.35	17.80	18.98	16.02	16.45	16.97	17.42	18.59
	8H	16.62	17.00	17.57	17.95	19.15	16.22	16.60	17.18	17.56	18.75
	12H	16.74	17.07	17.70	18.03	19.27	16.33	16.66	17.29	17.62	18.86
12H	4H	15.79	16.25	16.72	17.19	18.37	15.42	15.88	16.35	16.82	18.00
	6H	16.44	16.81	17.39	17.77	18.96	16.06	16.44	17.01	17.40	18.59
	8H	16.67	17.00	17.62	17.95	19.19	16.29	16.62	17.24	17.57	18.81

END OF REPORT