

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917206

Luminaire Tested: DFN2DIP-SQ2F0-070D030US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917206
REPORT IS A COMBINATION OF REPORTS P899780 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-070D030US930-RLFL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7015.6 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	66	65	64
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5187	5187	5187
5°	5186	5093	5130
10°	5126	4982	4956
15°	5046	4806	4691
20°	4944	4569	4369
25°	4839	4305	4057
30°	4701	4035	3666
35°	4566	3746	3321
40°	4427	3448	2928
45°	4268	3120	2572
50°	4102	2789	2224
55°	3928	2437	1891
60°	3726	2070	1550
65°	3493	1699	1387
70°	3211	1354	1244
75°	2855	1171	1118
80°	2344	952	947
85°	1525	590	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4268 cd/sqm

TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	3.2
10°-20°	606.9	8.7
20°-30°	852.0	12.1
30°-40°	928.8	13.2
40°-50°	853.6	12.2
50°-60°	670.4	9.6
60°-70°	436.4	6.2
70°-80°	224.6	3.2
80°-90°	59.5	0.8
90°-100°	47.9	0.7
100°-110°	152.1	2.2
110°-120°	260.3	3.7
120°-130°	342.3	4.9
130°-140°	384.2	5.5
140°-150°	376.8	5.4
150°-160°	316.1	4.5
160°-170°	209.6	3.0
170°-180°	73.3	1.0
0°-30°	1679.9	23.9
0°-40°	2608.7	37.2
0°-60°	4132.7	58.9
0°-90°	4853.2	69.2
90°-120°	460.2	6.6
90°-150°	1563.5	22.3
90°-180°	2162.0	30.8
0°-180°	7015.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	8	23	21	22	7
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P917206

CATALOG NUMBER: DFN2DIP-SQ2F0-070D030US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.38	15.39	15.16	16.19	17.16	10.34	11.36	11.12	12.15	13.12
	3H	16.05	16.96	16.84	17.77	18.77	11.52	12.43	12.32	13.24	14.24
	4H	16.65	17.51	17.47	18.33	19.34	11.97	12.83	12.78	13.64	14.65
	6H	17.07	17.86	17.89	18.68	19.71	12.28	13.07	13.11	13.90	14.92
	8H	17.19	17.94	18.03	18.79	19.81	12.37	13.12	13.20	13.96	14.99
	12H	17.25	17.97	18.09	18.80	19.86	12.41	13.13	13.25	13.96	15.01
4H	2H	14.41	15.27	15.23	16.09	17.10	10.95	11.80	11.76	12.62	13.63
	3H	16.24	16.95	17.06	17.80	18.83	12.29	13.00	13.12	13.85	14.88
	4H	16.92	17.57	17.76	18.42	19.47	12.83	13.48	13.67	14.33	15.38
	6H	17.43	17.99	18.28	18.86	19.92	13.24	13.80	14.10	14.67	15.73
	8H	17.60	18.12	18.46	18.98	20.06	13.36	13.88	14.22	14.75	15.82
	12H	17.69	18.16	18.57	19.04	20.12	13.43	13.89	14.31	14.78	15.86
8H	4H	16.90	17.42	17.76	18.29	19.36	13.11	13.63	13.97	14.50	15.57
	6H	17.45	17.88	18.34	18.79	19.86	13.61	14.04	14.50	14.95	16.03
	8H	17.65	18.04	18.55	18.94	20.03	13.79	14.17	14.69	15.08	16.17
	12H	17.79	18.12	18.69	19.02	20.16	13.90	14.24	14.80	15.13	16.28
12H	4H	16.86	17.33	17.74	18.21	19.29	13.12	13.59	14.00	14.48	15.56
	6H	17.42	17.81	18.32	18.71	19.80	13.66	14.04	14.56	14.94	16.03
	8H	17.64	17.97	18.54	18.87	20.01	13.86	14.20	14.76	15.09	16.24