

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903737

Luminaire Tested: DFN2DIP-SQ3F0-070D080US830-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P903737  
REPORT IS A COMBINATION OF REPORTS P901459 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-070D080US830-FLLONL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13996.8 lumens  
Efficiency: N/A  
Efficacy: 111.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 126  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903737  
CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P903737

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39	39	39	39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33	33	33	33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28	28	28	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	27	24	21	21	21	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21	18	18	18	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16	16	16	16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17	15	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2942	2942	2942
5°	2944	2899	2919
10°	2919	2858	2879
15°	2874	2809	2816
20°	2814	2741	2752
25°	2754	2661	2678
30°	2680	2586	2584
35°	2610	2499	2485
40°	2523	2410	2390
45°	2437	2321	2293
50°	2342	2227	2181
55°	2243	2119	2078
60°	2131	1991	1960
65°	2008	1858	1820
70°	1852	1695	1670
75°	1636	1500	1530
80°	1375	1252	1265
85°	968	830	827

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2437 cd/sqm



TEST NUMBER: P903737

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	241.6	1.7
10°-20°	679.9	4.9
20°-30°	999.1	7.1
30°-40°	1160.4	8.3
40°-50°	1159.0	8.3
50°-60°	1010.6	7.2
60°-70°	747.1	5.3
70°-80°	422.7	3.0
80°-90°	116.0	0.8
90°-100°	83.9	0.6
100°-110°	312.8	2.2
110°-120°	829.6	5.9
120°-130°	1376.0	9.8
130°-140°	1461.6	10.4
140°-150°	1358.4	9.7
150°-160°	1092.1	7.8
160°-170°	703.7	5.0
170°-180°	242.2	1.7
0°-30°	1920.6	13.7
0°-40°	3081.0	22.0
0°-60°	5250.6	37.5
0°-90°	6536.3	46.7
90°-120°	1226.4	8.8
90°-150°	5422.4	38.7
90°-180°	7460.0	53.3
0°-180°	13996.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2395	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	793	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	2	22	37	46	50	13
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P903737

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2567.2	2567.2	2567.2	2567.2	2567.2
2.5°	2582.2	2569.8	2542.6	2567.2	2562.5
5°	2567.2	2557.6	2530.3	2550.0	2545.2
7.5°	2550.0	2535.3	2508.0	2528.0	2523.0
10°	2523.0	2505.7	2476.1	2495.8	2488.4
12.5°	2485.8	2471.2	2441.6	2453.8	2448.8
15°	2443.9	2429.2	2397.0	2407.0	2394.6
17.5°	2392.0	2377.4	2345.1	2357.5	2345.1
20°	2335.1	2320.5	2285.9	2293.3	2283.6
22.5°	2278.6	2256.4	2224.1	2224.1	2219.1
25°	2211.9	2192.2	2150.3	2155.0	2150.3
27.5°	2137.7	2120.4	2088.5	2081.1	2068.8
30°	2063.9	2043.9	2007.0	1999.7	1989.7
32.5°	1984.7	1970.1	1930.5	1915.6	1905.6
35°	1908.3	1883.7	1844.1	1829.2	1816.8
37.5°	1821.8	1799.6	1760.0	1742.8	1730.4
40°	1733.1	1713.2	1673.6	1651.6	1641.6
42.5°	1646.6	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.6	1498.4	1471.4	1461.4
47.5°	1461.4	1444.2	1404.6	1377.3	1362.7
50°	1365.1	1352.7	1318.1	1283.6	1271.3
52.5°	1271.3	1254.1	1222.1	1194.9	1177.5
55°	1175.2	1160.3	1130.7	1101.1	1088.7
57.5°	1078.8	1066.5	1034.3	1004.7	994.8
60°	982.4	972.7	938.2	911.0	903.6
62.5°	888.6	871.4	846.8	822.2	812.2
65°	792.6	777.6	753.0	730.8	718.4
67.5°	693.8	681.3	659.2	642.0	632.0
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.4	469.1	461.8
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.1	227.1
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P903737

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8



TEST NUMBER: P903737  
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.67	11.51	11.66	12.50	13.82	10.23	11.06	11.21	12.06	13.38
	3H	12.33	13.07	13.32	14.08	15.42	11.84	12.58	12.83	13.59	14.93
	4H	12.91	13.62	13.92	14.63	15.97	12.42	13.12	13.43	14.13	15.48
	6H	13.31	13.96	14.32	14.97	16.33	12.81	13.46	13.82	14.47	15.83
	8H	13.41	14.03	14.43	15.06	16.41	12.91	13.53	13.93	14.56	15.91
	12H	13.45	14.04	14.48	15.07	16.45	12.94	13.53	13.97	14.56	15.94
4H	2H	11.13	11.83	12.14	12.84	14.19	10.77	11.48	11.79	12.49	13.84
	3H	12.98	13.57	14.01	14.61	15.97	12.58	13.17	13.60	14.21	15.57
	4H	13.69	14.23	14.73	15.26	16.65	13.27	13.81	14.30	14.84	16.22
	6H	14.20	14.67	15.24	15.72	17.10	13.77	14.24	14.81	15.29	16.67
	8H	14.35	14.78	15.39	15.83	17.22	13.91	14.35	14.96	15.39	16.79
	12H	14.42	14.81	15.48	15.87	17.27	13.97	14.36	15.03	15.42	16.82
8H	4H	13.88	14.32	14.93	15.36	16.76	13.51	13.94	14.55	14.99	16.38
	6H	14.51	14.87	15.57	15.96	17.35	14.12	14.48	15.19	15.57	16.96
	8H	14.73	15.04	15.80	16.11	17.52	14.33	14.65	15.41	15.72	17.13
	12H	14.85	15.13	15.93	16.20	17.65	14.44	14.72	15.52	15.79	17.24
12H	4H	13.87	14.26	14.93	15.32	16.72	13.50	13.89	14.56	14.95	16.35
	6H	14.54	14.85	15.61	15.92	17.34	14.16	14.48	15.24	15.55	16.96
	8H	14.77	15.05	15.85	16.12	17.57	14.39	14.67	15.47	15.74	17.19