

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917226

Luminaire Tested: DFN2DIP-SQ2F0-070D080US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P917226  
REPORT IS A COMBINATION OF REPORTS P899840 AND P896659  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-070D080US930-RLLFLL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10623.3 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 132.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P917226  
CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P917226

CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15	15	15	15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5187	5187	5187
5°	5186	5093	5130
10°	5126	4982	4956
15°	5046	4806	4691
20°	4944	4569	4369
25°	4839	4305	4057
30°	4701	4035	3666
35°	4566	3746	3321
40°	4427	3448	2928
45°	4268	3120	2572
50°	4102	2789	2224
55°	3928	2437	1891
60°	3726	2070	1550
65°	3493	1699	1387
70°	3211	1354	1244
75°	2855	1171	1118
80°	2344	952	947
85°	1525	590	674

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4268 cd/sqm



TEST NUMBER: P917226

CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.1	2.1
10°-20°	606.9	5.7
20°-30°	852.0	8.0
30°-40°	928.8	8.7
40°-50°	853.6	8.0
50°-60°	670.4	6.3
60°-70°	436.4	4.1
70°-80°	224.6	2.1
80°-90°	63.2	0.6
90°-100°	127.6	1.2
100°-110°	405.6	3.8
110°-120°	694.1	6.5
120°-130°	912.8	8.6
130°-140°	1024.6	9.6
140°-150°	1004.7	9.5
150°-160°	842.8	7.9
160°-170°	558.9	5.3
170°-180°	195.4	1.8
0°-30°	1679.9	15.8
0°-40°	2608.7	24.6
0°-60°	4132.7	38.9
0°-90°	4856.9	45.7
90°-120°	1227.3	11.6
90°-150°	4169.4	39.2
90°-180°	5766.0	54.3
0°-180°	10623.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	2	22	61	57	59	10
95°	91	108	111	111	108	101
105°	374	379	383	386	386	395
115°	696	706	703	702	696	689
125°	1013	1029	1024	1018	1016	905
135°	1310	1330	1333	1332	1326	1013
145°	1591	1603	1613	1615	1608	994
155°	1819	1824	1830	1838	1833	837
165°	1979	1977	1977	1989	1981	558
175°	2059	2054	2050	2063	2052	196
180°	2063	2063	2063	2063	2063	



TEST NUMBER: P917226

CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	1.9	22.4	61.0	57.2	59.1
92.5°	38.6	52.3	54.1	55.9	55.9
95°	90.8	108.2	111.3	111.3	108.2
97.5°	151.2	167.3	174.1	174.1	174.1
100°	220.8	235.1	240.0	240.0	238.1
102.5°	294.2	304.8	311.5	313.4	311.5
105°	374.4	379.4	383.1	386.2	386.2
107.5°	454.0	461.5	461.5	462.7	454.0
110°	531.1	541.0	541.0	541.0	536.1



TEST NUMBER: P917226

CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	614.4	625.0	623.1	618.2	614.4
115°	696.5	706.5	703.4	701.5	696.5
117.5°	778.0	791.7	782.9	778.0	773.0
120°	860.1	873.8	860.1	860.1	854.4
122.5°	934.7	952.1	943.4	938.4	934.7
125°	1013.0	1028.6	1023.6	1018.0	1016.2
127.5°	1089.6	1108.8	1102.0	1094.5	1089.6
130°	1161.1	1183.4	1180.3	1176.6	1169.8
132.5°	1241.3	1258.7	1260.0	1251.2	1246.3
135°	1310.3	1329.6	1333.3	1331.5	1326.5
137.5°	1387.4	1403.0	1406.1	1404.8	1397.3
140°	1455.2	1470.7	1479.4	1479.4	1472.6
142.5°	1524.9	1540.4	1545.4	1547.3	1540.4
145°	1590.8	1603.2	1613.1	1615.0	1608.2
147.5°	1649.8	1665.4	1672.8	1676.0	1669.2
150°	1710.8	1721.3	1728.2	1733.8	1728.2
152.5°	1764.9	1775.5	1784.2	1791.0	1784.2
155°	1819.0	1824.0	1829.6	1838.3	1832.7
157.5°	1865.6	1869.4	1872.5	1884.9	1876.2
160°	1907.3	1911.1	1912.9	1923.5	1916.0
162.5°	1945.9	1945.9	1947.7	1959.6	1950.8
165°	1978.8	1976.9	1976.9	1989.4	1980.7
167.5°	2008.7	2003.1	2003.1	2015.5	2006.8
170°	2031.1	2026.1	2024.2	2036.7	2026.1
172.5°	2046.6	2041.7	2039.8	2052.2	2041.7
175°	2059.0	2054.1	2050.3	2062.8	2052.2
177.5°	2065.9	2060.9	2057.2	2067.8	2057.2
180°	2062.8	2062.8	2062.8	2062.8	2062.8



TEST NUMBER: P917226  
 CATALOG NUMBER: DFN2DIP-SQ2F0-070D080US930-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.34	13.13	13.33	14.14	15.47	8.30	9.09	9.30	10.10	11.43
	3H	13.99	14.70	15.00	15.72	17.07	9.46	10.18	10.47	11.19	12.55
	4H	14.58	15.26	15.61	16.28	17.64	9.90	10.57	10.92	11.59	12.95
	6H	14.99	15.61	16.02	16.63	18.01	10.20	10.82	11.24	11.85	13.22
	8H	15.11	15.70	16.14	16.73	18.10	10.28	10.87	11.32	11.91	13.28
	12H	15.16	15.72	16.20	16.75	18.15	10.32	10.88	11.36	11.91	13.30
4H	2H	12.34	13.02	13.37	14.04	15.40	8.88	9.55	9.91	10.57	11.93
	3H	14.15	14.71	15.19	15.76	17.13	10.20	10.76	11.24	11.81	13.18
	4H	14.82	15.34	15.87	16.37	17.77	10.73	11.25	11.78	12.28	13.68
	6H	15.32	15.76	16.37	16.82	18.21	11.13	11.57	12.19	12.63	14.03
	8H	15.48	15.89	16.54	16.95	18.36	11.25	11.66	12.30	12.71	14.12
	12H	15.56	15.94	16.64	17.00	18.42	11.30	11.67	12.37	12.74	14.16
8H	4H	14.78	15.20	15.84	16.25	17.66	11.00	11.41	12.05	12.46	13.87
	6H	15.33	15.67	16.41	16.76	18.17	11.49	11.83	12.57	12.93	14.33
	8H	15.53	15.83	16.62	16.91	18.33	11.67	11.97	12.75	13.05	14.47
	12H	15.65	15.92	16.74	16.99	18.46	11.77	12.03	12.86	13.11	14.57
12H	4H	14.73	15.10	15.81	16.17	17.59	11.00	11.37	12.07	12.44	13.85
	6H	15.30	15.60	16.39	16.68	18.10	11.54	11.83	12.62	12.91	14.34
	8H	15.51	15.77	16.59	16.84	18.31	11.73	11.99	12.82	13.07	14.53