

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917241

Luminaire Tested: DFN2DIP-SQ2F0-080D060US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917241
REPORT IS A COMBINATION OF REPORTS P901337 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D060US930-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11300.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		63	63	63
1	99	95	91	88		92	89	85	82		77	74	72		66	64	62		55	54	53
2	91	83	77	72		84	77	72	67		67	63	59		58	55	52		49	47	45
3	83	73	66	60		77	68	62	56		59	54	50		51	47	44		43	40	38
4	76	65	57	50		70	61	53	48		53	47	43		45	41	38		39	35	33
5	69	58	49	43		64	54	47	41		47	41	37		41	36	33		35	31	29
6	64	52	44	38		59	49	41	36		43	37	32		37	32	29		32	28	25
7	59	47	39	33		55	44	37	31		39	33	28		34	29	25		29	25	22
8	55	43	35	29		51	40	33	28		35	29	25		31	26	23		27	23	20
9	51	39	31	26		48	37	30	25		32	27	23		28	24	20		25	21	18
10	48	36	28	24		45	34	27	22		30	24	20		26	22	18		23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5581	5581	5581
5°	5580	5491	5532
10°	5525	5405	5449
15°	5434	5303	5325
20°	5314	5168	5197
25°	5195	5008	5051
30°	5049	4858	4867
35°	4908	4684	4673
40°	4738	4507	4488
45°	4567	4329	4299
50°	4381	4142	4080
55°	4184	3927	3876
60°	3961	3672	3643
65°	3716	3406	3369
70°	3406	3083	3071
75°	2980	2694	2786
80°	2461	2200	2263
85°	1664	1389	1421

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4567 cd/sqm

TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.9	2.1
10°-20°	672.1	5.9
20°-30°	987.7	8.7
30°-40°	1147.1	10.2
40°-50°	1145.7	10.1
50°-60°	999.0	8.8
60°-70°	738.5	6.5
70°-80°	417.8	3.7
80°-90°	113.2	1.0
90°-100°	54.4	0.5
100°-110°	202.9	1.8
110°-120°	538.2	4.8
120°-130°	892.7	7.9
130°-140°	948.2	8.4
140°-150°	881.3	7.8
150°-160°	708.5	6.3
160°-170°	456.5	4.0
170°-180°	157.1	1.4
0°-30°	1898.6	16.8
0°-40°	3045.8	27.0
0°-60°	5190.5	45.9
0°-90°	6460.1	57.2
90°-120°	795.6	7.0
90°-150°	3517.8	31.1
90°-180°	4840.0	42.8
0°-180°	11300.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2538	2538	2538	2538	2538	
5°	2538	2528	2501	2521	2516	241
15°	2416	2402	2370	2379	2367	680
25°	2186	2167	2126	2130	2126	1006
35°	1886	1862	1823	1808	1796	1178
45°	1535	1518	1481	1455	1445	1185
55°	1162	1147	1118	1088	1076	1039
65°	784	769	744	722	710	775
75°	410	405	393	378	383	438
85°	100	98	95	88	85	112
90°	1	14	24	30	32	10
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	

TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2537.9	2537.9	2537.9	2537.9	2537.9
2.5°	2552.6	2540.5	2513.6	2537.9	2533.2
5°	2537.9	2528.3	2501.4	2520.8	2516.2
7.5°	2520.8	2506.3	2479.4	2499.1	2494.2
10°	2494.2	2477.0	2447.8	2467.2	2460.0
12.5°	2457.4	2442.9	2413.6	2425.8	2420.9
15°	2416.0	2401.5	2369.6	2379.4	2367.3
17.5°	2364.7	2350.2	2318.3	2330.5	2318.3
20°	2308.5	2294.0	2259.8	2267.1	2257.5
22.5°	2252.6	2230.6	2198.7	2198.7	2193.8
25°	2186.5	2167.1	2125.7	2130.4	2125.7
27.5°	2113.3	2096.2	2064.6	2057.3	2045.2
30°	2040.3	2020.6	1984.1	1976.9	1967.0
32.5°	1962.1	1947.6	1908.5	1893.7	1883.9
35°	1886.4	1862.1	1823.0	1808.2	1796.1
37.5°	1801.0	1779.0	1739.9	1722.8	1710.7
40°	1713.3	1693.5	1654.5	1632.7	1622.9
42.5°	1627.8	1608.1	1569.3	1544.7	1530.2
45°	1535.1	1518.0	1481.2	1454.6	1444.8
47.5°	1444.8	1427.7	1388.5	1361.6	1347.1
50°	1349.5	1337.3	1303.1	1268.9	1256.8
52.5°	1256.8	1239.7	1208.1	1181.2	1164.1
55°	1161.7	1147.0	1117.8	1088.5	1076.3
57.5°	1066.5	1054.3	1022.5	993.2	983.3
60°	971.2	961.6	927.4	900.5	893.2
62.5°	878.5	861.4	837.1	812.8	802.9
65°	783.5	768.7	744.4	722.4	710.2
67.5°	685.8	673.4	651.7	634.6	624.8
70°	595.5	585.6	563.7	546.6	537.0
72.5°	502.8	493.0	480.8	463.7	456.5
75°	409.9	405.2	392.8	378.3	383.2
77.5°	327.0	317.2	312.3	305.0	297.7
80°	244.2	241.6	236.7	229.4	224.5
82.5°	166.0	166.0	163.6	153.8	153.8
85°	100.0	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.2	26.9	24.4
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3

TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9

TEST NUMBER: P917241

CATALOG NUMBER: DFN2DIP-SQ2F0-080D060US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.77	14.70	14.66	15.61	16.77	13.32	14.25	14.22	15.17	16.33
	3H	15.41	16.25	16.32	17.17	18.36	14.92	15.76	15.83	16.68	17.87
	4H	15.99	16.78	16.91	17.71	18.91	15.50	16.29	16.42	17.21	18.41
	6H	16.38	17.11	17.31	18.04	19.25	15.88	16.61	16.81	17.54	18.75
	8H	16.48	17.17	17.42	18.12	19.33	15.98	16.67	16.92	17.62	18.83
	12H	16.52	17.18	17.47	18.13	19.36	16.01	16.67	16.96	17.62	18.85
4H	2H	14.23	15.01	15.15	15.94	17.14	13.87	14.66	14.80	15.59	16.79
	3H	16.07	16.73	17.01	17.69	18.91	15.67	16.33	16.60	17.28	18.50
	4H	16.78	17.38	17.72	18.33	19.57	16.35	16.95	17.30	17.91	19.15
	6H	17.28	17.80	18.24	18.77	20.01	16.84	17.36	17.80	18.34	19.58
	8H	17.42	17.90	18.38	18.87	20.13	16.98	17.47	17.94	18.44	19.69
	12H	17.49	17.92	18.47	18.91	20.17	17.04	17.48	18.02	18.46	19.72
8H	4H	16.97	17.45	17.93	18.42	19.68	16.59	17.07	17.55	18.04	19.30
	6H	17.58	17.98	18.56	18.99	20.24	17.19	17.59	18.18	18.61	19.86
	8H	17.79	18.14	18.78	19.14	20.41	17.39	17.75	18.39	18.75	20.02
	12H	17.91	18.22	18.91	19.21	20.53	17.50	17.81	18.50	18.80	20.12
12H	4H	16.95	17.39	17.93	18.38	19.64	16.58	17.02	17.56	18.01	19.27
	6H	17.60	17.96	18.60	18.96	20.23	17.23	17.58	18.23	18.58	19.85
	8H	17.83	18.14	18.83	19.14	20.46	17.45	17.76	18.45	18.76	20.07