

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919877

Luminaire Tested: DFN2DIP-SQ2F0-040D070US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919877
REPORT IS A COMBINATION OF REPORTS P901341 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D070US935-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9376.3 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919877
CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P919877

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31				31
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31	26				26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22				22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19				19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16				16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14				14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13				13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10				10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2947	2947	2947
5°	2946	2899	2921
10°	2917	2854	2877
15°	2869	2800	2812
20°	2806	2729	2744
25°	2743	2644	2667
30°	2666	2565	2570
35°	2592	2473	2468
40°	2502	2380	2370
45°	2411	2286	2270
50°	2313	2187	2154
55°	2209	2073	2047
60°	2091	1939	1924
65°	1962	1798	1779
70°	1798	1627	1621
75°	1574	1423	1471
80°	1299	1161	1195
85°	878	733	750

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2411 cd/sqm



TEST NUMBER: P919877

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	1.3
10°-20°	354.9	3.8
20°-30°	521.5	5.6
30°-40°	605.7	6.5
40°-50°	605.0	6.5
50°-60°	527.5	5.6
60°-70°	389.9	4.2
70°-80°	220.6	2.4
80°-90°	61.8	0.7
90°-100°	67.1	0.7
100°-110°	250.0	2.7
110°-120°	663.1	7.1
120°-130°	1099.8	11.7
130°-140°	1168.3	12.5
140°-150°	1085.8	11.6
150°-160°	872.9	9.3
160°-170°	562.5	6.0
170°-180°	193.6	2.1
0°-30°	1002.5	10.7
0°-40°	1608.3	17.2
0°-60°	2740.7	29.2
0°-90°	3413.1	36.4
90°-120°	980.2	10.5
90°-150°	4334.1	46.2
90°-180°	5963.0	63.6
0°-180°	9376.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	18	29	37	40	9
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	



TEST NUMBER: P919877

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P919877

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0



TEST NUMBER: P919877
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.50	10.26	10.57	11.32	12.78	9.06	9.81	10.13	10.88	12.33
	3H	11.14	11.81	12.21	12.89	14.36	10.65	11.32	11.72	12.40	13.87
	4H	11.71	12.35	12.79	13.42	14.90	11.21	11.85	12.30	12.93	14.41
	6H	12.09	12.67	13.18	13.76	15.24	11.59	12.17	12.68	13.26	14.75
	8H	12.18	12.74	13.28	13.84	15.32	11.68	12.24	12.78	13.34	14.82
	12H	12.22	12.75	13.32	13.84	15.35	11.71	12.24	12.81	13.33	14.84
4H	2H	9.94	10.58	11.03	11.66	13.14	9.59	10.22	10.68	11.30	12.78
	3H	11.77	12.31	12.87	13.41	14.90	11.37	11.90	12.47	13.00	14.49
	4H	12.47	12.96	13.57	14.05	15.56	12.04	12.53	13.15	13.63	15.14
	6H	12.96	13.38	14.07	14.50	16.00	12.53	12.95	13.64	14.06	15.57
	8H	13.10	13.49	14.21	14.60	16.12	12.66	13.05	13.77	14.16	15.68
	12H	13.15	13.51	14.28	14.63	16.16	12.71	13.06	13.84	14.18	15.71
8H	4H	12.64	13.04	13.76	14.15	15.67	12.27	12.66	13.38	13.77	15.29
	6H	13.25	13.57	14.38	14.72	16.24	12.86	13.19	14.00	14.34	15.86
	8H	13.45	13.74	14.59	14.87	16.41	13.06	13.34	14.20	14.48	16.01
	12H	13.57	13.82	14.71	14.95	16.52	13.16	13.41	14.30	14.54	16.11
12H	4H	12.62	12.98	13.75	14.10	15.63	12.25	12.61	13.38	13.73	15.26
	6H	13.27	13.55	14.41	14.69	16.22	12.90	13.18	14.04	14.31	15.85
	8H	13.49	13.74	14.64	14.87	16.44	13.11	13.36	14.26	14.49	16.06