

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903868

Luminaire Tested: DFN2DIP-SQ3F0-110D050US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903868
REPORT IS A COMBINATION OF REPORTS P899893 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D050US830-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14435.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 148.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	30
7	61	49	40	35	58	46	39	33	42	36	31	39	33	29	35	30	27
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24
9	53	41	33	28	50	39	32	27	36	29	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4623	4623	4623
5°	4627	4555	4587
10°	4586	4491	4524
15°	4516	4414	4425
20°	4422	4308	4324
25°	4328	4182	4208
30°	4212	4064	4060
35°	4101	3926	3904
40°	3965	3787	3756
45°	3829	3647	3604
50°	3681	3500	3428
55°	3525	3330	3266
60°	3349	3128	3080
65°	3156	2919	2861
70°	2910	2664	2624
75°	2571	2358	2404
80°	2161	1967	1987
85°	1522	1304	1300

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3829 cd/sqm

TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	2.6
10°-20°	1068.3	7.4
20°-30°	1570.0	10.9
30°-40°	1823.5	12.6
40°-50°	1821.2	12.6
50°-60°	1588.0	11.0
60°-70°	1173.9	8.1
70°-80°	664.2	4.6
80°-90°	179.5	1.2
90°-100°	92.2	0.6
100°-110°	293.0	2.0
110°-120°	501.5	3.5
120°-130°	659.5	4.6
130°-140°	740.3	5.1
140°-150°	725.9	5.0
150°-160°	609.0	4.2
160°-170°	403.9	2.8
170°-180°	141.2	1.0
0°-30°	3018.1	20.9
0°-40°	4841.6	33.5
0°-60°	8250.9	57.2
0°-90°	10268.5	71.1
90°-120°	886.7	6.1
90°-150°	3012.5	20.9
90°-180°	4167.0	28.9
0°-180°	14435.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3767	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1873
45°	2440	2413	2355	2312	2297	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	696
85°	159	155	152	140	136	177
90°	1	16	44	41	43	14
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.3	4034.3	4034.3	4034.3	4034.3
2.5°	4057.6	4038.3	3995.5	4034.3	4026.8
5°	4034.3	4019.0	3976.2	4007.0	3999.7
7.5°	4007.0	3984.0	3941.2	3972.5	3964.7
10°	3964.7	3937.5	3891.0	3921.8	3910.3
12.5°	3906.3	3883.2	3836.7	3856.0	3848.2
15°	3840.4	3817.3	3766.7	3782.3	3763.0
17.5°	3758.9	3735.9	3685.2	3704.6	3685.2
20°	3669.6	3646.5	3592.2	3603.7	3588.5
22.5°	3580.7	3545.7	3495.0	3495.0	3487.2
25°	3475.7	3444.9	3379.0	3386.5	3379.0
27.5°	3359.2	3332.1	3281.8	3270.3	3251.0
30°	3243.2	3211.9	3153.8	3142.3	3126.7
32.5°	3118.9	3095.9	3033.7	3010.2	2994.6
35°	2998.7	2960.1	2897.8	2874.4	2855.1
37.5°	2862.9	2827.9	2765.8	2738.6	2719.2
40°	2723.4	2692.1	2630.0	2595.4	2579.7
42.5°	2587.6	2556.3	2494.5	2455.4	2432.4
45°	2440.2	2413.0	2354.6	2312.2	2296.6
47.5°	2296.6	2269.5	2207.2	2164.5	2141.4
50°	2145.1	2125.8	2071.4	2017.1	1997.8
52.5°	1997.8	1970.6	1920.4	1877.5	1850.4
55°	1846.7	1823.3	1776.8	1730.2	1710.9
57.5°	1695.3	1675.9	1625.3	1578.8	1563.1
60°	1543.8	1528.6	1474.2	1431.4	1419.9
62.5°	1396.5	1369.3	1330.6	1291.9	1276.3
65°	1245.4	1221.9	1183.3	1148.3	1129.0
67.5°	1090.2	1070.5	1035.9	1008.8	993.2
70°	946.6	930.9	896.0	868.8	853.6
72.5°	799.3	783.6	764.3	737.2	725.6
75°	651.5	644.1	624.3	601.3	609.2
77.5°	519.8	504.2	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3

TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P903868

CATALOG NUMBER: DFN2DIP-SQ3F0-110D050US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.31	15.40	15.06	16.18	17.11	13.87	14.96	14.62	15.73	16.66
	3H	15.98	16.96	16.75	17.75	18.71	15.49	16.47	16.26	17.26	18.22
	4H	16.58	17.50	17.36	18.30	19.27	16.09	17.01	16.87	17.80	18.78
	6H	16.99	17.84	17.78	18.64	19.63	16.49	17.34	17.28	18.14	19.13
	8H	17.10	17.91	17.90	18.73	19.72	16.60	17.41	17.40	18.23	19.22
	12H	17.15	17.93	17.96	18.74	19.76	16.64	17.42	17.45	18.23	19.25
4H	2H	14.80	15.72	15.58	16.51	17.49	14.44	15.37	15.23	16.16	17.13
	3H	16.68	17.45	17.48	18.28	19.27	16.27	17.04	17.07	17.87	18.86
	4H	17.40	18.10	18.21	18.93	19.95	16.97	17.68	17.79	18.50	19.52
	6H	17.92	18.53	18.75	19.38	20.40	17.49	18.10	18.32	18.95	19.97
	8H	18.07	18.64	18.91	19.49	20.53	17.64	18.20	18.47	19.05	20.09
	12H	18.15	18.67	19.01	19.53	20.58	17.71	18.22	18.56	19.08	20.13
8H	4H	17.61	18.18	18.44	19.02	20.06	17.23	17.80	18.06	18.64	19.68
	6H	18.24	18.71	19.10	19.60	20.64	17.86	18.33	18.72	19.22	20.26
	8H	18.46	18.88	19.33	19.76	20.82	18.07	18.49	18.94	19.37	20.43
	12H	18.60	18.97	19.48	19.84	20.95	18.19	18.56	19.07	19.43	20.54
12H	4H	17.60	18.12	18.46	18.98	20.03	17.23	17.75	18.09	18.61	19.66
	6H	18.27	18.69	19.14	19.57	20.63	17.90	18.32	18.77	19.20	20.26
	8H	18.52	18.89	19.40	19.76	20.87	18.14	18.51	19.02	19.38	20.49