

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903872

Luminaire Tested: DFN2DIP-SQ3F0-110D060US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903872
REPORT IS A COMBINATION OF REPORTS P899911 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D060US830-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15269.1 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903872
CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P903872

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				67
1	102	97	93	90	96	92	88	85	82	79	76	72	70	68	64	62	61	57				57
2	93	85	79	73	87	80	75	70	72	67	63	63	60	57	56	54	51	47				47
3	85	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44	40				40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38	35				35
5	71	59	51	45	67	56	49	43	50	44	39	45	40	36	40	36	33	30				30
6	66	53	45	39	62	51	43	37	45	39	35	41	36	32	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23				23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23	21				21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4623	4623	4623
5°	4627	4555	4587
10°	4586	4491	4524
15°	4516	4414	4425
20°	4422	4308	4324
25°	4328	4182	4208
30°	4212	4064	4060
35°	4101	3926	3904
40°	3965	3787	3756
45°	3829	3647	3604
50°	3681	3500	3428
55°	3525	3330	3266
60°	3349	3128	3080
65°	3156	2919	2861
70°	2910	2664	2624
75°	2571	2358	2404
80°	2161	1967	1987
85°	1522	1304	1300

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3829 cd/sqm



TEST NUMBER: P903872

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	2.5
10°-20°	1068.3	7.0
20°-30°	1570.0	10.3
30°-40°	1823.5	11.9
40°-50°	1821.2	11.9
50°-60°	1588.0	10.4
60°-70°	1173.9	7.7
70°-80°	664.2	4.3
80°-90°	180.4	1.2
90°-100°	110.7	0.7
100°-110°	351.6	2.3
110°-120°	601.8	3.9
120°-130°	791.4	5.2
130°-140°	888.4	5.8
140°-150°	871.1	5.7
150°-160°	730.8	4.8
160°-170°	484.6	3.2
170°-180°	169.4	1.1
0°-30°	3018.1	19.8
0°-40°	4841.6	31.7
0°-60°	8250.9	54.0
0°-90°	10269.3	67.3
90°-120°	1064.1	7.0
90°-150°	3615.0	23.7
90°-180°	5000.0	32.7
0°-180°	15269.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3767	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1873
45°	2440	2413	2355	2312	2297	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	696
85°	159	155	152	140	136	177
90°	2	19	53	50	51	15
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	613	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1582	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1789	1779	170
180°	1789	1789	1789	1789	1789	



TEST NUMBER: P903872

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.3	4034.3	4034.3	4034.3	4034.3
2.5°	4057.6	4038.3	3995.5	4034.3	4026.8
5°	4034.3	4019.0	3976.2	4007.0	3999.7
7.5°	4007.0	3984.0	3941.2	3972.5	3964.7
10°	3964.7	3937.5	3891.0	3921.8	3910.3
12.5°	3906.3	3883.2	3836.7	3856.0	3848.2
15°	3840.4	3817.3	3766.7	3782.3	3763.0
17.5°	3758.9	3735.9	3685.2	3704.6	3685.2
20°	3669.6	3646.5	3592.2	3603.7	3588.5
22.5°	3580.7	3545.7	3495.0	3495.0	3487.2
25°	3475.7	3444.9	3379.0	3386.5	3379.0
27.5°	3359.2	3332.1	3281.8	3270.3	3251.0
30°	3243.2	3211.9	3153.8	3142.3	3126.7
32.5°	3118.9	3095.9	3033.7	3010.2	2994.6
35°	2998.7	2960.1	2897.8	2874.4	2855.1
37.5°	2862.9	2827.9	2765.8	2738.6	2719.2
40°	2723.4	2692.1	2630.0	2595.4	2579.7
42.5°	2587.6	2556.3	2494.5	2455.4	2432.4
45°	2440.2	2413.0	2354.6	2312.2	2296.6
47.5°	2296.6	2269.5	2207.2	2164.5	2141.4
50°	2145.1	2125.8	2071.4	2017.1	1997.8
52.5°	1997.8	1970.6	1920.4	1877.5	1850.4
55°	1846.7	1823.3	1776.8	1730.2	1710.9
57.5°	1695.3	1675.9	1625.3	1578.8	1563.1
60°	1543.8	1528.6	1474.2	1431.4	1419.9
62.5°	1396.5	1369.3	1330.6	1291.9	1276.3
65°	1245.4	1221.9	1183.3	1148.3	1129.0
67.5°	1090.2	1070.5	1035.9	1008.8	993.2
70°	946.6	930.9	896.0	868.8	853.6
72.5°	799.3	783.6	764.3	737.2	725.6
75°	651.5	644.1	624.3	601.3	609.2
77.5°	519.8	504.2	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.1	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.2	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.8



TEST NUMBER: P903872

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.9	540.3	535.9	532.7
115°	603.9	612.6	609.8	608.2	603.9
117.5°	674.6	686.5	678.8	674.6	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.5	817.9	813.7	810.4
125°	878.4	891.8	887.5	882.7	881.1
127.5°	944.7	961.4	955.5	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.3
132.5°	1076.3	1091.4	1092.4	1084.9	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.1
137.5°	1203.0	1216.4	1219.2	1218.0	1211.6
140°	1261.8	1275.3	1282.8	1282.8	1276.9
142.5°	1322.1	1335.6	1339.9	1341.5	1335.6
145°	1379.3	1390.1	1398.7	1400.3	1394.4
147.5°	1430.5	1444.0	1450.5	1453.1	1447.2
150°	1483.4	1492.5	1498.5	1503.3	1498.5
152.5°	1530.2	1539.5	1547.0	1552.9	1547.0
155°	1577.2	1581.5	1586.3	1593.9	1589.0
157.5°	1617.6	1620.9	1623.5	1634.4	1626.8
160°	1653.8	1657.0	1658.6	1667.7	1661.3
162.5°	1687.2	1687.2	1688.8	1699.0	1691.5
165°	1715.7	1714.1	1714.1	1724.9	1717.4
167.5°	1741.6	1736.8	1736.8	1747.6	1740.0
170°	1761.0	1756.7	1755.1	1765.9	1756.7
172.5°	1774.5	1770.2	1768.6	1779.3	1770.2
175°	1785.3	1781.0	1777.7	1788.6	1779.3
177.5°	1791.2	1787.0	1783.7	1792.8	1783.7
180°	1788.6	1788.6	1788.6	1788.6	1788.6



TEST NUMBER: P903872
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.01	15.05	14.81	15.87	16.87	13.57	14.61	14.36	15.43	16.43
	3H	15.68	16.62	16.49	17.44	18.47	15.19	16.13	16.00	16.95	17.98
	4H	16.28	17.16	17.10	17.99	19.03	15.78	16.66	16.60	17.50	18.54
	6H	16.68	17.50	17.52	18.34	19.39	16.18	17.00	17.02	17.84	18.89
	8H	16.79	17.57	17.63	18.43	19.48	16.29	17.06	17.13	17.92	18.98
	12H	16.84	17.58	17.69	18.44	19.52	16.33	17.07	17.18	17.93	19.01
4H	2H	14.49	15.38	15.32	16.21	17.25	14.14	15.02	14.96	15.85	16.90
	3H	16.37	17.11	17.21	17.97	19.03	15.96	16.70	16.80	17.57	18.62
	4H	17.09	17.76	17.94	18.62	19.71	16.66	17.33	17.52	18.20	19.28
	6H	17.61	18.19	18.48	19.08	20.17	17.18	17.76	18.04	18.64	19.73
	8H	17.76	18.30	18.63	19.19	20.29	17.32	17.86	18.19	18.75	19.85
	12H	17.84	18.33	18.73	19.23	20.34	17.39	17.88	18.28	18.78	19.89
8H	4H	17.29	17.84	18.16	18.72	19.82	16.92	17.46	17.79	18.34	19.44
	6H	17.93	18.38	18.83	19.30	20.40	17.54	17.99	18.44	18.92	20.02
	8H	18.14	18.54	19.05	19.46	20.58	17.75	18.15	18.66	19.07	20.19
	12H	18.28	18.63	19.19	19.54	20.71	17.87	18.22	18.78	19.13	20.30
12H	4H	17.29	17.78	18.18	18.68	19.79	16.92	17.41	17.81	18.31	19.42
	6H	17.96	18.35	18.87	19.27	20.39	17.58	17.98	18.49	18.90	20.02
	8H	18.20	18.55	19.11	19.46	20.63	17.82	18.17	18.73	19.08	20.25