

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922581

Luminaire Tested: DFN2DIP-SQ2F0-030D070US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922581
REPORT IS A COMBINATION OF REPORTS P901339 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D070US940-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8828.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 77.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		92	92	92	92		72	72	72		54	54	54		38	38	38
1	93	89	85	82		84	80	77	74		63	61	59		48	46	45		33	33	32
2	85	78	72	67		76	70	65	61		55	52	49		42	40	38		29	28	27
3	77	68	61	56		69	62	56	51		49	45	41		37	34	32		26	24	23
4	71	60	53	47		63	54	48	43		43	39	35		33	30	27		23	21	20
5	65	54	46	40		58	48	42	37		39	34	30		29	26	23		21	19	17
6	60	48	40	35		53	43	37	32		35	30	26		27	23	20		19	17	15
7	55	43	35	30		49	39	32	28		31	26	23		24	21	18		17	15	13
8	51	39	32	26		46	35	29	24		28	24	20		22	19	16		16	14	12
9	47	36	28	23		42	32	26	22		26	21	18		20	17	14		15	12	11
10	44	32	26	21		40	30	23	19		24	19	16		19	15	13		14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2289	2289	2289
5°	2289	2252	2269
10°	2266	2217	2235
15°	2229	2175	2184
20°	2180	2119	2132
25°	2131	2054	2072
30°	2071	1993	1996
35°	2013	1921	1917
40°	1943	1849	1841
45°	1873	1776	1763
50°	1797	1699	1673
55°	1716	1610	1590
60°	1624	1506	1494
65°	1524	1397	1382
70°	1397	1264	1260
75°	1222	1105	1143
80°	1009	902	928
85°	682	570	582

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2000 cd/sqm

TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	1.1
10°-20°	275.6	3.1
20°-30°	405.1	4.6
30°-40°	470.5	5.3
40°-50°	469.9	5.3
50°-60°	409.8	4.6
60°-70°	302.9	3.4
70°-80°	171.4	1.9
80°-90°	48.9	0.6
90°-100°	69.5	0.8
100°-110°	259.0	2.9
110°-120°	686.8	7.8
120°-130°	1139.1	12.9
130°-140°	1209.9	13.7
140°-150°	1124.5	12.7
150°-160°	904.1	10.2
160°-170°	582.6	6.6
170°-180°	200.5	2.3
0°-30°	778.7	8.8
0°-40°	1249.2	14.2
0°-60°	2128.9	24.1
0°-90°	2652.1	30.0
90°-120°	1015.2	11.5
90°-150°	4488.7	50.8
90°-180°	6176.0	70.0
0°-180°	8828.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1041	1041	1041	1041	1041	
5°	1041	1037	1026	1034	1032	99
15°	991	985	972	976	971	279
25°	897	889	872	874	872	413
35°	774	764	748	742	737	483
45°	630	623	608	597	592	486
55°	476	470	458	446	442	426
65°	321	315	305	296	291	318
75°	168	166	161	155	157	179
85°	41	40	39	36	35	46
90°	1	18	30	38	41	8
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	

TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1040.9	1040.9	1040.9	1040.9	1040.9
2.5°	1047.0	1042.0	1030.9	1040.9	1039.0
5°	1040.9	1037.0	1025.9	1033.9	1032.0
7.5°	1033.9	1028.0	1016.9	1025.0	1023.0
10°	1023.0	1015.9	1004.0	1011.9	1009.0
12.5°	1007.9	1001.9	990.0	994.9	992.9
15°	990.9	985.0	971.9	975.9	970.9
17.5°	969.8	963.9	950.8	955.8	950.8
20°	946.8	940.8	926.8	929.8	925.9
22.5°	923.9	914.9	901.8	901.8	899.7
25°	896.8	888.9	871.8	873.8	871.8
27.5°	866.7	859.7	846.8	843.8	838.8
30°	836.8	828.8	813.8	810.7	806.7
32.5°	804.8	798.8	782.7	776.7	772.7
35°	773.7	763.7	747.7	741.6	736.6
37.5°	738.7	729.7	713.6	706.6	701.6
40°	702.7	694.6	678.6	669.7	665.7
42.5°	667.6	659.6	643.6	633.6	627.6
45°	629.6	622.6	607.5	596.6	592.5
47.5°	592.5	585.6	569.5	558.5	552.5
50°	553.5	548.5	534.5	520.5	515.5
52.5°	515.5	508.5	495.5	484.5	477.4
55°	476.5	470.5	458.4	446.5	441.5
57.5°	437.4	432.4	419.4	407.3	403.3
60°	398.3	394.4	380.4	369.3	366.4
62.5°	360.3	353.3	343.3	333.3	329.3
65°	321.4	315.3	305.3	296.3	291.3
67.5°	281.3	276.3	267.2	260.3	256.3
70°	244.2	240.2	231.2	224.2	220.3
72.5°	206.3	202.2	197.2	190.2	187.3
75°	168.1	166.2	161.1	155.2	157.2
77.5°	134.1	130.1	128.0	125.1	122.2
80°	100.1	99.1	97.0	94.1	92.1
82.5°	68.0	68.0	67.1	63.0	63.0
85°	41.0	40.0	39.1	36.0	35.0
87.5°	18.0	16.1	14.0	11.1	10.0
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4

TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6

TEST NUMBER: P922581

CATALOG NUMBER: DFN2DIP-SQ2F0-030D070US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.83	8.53	8.94	9.64	11.17	7.38	8.09	8.49	9.19	10.72
	3H	9.46	10.09	10.57	11.20	12.75	8.97	9.60	10.08	10.71	12.26
	4H	10.02	10.62	11.15	11.74	13.29	9.53	10.13	10.66	11.25	12.80
	6H	10.40	10.95	11.54	12.07	13.63	9.90	10.45	11.04	11.57	13.14
	8H	10.49	11.02	11.63	12.15	13.71	9.99	10.52	11.13	11.65	13.21
	12H	10.53	11.03	11.67	12.15	13.73	10.02	10.52	11.17	11.65	13.23
4H	2H	8.26	8.86	9.39	9.97	11.53	7.90	8.50	9.04	9.62	11.17
	3H	10.09	10.59	11.23	11.73	13.29	9.68	10.18	10.82	11.32	12.89
	4H	10.78	11.24	11.92	12.37	13.95	10.35	10.82	11.50	11.95	13.53
	6H	11.27	11.66	12.42	12.81	14.39	10.83	11.23	11.99	12.38	13.96
	8H	11.40	11.77	12.55	12.92	14.51	10.97	11.33	12.12	12.48	14.07
	12H	11.46	11.79	12.63	12.95	14.55	11.01	11.35	12.18	12.50	14.10
8H	4H	10.95	11.32	12.10	12.46	14.06	10.57	10.94	11.72	12.09	13.68
	6H	11.55	11.86	12.72	13.04	14.63	11.17	11.47	12.34	12.66	14.25
	8H	11.76	12.02	12.93	13.19	14.80	11.36	11.63	12.54	12.80	14.40
	12H	11.87	12.10	13.05	13.26	14.91	11.46	11.69	12.64	12.85	14.50
12H	4H	10.93	11.26	12.09	12.42	14.01	10.56	10.89	11.72	12.05	13.64
	6H	11.57	11.84	12.75	13.01	14.62	11.20	11.47	12.38	12.63	14.24
	8H	11.79	12.03	12.97	13.19	14.83	11.41	11.65	12.59	12.81	14.45