

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922595

Luminaire Tested: DFN2DIP-SQ2F0-040D040US940-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922595  
REPORT IS A COMBINATION OF REPORTS P901306 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-040D040US940-RLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6563.0 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 63.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922595  
CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P922595  
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39	34			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34	29			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15	13			13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3242	3242	3242
5°	3241	3183	3206
10°	3204	3114	3097
15°	3154	3004	2932
20°	3090	2856	2730
25°	3024	2690	2536
30°	2938	2522	2291
35°	2854	2341	2076
40°	2767	2155	1830
45°	2667	1950	1608
50°	2564	1743	1390
55°	2455	1523	1182
60°	2329	1294	969
65°	2183	1062	867
70°	2007	846	778
75°	1784	732	699
80°	1465	594	593
85°	953	369	421

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2667 cd/sqm



TEST NUMBER: P922595

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.2	2.1
10°-20°	379.3	5.8
20°-30°	532.5	8.1
30°-40°	580.5	8.8
40°-50°	533.5	8.1
50°-60°	419.0	6.4
60°-70°	272.7	4.2
70°-80°	140.4	2.1
80°-90°	38.0	0.6
90°-100°	39.7	0.6
100°-110°	148.0	2.3
110°-120°	392.4	6.0
120°-130°	650.9	9.9
130°-140°	691.4	10.5
140°-150°	642.6	9.8
150°-160°	516.6	7.9
160°-170°	332.9	5.1
170°-180°	114.6	1.7
0°-30°	1049.9	16.0
0°-40°	1630.4	24.8
0°-60°	2582.9	39.4
0°-90°	3033.9	46.2
90°-120°	580.1	8.8
90°-150°	2565.0	39.1
90°-180°	3529.0	53.8
0°-180°	6563.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	10	17	22	24	6
95°	56	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	537	134	72	493
125°	708	720	736	742	745	632
135°	876	890	898	907	905	677
145°	1016	1016	1030	1036	1032	636
155°	1119	1112	1122	1127	1120	516
165°	1179	1174	1177	1183	1177	333
175°	1206	1200	1202	1208	1199	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P922595

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.8	10.4	17.4	21.8	23.5
92.5°	21.8	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.3	37.5
97.5°	101.9	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.5	58.3
102.5°	211.6	210.0	51.4	60.9	63.6
105°	264.7	291.0	53.1	62.7	66.2
107.5°	326.6	348.4	54.9	64.5	67.9
110°	385.9	404.1	152.5	65.4	68.8



TEST NUMBER: P922595

CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	441.7	457.3	442.5	67.1	69.7
115°	500.8	515.6	537.4	134.1	71.5
117.5°	552.2	569.6	584.5	459.9	231.7
120°	609.8	622.8	638.5	649.0	531.4
122.5°	658.4	672.4	689.9	695.1	696.0
125°	708.1	719.5	736.0	742.2	744.8
127.5°	753.4	765.6	778.7	787.5	788.3
130°	796.1	810.1	819.6	829.2	828.4
132.5°	839.6	851.0	860.6	868.4	867.6
135°	876.3	890.3	898.0	906.8	905.1
137.5°	914.5	925.0	933.8	942.4	939.9
140°	952.0	959.0	968.6	976.4	972.1
142.5°	983.5	989.5	1000.9	1007.7	1003.4
145°	1016.5	1015.7	1030.4	1036.5	1032.2
147.5°	1045.2	1042.6	1057.4	1061.8	1058.4
150°	1073.1	1067.0	1081.0	1086.2	1081.8
152.5°	1096.6	1089.7	1102.7	1108.0	1101.9
155°	1119.3	1111.5	1121.9	1127.1	1120.2
157.5°	1137.6	1130.6	1138.5	1144.6	1137.6
160°	1153.2	1148.0	1153.2	1158.4	1152.4
162.5°	1167.2	1162.0	1166.4	1172.4	1164.6
165°	1179.4	1174.2	1176.8	1182.9	1176.8
167.5°	1189.0	1183.7	1186.4	1192.5	1184.6
170°	1196.9	1191.6	1193.3	1199.4	1191.6
172.5°	1202.0	1196.9	1198.6	1204.7	1196.9
175°	1206.3	1200.2	1202.0	1208.1	1199.4
177.5°	1208.1	1202.0	1202.9	1209.1	1201.2
180°	1203.8	1203.8	1203.8	1203.8	1203.8



TEST NUMBER: P922595  
 CATALOG NUMBER: DFN2DIP-SQ2F0-040D040US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.75	11.56	11.75	12.56	13.88	6.71	7.51	7.71	8.52	9.84
	3H	12.41	13.13	13.42	14.14	15.49	7.88	8.60	8.89	9.61	10.96
	4H	13.00	13.68	14.02	14.70	16.05	8.32	9.00	9.34	10.01	11.37
	6H	13.41	14.03	14.44	15.05	16.42	8.62	9.25	9.65	10.27	11.63
	8H	13.53	14.12	14.56	15.15	16.52	8.70	9.30	9.74	10.33	11.70
	12H	13.58	14.14	14.62	15.17	16.56	8.74	9.30	9.78	10.33	11.72
4H	2H	10.76	11.44	11.79	12.46	13.81	7.30	7.97	8.32	8.99	10.34
	3H	12.57	13.13	13.60	14.17	15.54	8.62	9.19	9.66	10.23	11.60
	4H	13.24	13.76	14.28	14.79	16.19	9.15	9.67	10.19	10.70	12.10
	6H	13.74	14.18	14.79	15.24	16.63	9.55	9.99	10.60	11.05	12.44
	8H	13.90	14.32	14.95	15.37	16.77	9.67	10.08	10.72	11.13	12.54
	12H	13.99	14.36	15.05	15.42	16.83	9.72	10.10	10.79	11.16	12.57
8H	4H	13.21	13.62	14.26	14.67	16.07	9.42	9.83	10.47	10.88	12.29
	6H	13.75	14.09	14.82	15.18	16.58	9.91	10.25	10.99	11.35	12.75
	8H	13.95	14.25	15.03	15.33	16.75	10.09	10.39	11.17	11.47	12.89
	12H	14.08	14.34	15.16	15.41	16.87	10.19	10.46	11.28	11.53	12.99
12H	4H	13.16	13.53	14.22	14.59	16.00	9.42	9.79	10.49	10.86	12.27
	6H	13.72	14.02	14.80	15.10	16.52	9.96	10.26	11.04	11.33	12.75
	8H	13.93	14.19	15.01	15.26	16.72	10.15	10.41	11.23	11.49	12.95