

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922626

Luminaire Tested: DFN2DIP-SQ2F0-050D060US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922626  
REPORT IS A COMBINATION OF REPORTS P899812 AND P896659  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-050D060US940-RLLFLL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8524.8 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 90.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922626  
CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P922626

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38	38	38	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33	33	33	33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33	28	28	28	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28	25	25	25	25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22	22	22	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22	19	19	19	19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17	17	17	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16	16	16	16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14	14	14	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13	13	13	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4052	4052	4052
5°	4051	3979	4007
10°	4004	3892	3871
15°	3942	3755	3665
20°	3862	3569	3413
25°	3780	3363	3170
30°	3673	3152	2864
35°	3567	2927	2595
40°	3459	2694	2288
45°	3334	2437	2009
50°	3205	2179	1738
55°	3069	1904	1478
60°	2911	1617	1211
65°	2729	1328	1084
70°	2508	1058	972
75°	2230	915	873
80°	1831	744	740
85°	1193	462	527

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3334 cd/sqm



TEST NUMBER: P922626

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.7	2.0
10°-20°	474.1	5.6
20°-30°	665.6	7.8
30°-40°	725.6	8.5
40°-50°	666.9	7.8
50°-60°	523.7	6.1
60°-70°	340.9	4.0
70°-80°	175.5	2.1
80°-90°	49.6	0.6
90°-100°	104.7	1.2
100°-110°	332.7	3.9
110°-120°	569.3	6.7
120°-130°	748.8	8.8
130°-140°	840.5	9.9
140°-150°	824.2	9.7
150°-160°	691.4	8.1
160°-170°	458.5	5.4
170°-180°	160.3	1.9
0°-30°	1312.4	15.4
0°-40°	2038.0	23.9
0°-60°	3228.6	37.9
0°-90°	3794.6	44.5
90°-120°	1006.7	11.8
90°-150°	3420.1	40.1
90°-180°	4730.0	55.5
0°-180°	8524.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	2	18	50	47	48	8
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P922626

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P922626

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1



TEST NUMBER: P922626  
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.36	12.14	12.37	13.16	14.51	7.32	8.10	8.33	9.12	10.47
	3H	13.01	13.71	14.03	14.74	16.11	8.48	9.19	9.50	10.21	11.58
	4H	13.60	14.27	14.64	15.30	16.68	8.92	9.59	9.95	10.61	11.99
	6H	14.01	14.62	15.05	15.65	17.04	9.22	9.84	10.26	10.87	12.26
	8H	14.12	14.71	15.17	15.75	17.14	9.30	9.89	10.35	10.93	12.32
	12H	14.18	14.73	15.23	15.77	17.18	9.34	9.89	10.39	10.93	12.34
4H	2H	11.36	12.03	12.40	13.06	14.44	7.90	8.56	8.94	9.59	10.97
	3H	13.17	13.72	14.21	14.78	16.17	9.22	9.78	10.27	10.83	12.22
	4H	13.84	14.35	14.90	15.40	16.81	9.75	10.26	10.81	11.31	12.72
	6H	14.34	14.77	15.40	15.84	17.25	10.15	10.58	11.21	11.65	13.06
	8H	14.50	14.91	15.56	15.97	17.39	10.27	10.67	11.33	11.74	13.16
	12H	14.58	14.95	15.66	16.03	17.45	10.32	10.69	11.40	11.76	13.19
8H	4H	13.80	14.21	14.87	15.27	16.69	10.02	10.42	11.08	11.49	12.91
	6H	14.35	14.68	15.43	15.78	17.21	10.51	10.85	11.60	11.95	13.37
	8H	14.55	14.84	15.64	15.93	17.37	10.69	10.98	11.78	12.07	13.51
	12H	14.67	14.93	15.77	16.01	17.49	10.79	11.05	11.88	12.13	13.61
12H	4H	13.75	14.12	14.83	15.19	16.62	10.02	10.38	11.10	11.46	12.89
	6H	14.32	14.61	15.41	15.70	17.14	10.55	10.85	11.65	11.94	13.38
	8H	14.52	14.78	15.62	15.86	17.35	10.75	11.00	11.84	12.09	13.57