

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922627

Luminaire Tested: DFN2DIP-SQ2F0-050D060US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922627
REPORT IS A COMBINATION OF REPORTS P901332 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D060US940-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9086.5 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 90.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4052	4052	4052
5°	4051	3979	4007
10°	4004	3892	3871
15°	3942	3755	3665
20°	3862	3569	3413
25°	3780	3363	3170
30°	3673	3152	2864
35°	3567	2927	2595
40°	3459	2694	2288
45°	3334	2437	2009
50°	3205	2179	1738
55°	3069	1904	1478
60°	2911	1617	1211
65°	2729	1328	1084
70°	2508	1058	972
75°	2230	915	873
80°	1831	744	740
85°	1193	462	527

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3334 cd/sqm

TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.9
10°-20°	474.1	5.2
20°-30°	665.6	7.3
30°-40°	725.6	8.0
40°-50°	666.9	7.3
50°-60°	523.7	5.8
60°-70°	340.9	3.8
70°-80°	175.5	1.9
80°-90°	48.0	0.5
90°-100°	59.5	0.7
100°-110°	222.0	2.4
110°-120°	588.7	6.5
120°-130°	976.3	10.7
130°-140°	1037.1	11.4
140°-150°	963.9	10.6
150°-160°	774.9	8.5
160°-170°	499.3	5.5
170°-180°	171.9	1.9
0°-30°	1312.4	14.4
0°-40°	2038.0	22.4
0°-60°	3228.6	35.5
0°-90°	3793.0	41.7
90°-120°	870.2	9.6
90°-150°	3847.4	42.3
90°-180°	5294.0	58.3
0°-180°	9086.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	1	16	26	33	35	8
95°	85	42	51	58	56	101
105°	397	436	80	94	99	424
115°	751	774	806	201	107	740
125°	1062	1079	1104	1113	1117	947
135°	1314	1335	1347	1360	1358	1015
145°	1525	1523	1546	1555	1548	954
155°	1679	1667	1683	1691	1680	774
165°	1769	1761	1765	1774	1765	500
175°	1810	1800	1803	1812	1799	172
180°	1806	1806	1806	1806	1806	

TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.8	45.7	66.5	70.6	71.9
100°	231.3	52.3	74.5	84.9	87.5
102.5°	317.4	315.0	77.1	91.4	95.4
105°	397.2	436.4	79.7	94.0	99.3
107.5°	490.0	522.5	82.4	96.7	101.9
110°	578.9	606.2	228.7	98.1	103.2

TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.5	685.9	663.7	100.5	104.6
115°	751.3	773.5	806.2	201.3	107.2
117.5°	828.3	854.4	876.7	689.8	347.5
120°	914.6	934.2	957.8	973.4	797.0
122.5°	987.7	1008.6	1034.8	1042.6	1044.0
125°	1062.2	1079.2	1104.0	1113.2	1117.0
127.5°	1130.2	1148.4	1168.1	1181.2	1182.4
130°	1194.2	1215.1	1229.4	1243.8	1242.6
132.5°	1259.5	1276.6	1290.8	1302.6	1301.4
135°	1314.5	1335.4	1347.0	1360.2	1357.5
137.5°	1371.8	1387.5	1400.7	1413.7	1409.9
140°	1428.0	1438.6	1452.9	1464.6	1458.1
142.5°	1475.2	1484.3	1501.3	1511.6	1505.1
145°	1524.8	1523.4	1545.6	1554.8	1548.3
147.5°	1567.8	1563.9	1586.1	1592.6	1587.5
150°	1609.7	1600.5	1621.5	1629.2	1622.7
152.5°	1644.9	1634.5	1654.0	1662.0	1652.8
155°	1678.9	1667.2	1682.9	1690.7	1680.2
157.5°	1706.4	1695.9	1707.7	1716.9	1706.4
160°	1729.9	1722.0	1729.9	1737.7	1728.6
162.5°	1750.7	1742.9	1749.4	1758.6	1746.9
165°	1769.1	1761.3	1765.1	1774.3	1765.1
167.5°	1783.4	1775.6	1779.6	1788.8	1776.9
170°	1795.3	1787.3	1790.0	1799.1	1787.3
172.5°	1803.0	1795.3	1797.9	1807.1	1795.3
175°	1809.5	1800.4	1803.0	1812.1	1799.1
177.5°	1812.1	1803.0	1804.4	1813.6	1801.8
180°	1805.6	1805.6	1805.6	1805.6	1805.6

TEST NUMBER: P922627

CATALOG NUMBER: DFN2DIP-SQ2F0-050D060US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.07	11.84	12.10	12.87	14.26	7.03	7.80	8.06	8.83	10.22
	3H	12.72	13.41	13.76	14.45	15.86	8.20	8.88	9.24	9.93	11.33
	4H	13.32	13.97	14.37	15.01	16.42	8.63	9.28	9.68	10.33	11.74
	6H	13.72	14.32	14.78	15.37	16.79	8.93	9.53	10.00	10.58	12.01
	8H	13.83	14.40	14.90	15.47	16.89	9.01	9.58	10.08	10.65	12.07
	12H	13.89	14.43	14.96	15.48	16.93	9.05	9.59	10.12	10.64	12.09
4H	2H	11.08	11.73	12.14	12.77	14.18	7.61	8.26	8.67	9.30	10.72
	3H	12.88	13.42	13.94	14.49	15.92	8.93	9.47	10.00	10.55	11.97
	4H	13.55	14.05	14.62	15.11	16.56	9.46	9.96	10.53	11.02	12.47
	6H	14.04	14.47	15.13	15.56	17.00	9.86	10.28	10.94	11.37	12.81
	8H	14.21	14.60	15.29	15.68	17.14	9.97	10.37	11.06	11.45	12.91
	12H	14.29	14.65	15.39	15.74	17.20	10.03	10.38	11.13	11.48	12.94
8H	4H	13.51	13.91	14.59	14.99	16.44	9.73	10.12	10.81	11.20	12.66
	6H	14.05	14.38	15.16	15.50	16.96	10.22	10.54	11.32	11.67	13.12
	8H	14.26	14.54	15.37	15.65	17.12	10.39	10.68	11.50	11.78	13.26
	12H	14.38	14.63	15.49	15.73	17.24	10.49	10.75	11.61	11.85	13.36
12H	4H	13.46	13.82	14.56	14.91	16.37	9.72	10.08	10.82	11.18	12.64
	6H	14.03	14.31	15.14	15.42	16.89	10.26	10.55	11.37	11.65	13.13
	8H	14.23	14.48	15.34	15.58	17.09	10.45	10.70	11.57	11.80	13.32