

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922637

Luminaire Tested: DFN2DIP-SQ2F0-060D030US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922637
REPORT IS A COMBINATION OF REPORTS P901297 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-060D030US940-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7945.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4578	4578	4578
5°	4577	4504	4538
10°	4532	4433	4470
15°	4457	4350	4368
20°	4359	4239	4263
25°	4262	4108	4143
30°	4142	3985	3993
35°	4027	3842	3834
40°	3886	3697	3682
45°	3747	3551	3526
50°	3593	3398	3346
55°	3432	3221	3179
60°	3249	3012	2988
65°	3048	2794	2763
70°	2794	2529	2519
75°	2444	2210	2285
80°	2019	1804	1856
85°	1362	1139	1166

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3747 cd/sqm

TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	2.5
10°-20°	551.3	6.9
20°-30°	810.2	10.2
30°-40°	941.0	11.8
40°-50°	939.8	11.8
50°-60°	819.5	10.3
60°-70°	605.8	7.6
70°-80°	342.7	4.3
80°-90°	92.1	1.2
90°-100°	29.8	0.4
100°-110°	111.0	1.4
110°-120°	294.3	3.7
120°-130°	488.2	6.1
130°-140°	518.5	6.5
140°-150°	481.9	6.1
150°-160°	387.5	4.9
160°-170°	249.7	3.1
170°-180°	85.9	1.1
0°-30°	1557.4	19.6
0°-40°	2498.4	31.4
0°-60°	4257.8	53.6
0°-90°	5298.4	66.7
90°-120°	435.1	5.5
90°-150°	1923.7	24.2
90°-180°	2647.0	33.3
0°-180°	7945.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2074	2052	2068	2064	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	825
35°	1548	1528	1495	1483	1473	966
45°	1259	1245	1215	1193	1185	972
55°	953	941	917	893	883	852
65°	643	631	611	592	583	635
75°	336	332	322	310	314	359
85°	82	80	78	72	70	91
90°	1	8	13	16	18	7
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2081.8	2081.8	2081.8	2081.8	2081.8
2.5°	2093.9	2083.9	2061.8	2081.8	2078.0
5°	2081.8	2073.9	2051.8	2067.8	2064.0
7.5°	2067.8	2055.9	2033.8	2050.0	2045.9
10°	2045.9	2031.9	2007.9	2023.8	2017.9
12.5°	2015.8	2003.9	1979.9	1989.9	1985.8
15°	1981.7	1969.9	1943.8	1951.9	1941.9
17.5°	1939.7	1927.9	1901.8	1911.6	1901.8
20°	1893.6	1881.8	1853.7	1859.7	1851.8
22.5°	1847.8	1829.7	1803.6	1803.6	1799.6
25°	1793.6	1777.7	1743.7	1747.5	1743.7
27.5°	1733.5	1719.5	1693.5	1687.7	1677.7
30°	1673.7	1657.4	1627.5	1621.6	1613.5
32.5°	1609.4	1597.6	1565.5	1553.4	1545.3
35°	1547.5	1527.5	1495.4	1483.3	1473.3
37.5°	1477.4	1459.3	1427.3	1413.2	1403.2
40°	1405.3	1389.2	1357.2	1339.3	1331.2
42.5°	1335.2	1319.1	1287.3	1267.1	1255.2
45°	1259.3	1245.2	1215.0	1193.2	1185.1
47.5°	1185.1	1171.1	1139.1	1117.0	1105.0
50°	1107.0	1097.0	1069.0	1040.9	1030.9
52.5°	1030.9	1016.9	991.0	968.9	954.9
55°	953.0	940.8	916.9	892.9	882.9
57.5°	874.9	864.9	838.7	814.8	806.6
60°	796.7	788.8	760.8	738.7	732.7
62.5°	720.6	706.6	686.6	666.6	658.6
65°	642.7	630.6	610.6	592.5	582.6
67.5°	562.6	552.4	534.6	520.6	512.5
70°	488.5	480.5	462.4	448.4	440.5
72.5°	412.4	404.4	394.4	380.4	374.4
75°	336.2	332.4	322.2	310.3	314.3
77.5°	268.2	260.2	256.1	250.2	244.2
80°	200.3	198.1	194.1	188.2	184.1
82.5°	136.2	136.2	134.2	126.2	126.2
85°	81.9	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6

TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P922637

CATALOG NUMBER: DFN2DIP-SQ2F0-060D030US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.86	14.89	14.65	15.71	16.72	13.41	14.44	14.21	15.27	16.28
	3H	15.51	16.44	16.32	17.27	18.31	15.02	15.95	15.83	16.78	17.82
	4H	16.09	16.97	16.92	17.81	18.86	15.60	16.48	16.43	17.31	18.37
	6H	16.49	17.29	17.33	18.14	19.21	15.99	16.79	16.83	17.64	18.71
	8H	16.59	17.36	17.44	18.22	19.29	16.09	16.86	16.94	17.72	18.79
	12H	16.63	17.37	17.49	18.23	19.32	16.13	16.86	16.98	17.72	18.81
4H	2H	14.33	15.20	15.16	16.04	17.09	13.97	14.85	14.80	15.69	16.74
	3H	16.18	16.92	17.03	17.79	18.86	15.78	16.51	16.62	17.38	18.45
	4H	16.89	17.56	17.75	18.43	19.52	16.47	17.13	17.32	18.00	19.10
	6H	17.40	17.97	18.27	18.87	19.96	16.96	17.54	17.84	18.44	19.53
	8H	17.54	18.08	18.42	18.97	20.08	17.10	17.64	17.98	18.53	19.64
	12H	17.61	18.10	18.51	19.01	20.12	17.17	17.65	18.06	18.56	19.68
8H	4H	17.09	17.63	17.97	18.52	19.63	16.71	17.25	17.59	18.14	19.25
	6H	17.70	18.15	18.61	19.08	20.19	17.32	17.77	18.22	18.70	19.81
	8H	17.91	18.31	18.83	19.23	20.36	17.52	17.92	18.43	18.84	19.97
	12H	18.04	18.39	18.96	19.30	20.48	17.63	17.98	18.55	18.89	20.07
12H	4H	17.08	17.57	17.98	18.48	19.59	16.71	17.20	17.61	18.11	19.22
	6H	17.73	18.13	18.64	19.05	20.18	17.36	17.75	18.27	18.68	19.80
	8H	17.96	18.31	18.88	19.23	20.41	17.58	17.93	18.50	18.85	20.03

END OF REPORT