

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906375

Luminaire Tested: DFN2DIP-SQ3F0-040D120US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906375
REPORT IS A COMBINATION OF REPORTS P901526 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-040D120US835-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15280.0 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 126.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26			19
2	84	77	71	66	74	68	64	60	52	49	47	38	36	34	24	23	22			16
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19			14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17			12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15			11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13			10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12			9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10			8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9			7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1894	1894	1894
5°	1896	1863	1876
10°	1876	1825	1814
15°	1849	1764	1719
20°	1814	1679	1603
25°	1777	1585	1490
30°	1729	1488	1348
35°	1682	1385	1223
40°	1634	1278	1080
45°	1578	1159	951
50°	1520	1039	824
55°	1459	911	703
60°	1389	778	578
65°	1308	642	519
70°	1210	516	469
75°	1086	452	425
80°	908	375	367
85°	616	244	272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2774 cd/sqm

TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	1.0
10°-20°	425.3	2.8
20°-30°	597.2	3.9
30°-40°	650.9	4.3
40°-50°	598.3	3.9
50°-60°	469.9	3.1
60°-70°	305.8	2.0
70°-80°	157.4	1.0
80°-90°	47.3	0.3
90°-100°	133.5	0.9
100°-110°	497.8	3.3
110°-120°	1320.3	8.6
120°-130°	2189.8	14.3
130°-140°	2326.1	15.2
140°-150°	2161.8	14.1
150°-160°	1738.1	11.4
160°-170°	1119.9	7.3
170°-180°	385.5	2.5
0°-30°	1177.4	7.7
0°-40°	1828.4	12.0
0°-60°	2896.5	19.0
0°-90°	3407.1	22.3
90°-120°	1951.7	12.8
90°-150°	8629.4	56.5
90°-180°	11873.0	77.7
0°-180°	15280.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	3	35	58	73	79	14
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	

TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4



TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9

TEST NUMBER: P906375

CATALOG NUMBER: DFN2DIP-SQ3F0-040D120US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.91	6.55	7.07	7.70	9.32	1.87	2.51	3.04	3.66	5.28
	3H	7.57	8.14	8.74	9.30	10.94	3.04	3.61	4.21	4.77	6.41
	4H	8.16	8.71	9.35	9.87	11.51	3.47	4.02	4.66	5.18	6.82
	6H	8.57	9.08	9.76	10.23	11.88	3.78	4.28	4.97	5.44	7.09
	8H	8.69	9.17	9.88	10.34	11.99	3.86	4.34	5.05	5.51	7.16
	12H	8.74	9.20	9.94	10.37	12.03	3.89	4.35	5.09	5.52	7.18
4H	2H	5.90	6.45	7.09	7.61	9.25	2.44	2.99	3.63	4.14	5.78
	3H	7.71	8.16	8.90	9.35	11.00	3.76	4.22	4.96	5.40	7.05
	4H	8.39	8.81	9.58	9.98	11.65	4.30	4.72	5.49	5.89	7.56
	6H	8.89	9.25	10.09	10.44	12.10	4.70	5.06	5.90	6.25	7.91
	8H	9.06	9.39	10.26	10.58	12.25	4.82	5.16	6.02	6.34	8.02
	12H	9.14	9.45	10.35	10.64	12.32	4.87	5.18	6.09	6.37	8.05
8H	4H	8.34	8.68	9.54	9.86	11.54	4.56	4.90	5.76	6.08	7.76
	6H	8.89	9.17	10.11	10.40	12.07	5.07	5.34	6.28	6.57	8.24
	8H	9.11	9.35	10.33	10.55	12.24	5.25	5.49	6.47	6.69	8.39
	12H	9.23	9.45	10.46	10.65	12.37	5.36	5.57	6.58	6.77	8.49
12H	4H	8.28	8.59	9.50	9.78	11.46	4.56	4.86	5.77	6.06	7.74
	6H	8.87	9.11	10.09	10.31	12.01	5.11	5.35	6.33	6.56	8.25
	8H	9.08	9.29	10.30	10.49	12.21	5.31	5.52	6.53	6.72	8.44

END OF REPORT