

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925306

Luminaire Tested: DFN2DIP-SQ2F0-030D060US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925306
REPORT IS A COMBINATION OF REPORTS P899808 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D060US950-RLFL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7498.4 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 68.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2601	2601	2601
5°	2601	2554	2572
10°	2570	2498	2485
15°	2531	2410	2352
20°	2479	2291	2191
25°	2427	2159	2035
30°	2358	2024	1838
35°	2290	1878	1666
40°	2220	1729	1469
45°	2140	1565	1290
50°	2057	1399	1115
55°	1969	1222	949
60°	1868	1039	777
65°	1752	852	695
70°	1610	679	624
75°	1431	588	560
80°	1176	477	475
85°	765	296	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2520 cd/sqm

TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	1.5
10°-20°	304.3	4.1
20°-30°	427.3	5.7
30°-40°	465.7	6.2
40°-50°	428.1	5.7
50°-60°	336.2	4.5
60°-70°	218.8	2.9
70°-80°	112.6	1.5
80°-90°	33.9	0.5
90°-100°	112.0	1.5
100°-110°	355.9	4.7
110°-120°	609.1	8.1
120°-130°	801.1	10.7
130°-140°	899.2	12.0
140°-150°	881.7	11.8
150°-160°	739.6	9.9
160°-170°	490.5	6.5
170°-180°	171.4	2.3
0°-30°	842.5	11.2
0°-40°	1308.2	17.4
0°-60°	2072.5	27.6
0°-90°	2437.8	32.5
90°-120°	1077.0	14.4
90°-150°	3659.0	48.8
90°-180°	5061.0	67.5
0°-180°	7498.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1183	1183	1183	1183	1183	
5°	1183	1178	1164	1173	1170	112
15°	1125	1113	1077	1057	1046	317
25°	1021	987	916	872	856	470
35°	880	825	731	664	640	551
45°	719	648	535	459	434	556
55°	547	464	348	284	263	489
65°	369	283	186	150	147	366
75°	197	122	86	78	77	208
85°	46	24	20	20	20	53
90°	2	20	54	50	52	7
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	

TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1182.9	1182.9	1182.9	1182.9	1182.9
2.5°	1188.2	1182.9	1171.0	1181.8	1179.7
5°	1182.9	1177.5	1163.6	1173.2	1170.0
7.5°	1173.2	1166.8	1151.9	1156.1	1150.7
10°	1160.4	1152.9	1131.5	1128.2	1121.9
12.5°	1144.3	1134.7	1105.8	1099.4	1087.6
15°	1125.1	1113.2	1076.9	1056.6	1045.9
17.5°	1102.5	1085.5	1040.4	1017.0	999.8
20°	1076.9	1055.4	1001.9	975.3	951.6
22.5°	1049.1	1024.4	962.3	926.0	909.9
25°	1021.3	986.9	916.3	872.4	856.3
27.5°	988.1	951.6	873.5	823.2	798.5
30°	952.8	912.0	826.4	771.9	742.9
32.5°	918.4	869.2	781.5	717.2	690.4
35°	880.0	825.3	731.1	663.7	640.1
37.5°	842.5	783.5	684.0	610.1	583.5
40°	802.9	738.7	634.8	558.8	531.0
42.5°	762.2	693.7	585.6	506.3	479.6
45°	719.4	647.6	535.3	459.2	433.5
47.5°	678.7	602.7	487.1	411.0	387.5
50°	633.7	557.7	440.0	366.0	343.6
52.5°	589.8	509.5	395.1	324.4	304.0
55°	546.9	463.5	347.8	283.7	263.4
57.5°	503.1	417.5	306.2	246.2	229.1
60°	458.1	372.5	262.3	207.7	190.6
62.5°	414.3	328.7	224.8	173.4	164.9
65°	369.3	282.6	186.2	149.9	146.6
67.5°	326.6	239.7	149.9	131.7	128.4
70°	281.5	198.1	124.1	113.4	109.1
72.5°	238.7	159.4	103.8	95.3	93.1
75°	196.9	122.0	85.7	78.1	77.1
77.5°	155.2	86.6	67.4	63.2	61.0
80°	116.7	62.1	51.3	47.1	47.1
82.5°	81.3	41.8	35.3	33.2	33.2
85°	46.0	23.5	20.3	20.3	20.3
87.5°	17.2	8.5	8.5	7.5	7.5
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4

TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3

TEST NUMBER: P925306

CATALOG NUMBER: DFN2DIP-SQ2F0-030D060US950-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.45	9.16	9.55	10.25	11.75	4.41	5.12	5.51	6.21	7.71
	3H	10.10	10.73	11.21	11.83	13.35	5.57	6.20	6.68	7.30	8.82
	4H	10.69	11.29	11.81	12.39	13.92	6.00	6.60	7.12	7.70	9.23
	6H	11.09	11.64	12.22	12.74	14.28	6.30	6.85	7.43	7.96	9.50
	8H	11.20	11.73	12.33	12.85	14.38	6.38	6.90	7.51	8.02	9.56
	12H	11.25	11.75	12.39	12.86	14.42	6.41	6.91	7.55	8.02	9.58
4H	2H	8.45	9.05	9.57	10.15	11.68	4.98	5.58	6.11	6.68	8.21
	3H	10.24	10.74	11.38	11.87	13.41	6.30	6.80	7.43	7.93	9.46
	4H	10.92	11.37	12.05	12.49	14.05	6.83	7.28	7.96	8.40	9.96
	6H	11.41	11.80	12.55	12.94	14.49	7.22	7.61	8.36	8.75	10.30
	8H	11.57	11.93	12.71	13.07	14.63	7.33	7.70	8.47	8.83	10.40
	12H	11.65	11.98	12.80	13.12	14.69	7.38	7.71	8.54	8.86	10.43
8H	4H	10.87	11.24	12.01	12.37	13.93	7.09	7.45	8.23	8.58	10.15
	6H	11.41	11.71	12.57	12.89	14.45	7.57	7.88	8.74	9.05	10.61
	8H	11.61	11.88	12.78	13.03	14.61	7.75	8.01	8.92	9.17	10.75
	12H	11.73	11.96	12.90	13.11	14.73	7.85	8.08	9.02	9.23	10.85
12H	4H	10.82	11.15	11.97	12.29	13.86	7.08	7.41	8.24	8.56	10.13
	6H	11.38	11.65	12.55	12.80	14.38	7.62	7.88	8.78	9.04	10.62
	8H	11.58	11.82	12.75	12.97	14.58	7.81	8.04	8.98	9.19	10.81