

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925334

Luminaire Tested: DFN2DIP-SQ2F0-040D070US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925334
REPORT IS A COMBINATION OF REPORTS P899822 AND P896659
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-040D070US950-RLLFLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9153.7 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	27	25	24
5	67	56	48	42	60	51	44	39	42	37	33	33	29	27	25	23	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	24	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17
8	53	41	33	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3468	3468	3468
5°	3468	3405	3430
10°	3427	3331	3314
15°	3374	3214	3137
20°	3306	3055	2921
25°	3235	2878	2713
30°	3143	2698	2451
35°	3053	2505	2221
40°	2961	2306	1958
45°	2854	2086	1720
50°	2743	1865	1487
55°	2626	1629	1265
60°	2491	1384	1036
65°	2336	1136	927
70°	2147	905	832
75°	1908	783	747
80°	1567	636	634
85°	1020	395	451

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2943 cd/sqm

TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	1.6
10°-20°	405.8	4.4
20°-30°	569.7	6.2
30°-40°	621.0	6.8
40°-50°	570.8	6.2
50°-60°	448.2	4.9
60°-70°	291.8	3.2
70°-80°	150.2	1.6
80°-90°	44.4	0.5
90°-100°	130.7	1.4
100°-110°	415.3	4.5
110°-120°	710.6	7.8
120°-130°	934.6	10.2
130°-140°	1049.0	11.5
140°-150°	1028.7	11.2
150°-160°	862.9	9.4
160°-170°	572.3	6.3
170°-180°	200.0	2.2
0°-30°	1123.3	12.3
0°-40°	1744.3	19.1
0°-60°	2763.3	30.2
0°-90°	3249.6	35.5
90°-120°	1256.6	13.7
90°-150°	4268.9	46.6
90°-180°	5904.0	64.5
0°-180°	9153.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	23	62	59	60	9
95°	93	111	114	114	111	103
105°	383	388	392	395	395	405
115°	713	723	720	718	713	705
125°	1037	1053	1048	1042	1040	927
135°	1342	1361	1365	1363	1358	1037
145°	1629	1642	1652	1654	1647	1018
155°	1862	1868	1873	1882	1876	857
165°	2026	2024	2024	2037	2028	572
175°	2108	2103	2099	2112	2101	200
180°	2112	2112	2112	2112	2112	

TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	1.9	22.9	62.4	58.6	60.5
92.5°	39.5	53.5	55.4	57.3	57.3
95°	92.9	110.8	114.0	114.0	110.8
97.5°	154.7	171.2	178.3	178.3	178.3
100°	226.0	240.7	245.8	245.8	243.8
102.5°	301.2	312.0	319.0	320.9	319.0
105°	383.3	388.4	392.2	395.4	395.4
107.5°	464.8	472.4	472.4	473.8	464.8
110°	543.8	554.0	554.0	554.0	548.8

TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.1	639.9	638.0	632.9	629.1
115°	713.1	723.3	720.2	718.3	713.1
117.5°	796.5	810.5	801.6	796.5	791.4
120°	880.5	894.6	880.5	880.5	874.8
122.5°	957.0	974.8	965.9	960.8	957.0
125°	1037.2	1053.1	1048.1	1042.3	1040.4
127.5°	1115.5	1135.3	1128.3	1120.7	1115.5
130°	1188.8	1211.7	1208.5	1204.7	1197.7
132.5°	1270.9	1288.8	1290.0	1281.1	1276.0
135°	1341.6	1361.3	1365.2	1363.2	1358.1
137.5°	1420.5	1436.4	1439.6	1438.3	1430.7
140°	1490.0	1505.9	1514.8	1514.8	1507.8
142.5°	1561.2	1577.2	1582.2	1584.1	1577.2
145°	1628.8	1641.5	1651.7	1653.6	1646.6
147.5°	1689.2	1705.2	1712.8	1716.0	1709.0
150°	1751.6	1762.4	1769.5	1775.2	1769.5
152.5°	1807.0	1817.8	1826.7	1833.8	1826.7
155°	1862.4	1867.5	1873.3	1882.1	1876.4
157.5°	1910.2	1914.0	1917.2	1929.9	1921.0
160°	1952.8	1956.7	1958.6	1969.3	1961.7
162.5°	1992.3	1992.3	1994.2	2006.3	1997.4
165°	2026.0	2024.1	2024.1	2036.9	2027.9
167.5°	2056.6	2050.9	2050.9	2063.6	2054.7
170°	2079.5	2074.5	2072.6	2085.3	2074.5
172.5°	2095.5	2090.3	2088.4	2101.2	2090.3
175°	2108.1	2103.1	2099.3	2112.0	2101.2
177.5°	2115.2	2110.1	2106.2	2117.1	2106.2
180°	2112.0	2112.0	2112.0	2112.0	2112.0

TEST NUMBER: P925334

CATALOG NUMBER: DFN2DIP-SQ2F0-040D070US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.82	10.55	10.90	11.62	13.09	5.78	6.51	6.86	7.58	9.05
	3H	11.47	12.12	12.56	13.20	14.69	6.95	7.59	8.03	8.68	10.16
	4H	12.06	12.68	13.16	13.76	15.25	7.38	7.99	8.48	9.08	10.57
	6H	12.46	13.03	13.57	14.12	15.62	7.68	8.24	8.78	9.33	10.83
	8H	12.58	13.12	13.69	14.22	15.72	7.76	8.29	8.87	9.40	10.89
	12H	12.63	13.14	13.74	14.24	15.76	7.79	8.30	8.90	9.40	10.91
4H	2H	9.82	10.44	10.93	11.52	13.01	6.36	6.97	7.46	8.05	9.54
	3H	11.62	12.13	12.73	13.24	14.75	7.67	8.19	8.79	9.30	10.80
	4H	12.29	12.76	13.41	13.86	15.39	8.20	8.67	9.32	9.77	11.30
	6H	12.78	13.19	13.91	14.31	15.83	8.60	9.00	9.72	10.12	11.64
	8H	12.95	13.32	14.07	14.44	15.97	8.71	9.09	9.84	10.20	11.74
	12H	13.03	13.36	14.16	14.49	16.03	8.76	9.10	9.90	10.23	11.77
8H	4H	12.25	12.62	13.37	13.74	15.27	8.46	8.84	9.59	9.95	11.49
	6H	12.79	13.10	13.93	14.26	15.79	8.95	9.26	10.10	10.42	11.95
	8H	12.99	13.26	14.14	14.40	15.95	9.13	9.40	10.28	10.54	12.09
	12H	13.11	13.35	14.26	14.49	16.07	9.23	9.47	10.38	10.60	12.19
12H	4H	12.20	12.53	13.33	13.66	15.20	8.46	8.80	9.60	9.93	11.47
	6H	12.76	13.03	13.91	14.17	15.72	9.00	9.27	10.15	10.41	11.96
	8H	12.96	13.20	14.12	14.34	15.92	9.19	9.42	10.34	10.56	12.14

END OF REPORT