

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906458

Luminaire Tested: DFN2DIP-SQ3F0-070D060US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906458
REPORT IS A COMBINATION OF REPORTS P899904 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D060US835-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11260.0 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906458
CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P906458
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53	53	53	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	60	53	52	51	46	46	46	46
2	91	83	77	72	84	78	72	68	67	63	59	56	54	51	47	45	43	39	39	39	39
3	83	74	67	61	77	69	62	57	59	54	51	50	47	44	42	40	38	34	34	34	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29	29	29	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	26	26	26	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	31	28	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19	19	19	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	19	23	20	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3315	3315	3315
5°	3318	3260	3282
10°	3283	3194	3174
15°	3236	3086	3008
20°	3174	2939	2805
25°	3111	2774	2608
30°	3026	2605	2360
35°	2943	2423	2141
40°	2859	2236	1891
45°	2761	2028	1664
50°	2660	1818	1442
55°	2553	1595	1230
60°	2431	1361	1011
65°	2289	1124	909
70°	2117	903	821
75°	1901	791	744
80°	1589	657	642
85°	1077	428	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2761 cd/sqm



TEST NUMBER: P906458

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	2.4
10°-20°	744.3	6.6
20°-30°	1045.0	9.3
30°-40°	1139.2	10.1
40°-50°	1047.0	9.3
50°-60°	822.3	7.3
60°-70°	535.2	4.8
70°-80°	275.5	2.4
80°-90°	75.7	0.7
90°-100°	117.4	1.0
100°-110°	373.1	3.3
110°-120°	638.5	5.7
120°-130°	839.7	7.5
130°-140°	942.5	8.4
140°-150°	924.2	8.2
150°-160°	775.3	6.9
160°-170°	514.2	4.6
170°-180°	179.7	1.6
0°-30°	2060.5	18.3
0°-40°	3199.7	28.4
0°-60°	5068.9	45.0
0°-90°	5955.4	52.9
90°-120°	1129.0	10.0
90°-150°	3835.4	34.1
90°-180°	5305.0	47.1
0°-180°	11260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	2	21	56	53	54	11
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	



TEST NUMBER: P906458

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1



TEST NUMBER: P906458

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6



TEST NUMBER: P906458
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.54	12.40	12.48	13.35	14.58	7.50	8.36	8.44	9.31	10.54
	3H	13.22	13.98	14.17	14.94	16.20	8.69	9.45	9.64	10.41	11.67
	4H	13.82	14.55	14.79	15.51	16.77	9.13	9.86	10.10	10.82	12.08
	6H	14.24	14.91	15.22	15.88	17.15	9.45	10.11	10.43	11.08	12.36
	8H	14.37	15.00	15.35	15.99	17.26	9.54	10.17	10.52	11.16	12.43
	12H	14.43	15.03	15.41	16.01	17.31	9.58	10.18	10.57	11.16	12.46
4H	2H	11.56	12.28	12.53	13.25	14.51	8.10	8.82	9.07	9.78	11.05
	3H	13.39	13.99	14.37	14.98	16.26	9.44	10.04	10.42	11.04	12.32
	4H	14.08	14.62	15.06	15.61	16.91	9.99	10.53	10.98	11.52	12.82
	6H	14.59	15.06	15.59	16.07	17.37	10.40	10.87	11.40	11.88	13.18
	8H	14.76	15.20	15.76	16.21	17.52	10.53	10.97	11.53	11.97	13.28
	12H	14.85	15.25	15.87	16.27	17.59	10.59	10.98	11.61	12.01	13.32
8H	4H	14.04	14.48	15.05	15.49	16.80	10.27	10.71	11.27	11.71	13.02
	6H	14.61	14.97	15.63	16.02	17.33	10.78	11.14	11.80	12.19	13.50
	8H	14.82	15.14	15.85	16.17	17.50	10.96	11.28	12.00	12.32	13.65
	12H	14.96	15.24	15.99	16.26	17.64	11.08	11.36	12.11	12.39	13.76
12H	4H	14.00	14.39	15.02	15.41	16.73	10.27	10.67	11.29	11.69	13.01
	6H	14.58	14.90	15.61	15.93	17.27	10.82	11.14	11.86	12.18	13.51
	8H	14.80	15.08	15.84	16.11	17.48	11.03	11.31	12.07	12.34	13.71