

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925361

Luminaire Tested: DFN2DIP-SQ2F0-050D080US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925361
REPORT IS A COMBINATION OF REPORTS P901355 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-050D080US950-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12278.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 109.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925361
CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P925361

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38				38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4081	4081	4081
5°	4081	4015	4046
10°	4040	3953	3985
15°	3974	3878	3894
20°	3887	3779	3801
25°	3800	3662	3694
30°	3692	3553	3560
35°	3590	3425	3418
40°	3465	3296	3282
45°	3340	3166	3144
50°	3203	3029	2983
55°	3060	2871	2835
60°	2897	2686	2664
65°	2718	2491	2464
70°	2491	2254	2246
75°	2179	1970	2038
80°	1800	1609	1655
85°	1216	1015	1040

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3340 cd/sqm



TEST NUMBER: P925361

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	1.4
10°-20°	491.5	4.0
20°-30°	722.3	5.9
30°-40°	838.9	6.8
40°-50°	837.9	6.8
50°-60°	730.6	6.0
60°-70°	540.1	4.4
70°-80°	305.6	2.5
80°-90°	85.2	0.7
90°-100°	84.9	0.7
100°-110°	316.6	2.6
110°-120°	839.7	6.8
120°-130°	1392.7	11.3
130°-140°	1479.4	12.0
140°-150°	1374.9	11.2
150°-160°	1105.4	9.0
160°-170°	712.3	5.8
170°-180°	245.2	2.0
0°-30°	1388.5	11.3
0°-40°	2227.5	18.1
0°-60°	3796.0	30.9
0°-90°	4726.8	38.5
90°-120°	1241.3	10.1
90°-150°	5488.3	44.7
90°-180°	7551.0	61.5
0°-180°	12278.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	2	22	37	47	50	11
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P925361

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P925361

CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P925361
 CATALOG NUMBER: DFN2DIP-SQ2F0-050D080US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.88	11.64	11.93	12.70	14.12	10.43	11.20	11.48	12.25	13.68
	3H	12.51	13.20	13.57	14.26	15.71	12.02	12.71	13.08	13.77	15.22
	4H	13.08	13.73	14.15	14.80	16.25	12.59	13.24	13.66	14.30	15.76
	6H	13.46	14.06	14.54	15.13	16.59	12.96	13.56	14.04	14.63	16.09
	8H	13.55	14.13	14.64	15.21	16.67	13.05	13.62	14.14	14.71	16.17
	12H	13.59	14.14	14.68	15.21	16.70	13.08	13.63	14.17	14.71	16.19
4H	2H	11.31	11.97	12.39	13.03	14.48	10.96	11.61	12.04	12.68	14.13
	3H	13.15	13.69	14.23	14.79	16.25	12.74	13.28	13.83	14.38	15.84
	4H	13.84	14.34	14.93	15.43	16.91	13.42	13.92	14.51	15.00	16.49
	6H	14.34	14.76	15.43	15.87	17.35	13.90	14.33	15.00	15.44	16.92
	8H	14.47	14.87	15.57	15.97	17.47	14.04	14.44	15.14	15.53	17.03
	12H	14.53	14.89	15.65	16.01	17.51	14.08	14.45	15.20	15.56	17.06
8H	4H	14.02	14.42	15.12	15.52	17.01	13.64	14.04	14.74	15.14	16.64
	6H	14.62	14.96	15.75	16.10	17.59	14.24	14.57	15.36	15.71	17.20
	8H	14.83	15.12	15.96	16.24	17.75	14.44	14.73	15.57	15.85	17.36
	12H	14.95	15.20	16.08	16.32	17.87	14.54	14.79	15.67	15.91	17.46
12H	4H	14.00	14.36	15.12	15.47	16.97	13.63	13.99	14.75	15.10	16.60
	6H	14.65	14.94	15.78	16.06	17.57	14.28	14.57	15.40	15.69	17.20
	8H	14.87	15.13	16.00	16.24	17.79	14.49	14.74	15.62	15.86	17.41