

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925371

Luminaire Tested: DFN2DIP-SQ2F0-060D040US950-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925371  
REPORT IS A COMBINATION OF REPORTS P901310 AND P898215  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ2F0-060D040US950-RLLONL  
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8643.2 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 84.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925371  
CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P925371

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49	49	49	49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42	42	42	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27	27	27	27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24	24	24	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5202	5202	5202
5°	5201	5108	5145
10°	5141	4997	4970
15°	5061	4820	4705
20°	4958	4583	4381
25°	4853	4318	4070
30°	4715	4047	3677
35°	4579	3757	3331
40°	4441	3459	2937
45°	4280	3129	2580
50°	4114	2797	2231
55°	3940	2444	1897
60°	3737	2077	1554
65°	3504	1704	1391
70°	3220	1357	1248
75°	2864	1174	1122
80°	2351	954	950
85°	1530	592	675

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4280 cd/sqm



TEST NUMBER: P925371

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.7	2.6
10°-20°	608.7	7.0
20°-30°	854.5	9.9
30°-40°	931.5	10.8
40°-50°	856.2	9.9
50°-60°	672.4	7.8
60°-70°	437.7	5.1
70°-80°	225.3	2.6
80°-90°	59.8	0.7
90°-100°	42.5	0.5
100°-110°	158.3	1.8
110°-120°	419.9	4.9
120°-130°	696.4	8.1
130°-140°	739.7	8.6
140°-150°	687.5	8.0
150°-160°	552.7	6.4
160°-170°	356.1	4.1
170°-180°	122.6	1.4
0°-30°	1684.9	19.5
0°-40°	2616.4	30.3
0°-60°	4144.9	48.0
0°-90°	4867.7	56.3
90°-120°	620.6	7.2
90°-150°	2744.1	31.7
90°-180°	3776.0	43.7
0°-180°	8643.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	1	11	19	23	25	8
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	



TEST NUMBER: P925371

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6



TEST NUMBER: P925371

CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9



TEST NUMBER: P925371  
 CATALOG NUMBER: DFN2DIP-SQ2F0-060D040US950-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.22	14.24	15.14	16.32	9.29	10.18	10.20	11.10	12.28
	3H	14.99	15.78	15.91	16.72	17.92	10.47	11.26	11.39	12.19	13.40
	4H	15.59	16.34	16.53	17.28	18.49	10.91	11.65	11.84	12.59	13.81
	6H	16.00	16.69	16.95	17.63	18.86	11.22	11.90	12.16	12.85	14.07
	8H	16.12	16.77	17.07	17.73	18.96	11.30	11.95	12.25	12.91	14.14
	12H	16.18	16.80	17.13	17.75	19.00	11.34	11.96	12.29	12.91	14.16
4H	2H	13.35	14.10	14.29	15.04	16.25	9.88	10.63	10.83	11.57	12.78
	3H	15.16	15.78	16.11	16.75	17.98	11.22	11.84	12.17	12.81	14.04
	4H	15.84	16.41	16.80	17.37	18.62	11.75	12.32	12.71	13.28	14.53
	6H	16.34	16.83	17.31	17.81	19.07	12.16	12.64	13.13	13.63	14.88
	8H	16.51	16.96	17.48	17.94	19.21	12.28	12.73	13.25	13.71	14.98
	12H	16.59	17.00	17.59	18.00	19.27	12.33	12.74	13.33	13.74	15.01
8H	4H	15.81	16.26	16.78	17.24	18.51	12.03	12.48	13.00	13.46	14.73
	6H	16.36	16.73	17.36	17.75	19.02	12.52	12.90	13.52	13.92	15.18
	8H	16.56	16.89	17.57	17.90	19.18	12.70	13.03	13.71	14.04	15.32
	12H	16.69	16.98	17.70	17.98	19.31	12.80	13.10	13.82	14.10	15.43
12H	4H	15.76	16.17	16.76	17.17	18.44	12.03	12.44	13.02	13.43	14.71
	6H	16.33	16.66	17.34	17.67	18.95	12.57	12.90	13.57	13.91	15.19
	8H	16.54	16.83	17.55	17.83	19.16	12.76	13.05	13.77	14.06	15.39