

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906521

Luminaire Tested: DFN2DIP-SQ3F0-090D040US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906521
REPORT IS A COMBINATION OF REPORTS P901391 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-090D040US835-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12870.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 118.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94		83	83	83		74
1	102	98	94	90	96	92	89	86	83	80	77		74	72	70		65
2	93	85	79	74	88	81	75	70	72	68	64		65	61	58		57
3	85	75	67	61	80	71	64	59	64	59	54		57	53	49		51
4	78	67	58	52	73	63	56	50	57	51	46		51	46	42		46
5	71	59	51	45	67	57	49	43	51	45	40		46	41	37		41
6	66	53	45	39	62	51	43	38	46	40	35		42	36	32		37
7	61	48	40	34	58	46	39	33	42	36	31		38	33	29		34
8	57	44	36	31	54	42	35	30	38	32	28		35	29	26		31
9	53	40	33	27	50	39	31	27	35	29	25		32	27	23		29
10	50	37	30	25	47	36	29	24	32	27	22		30	25	21		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4012	4012	4012
5°	4016	3954	3982
10°	3981	3898	3927
15°	3920	3831	3841
20°	3838	3739	3754
25°	3757	3630	3653
30°	3656	3528	3525
35°	3560	3408	3389
40°	3442	3287	3260
45°	3324	3166	3128
50°	3195	3038	2976
55°	3060	2890	2835
60°	2907	2716	2674
65°	2739	2534	2483
70°	2526	2313	2278
75°	2232	2047	2087
80°	1876	1708	1725
85°	1320	1132	1129

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3324 cd/sqm

TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	2.6
10°-20°	927.4	7.2
20°-30°	1362.9	10.6
30°-40°	1582.9	12.3
40°-50°	1580.9	12.3
50°-60°	1378.5	10.7
60°-70°	1019.0	7.9
70°-80°	576.6	4.5
80°-90°	154.5	1.2
90°-100°	44.5	0.3
100°-110°	165.9	1.3
110°-120°	440.1	3.4
120°-130°	729.9	5.7
130°-140°	775.4	6.0
140°-150°	720.6	5.6
150°-160°	579.4	4.5
160°-170°	373.3	2.9
170°-180°	128.5	1.0
0°-30°	2619.9	20.4
0°-40°	4202.8	32.7
0°-60°	7162.3	55.7
0°-90°	8912.4	69.2
90°-120°	650.5	5.1
90°-150°	2876.4	22.4
90°-180°	3958.0	30.8
0°-180°	12870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	1	12	20	24	26	12
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P906521

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.68	14.74	14.45	15.54	16.50	13.23	14.30	14.00	15.09	16.06
	3H	15.35	16.31	16.13	17.11	18.11	14.86	15.82	15.64	16.62	17.62
	4H	15.94	16.85	16.74	17.66	18.67	15.45	16.35	16.25	17.16	18.17
	6H	16.35	17.18	17.16	18.00	19.03	15.85	16.68	16.66	17.50	18.53
	8H	16.46	17.25	17.28	18.09	19.11	15.96	16.75	16.78	17.59	18.61
	12H	16.51	17.27	17.34	18.10	19.15	16.00	16.76	16.83	17.59	18.64
4H	2H	14.16	15.06	14.97	15.88	16.88	13.80	14.71	14.61	15.52	16.53
	3H	16.04	16.79	16.86	17.64	18.66	15.63	16.38	16.45	17.23	18.26
	4H	16.76	17.44	17.59	18.29	19.34	16.33	17.02	17.16	17.86	18.92
	6H	17.28	17.87	18.13	18.74	19.80	16.85	17.44	17.70	18.31	19.37
	8H	17.43	17.99	18.28	18.85	19.92	16.99	17.55	17.85	18.41	19.48
	12H	17.51	18.01	18.38	18.90	19.97	17.06	17.56	17.93	18.45	19.52
8H	4H	16.96	17.52	17.82	18.39	19.45	16.59	17.14	17.44	18.01	19.08
	6H	17.60	18.06	18.48	18.97	20.03	17.21	17.68	18.10	18.58	19.65
	8H	17.82	18.23	18.71	19.13	20.21	17.42	17.83	18.32	18.73	19.82
	12H	17.96	18.32	18.85	19.21	20.35	17.54	17.91	18.44	18.80	19.94
12H	4H	16.96	17.46	17.83	18.34	19.42	16.59	17.09	17.46	17.98	19.05
	6H	17.63	18.04	18.52	18.94	20.02	17.26	17.67	18.15	18.57	19.65
	8H	17.88	18.24	18.77	19.13	20.27	17.50	17.86	18.39	18.75	19.89