

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906525

Luminaire Tested: DFN2DIP-SQ3F0-090D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906525
REPORT IS A COMBINATION OF REPORTS P901409 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-090D050US835-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13860.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 124.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69
1	101	97	93	89	95	91	87	84	80	78	75		70	68	67		61
2	92	84	78	73	86	79	74	69	70	66	62		62	59	56		54
3	84	74	67	61	79	70	63	58	62	57	52		55	51	47		48
4	77	66	58	51	72	62	55	49	55	49	45		49	44	40		43
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		39
6	65	53	44	38	61	50	42	37	45	38	34		40	35	31		35
7	60	48	40	34	57	45	38	33	41	34	30		36	31	27		32
8	56	43	35	30	53	41	34	29	37	31	27		33	28	24		29
9	52	40	32	27	49	38	31	26	34	28	24		30	26	22		27
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4012	4012	4012
5°	4016	3954	3982
10°	3981	3898	3927
15°	3920	3831	3841
20°	3838	3739	3754
25°	3757	3630	3653
30°	3656	3528	3525
35°	3560	3408	3389
40°	3442	3287	3260
45°	3324	3166	3128
50°	3195	3038	2976
55°	3060	2890	2835
60°	2907	2716	2674
65°	2739	2534	2483
70°	2526	2313	2278
75°	2232	2047	2087
80°	1876	1708	1725
85°	1320	1132	1129

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3324 cd/sqm

TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	2.4
10°-20°	927.4	6.7
20°-30°	1362.9	9.8
30°-40°	1582.9	11.4
40°-50°	1580.9	11.4
50°-60°	1378.5	9.9
60°-70°	1019.0	7.4
70°-80°	576.6	4.2
80°-90°	155.1	1.1
90°-100°	55.7	0.4
100°-110°	207.4	1.5
110°-120°	550.1	4.0
120°-130°	912.4	6.6
130°-140°	969.2	7.0
140°-150°	900.8	6.5
150°-160°	724.2	5.2
160°-170°	466.6	3.4
170°-180°	160.6	1.2
0°-30°	2619.9	18.9
0°-40°	4202.8	30.3
0°-60°	7162.3	51.7
0°-90°	8913.0	64.3
90°-120°	813.2	5.9
90°-150°	3595.6	25.9
90°-180°	4947.0	35.7
0°-180°	13860.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	1	15	24	31	33	13
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P906525

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.29	14.30	14.11	15.14	16.19	12.85	13.85	13.67	14.70	15.75
	3H	14.96	15.86	15.79	16.72	17.80	14.47	15.37	15.30	16.23	17.31
	4H	15.55	16.40	16.40	17.26	18.35	15.05	15.91	15.91	16.77	17.86
	6H	15.95	16.74	16.82	17.61	18.71	15.45	16.24	16.32	17.11	18.21
	8H	16.06	16.81	16.93	17.70	18.80	15.56	16.31	16.43	17.20	18.30
	12H	16.11	16.83	16.99	17.71	18.84	15.60	16.32	16.48	17.20	18.33
4H	2H	13.76	14.62	14.62	15.48	16.57	13.41	14.26	14.27	15.13	16.22
	3H	15.64	16.35	16.51	17.25	18.35	15.23	15.94	16.10	16.84	17.94
	4H	16.35	17.00	17.24	17.90	19.03	15.93	16.58	16.81	17.47	18.60
	6H	16.87	17.44	17.77	18.35	19.48	16.44	17.00	17.34	17.92	19.05
	8H	17.02	17.55	17.92	18.46	19.61	16.59	17.11	17.49	18.02	19.17
	12H	17.10	17.58	18.02	18.50	19.66	16.65	17.13	17.57	18.06	19.21
8H	4H	16.56	17.08	17.46	17.99	19.14	16.18	16.71	17.08	17.62	18.76
	6H	17.19	17.62	18.12	18.58	19.72	16.81	17.24	17.73	18.19	19.34
	8H	17.41	17.79	18.35	18.74	19.90	17.02	17.40	17.95	18.35	19.51
	12H	17.54	17.88	18.48	18.82	20.03	17.13	17.47	18.07	18.41	19.62
12H	4H	16.55	17.02	17.47	17.95	19.11	16.18	16.65	17.10	17.58	18.74
	6H	17.22	17.60	18.16	18.55	19.71	16.85	17.23	17.78	18.18	19.34
	8H	17.46	17.80	18.40	18.74	19.95	17.08	17.42	18.02	18.36	19.57