

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925429

Luminaire Tested: DFN2DIP-SQ2F0-080D070US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925429
REPORT IS A COMBINATION OF REPORTS P901349 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-080D070US950-FLLONL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14166.9 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		72	72	72		59
1	99	94	90	87	91	87	84	81	75	72	70		63	61	60		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	50		46
3	82	72	65	59	76	67	61	56	58	53	49		49	45	42		41
4	75	64	56	50	69	60	53	47	51	46	42		44	40	36		37
5	69	57	49	43	63	53	46	41	46	40	36		39	35	31		33
6	63	51	43	37	59	48	41	35	41	36	31		35	31	28		30
7	59	46	38	33	54	43	36	31	38	32	28		32	28	24		27
8	54	42	34	29	50	39	32	27	34	29	25		30	25	22		25
9	51	38	31	26	47	36	29	25	31	26	22		27	23	20		23
10	47	35	28	23	44	33	26	22	29	24	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6530	6530	6530
5°	6529	6425	6473
10°	6465	6324	6376
15°	6359	6206	6230
20°	6219	6047	6081
25°	6079	5860	5910
30°	5908	5685	5695
35°	5744	5481	5469
40°	5544	5274	5252
45°	5344	5066	5030
50°	5126	4847	4774
55°	4895	4595	4535
60°	4635	4297	4263
65°	4349	3986	3942
70°	3985	3607	3593
75°	3487	3153	3260
80°	2880	2573	2647
85°	1946	1625	1664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5344 cd/sqm

TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.0
10°-20°	786.4	5.6
20°-30°	1155.7	8.2
30°-40°	1342.3	9.5
40°-50°	1340.6	9.5
50°-60°	1169.0	8.3
60°-70°	864.1	6.1
70°-80°	488.9	3.5
80°-90°	133.0	0.9
90°-100°	74.3	0.5
100°-110°	277.0	2.0
110°-120°	734.8	5.2
120°-130°	1218.6	8.6
130°-140°	1294.5	9.1
140°-150°	1203.1	8.5
150°-160°	967.2	6.8
160°-170°	623.3	4.4
170°-180°	214.5	1.5
0°-30°	2221.6	15.7
0°-40°	3563.9	25.2
0°-60°	6073.6	42.9
0°-90°	7559.6	53.4
90°-120°	1086.1	7.7
90°-150°	4802.2	33.9
90°-180°	6607.0	46.6
0°-180°	14166.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	2	20	32	41	44	13
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	

TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8

TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7

TEST NUMBER: P925429

CATALOG NUMBER: DFN2DIP-SQ2F0-080D070US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.98	14.87	14.91	15.82	17.04	13.54	14.43	14.46	15.38	16.60
	3H	15.63	16.43	16.56	17.38	18.63	15.14	15.94	16.07	16.89	18.14
	4H	16.20	16.96	17.15	17.92	19.17	15.71	16.46	16.66	17.42	18.68
	6H	16.59	17.29	17.55	18.25	19.52	16.09	16.79	17.05	17.75	19.02
	8H	16.69	17.35	17.66	18.33	19.60	16.18	16.85	17.16	17.83	19.10
	12H	16.73	17.36	17.71	18.34	19.63	16.22	16.85	17.20	17.83	19.12
4H	2H	14.44	15.19	15.40	16.15	17.41	14.08	14.84	15.04	15.80	17.05
	3H	16.28	16.91	17.25	17.90	19.17	15.87	16.51	16.84	17.49	18.76
	4H	16.98	17.56	17.96	18.54	19.84	16.56	17.14	17.54	18.12	19.41
	6H	17.48	17.98	18.47	18.98	20.28	17.05	17.55	18.04	18.55	19.84
	8H	17.62	18.09	18.61	19.09	20.39	17.18	17.65	18.18	18.65	19.95
	12H	17.69	18.11	18.70	19.12	20.43	17.24	17.66	18.25	18.67	19.99
8H	4H	17.17	17.63	18.16	18.63	19.94	16.79	17.26	17.78	18.26	19.56
	6H	17.78	18.16	18.79	19.20	20.51	17.39	17.78	18.41	18.82	20.12
	8H	17.99	18.32	19.01	19.35	20.68	17.59	17.93	18.62	18.96	20.28
	12H	18.11	18.40	19.13	19.43	20.79	17.70	17.99	18.72	19.02	20.38
12H	4H	17.15	17.57	18.16	18.59	19.90	16.78	17.20	17.80	18.22	19.53
	6H	17.80	18.14	18.83	19.17	20.49	17.43	17.77	18.45	18.80	20.12
	8H	18.03	18.33	19.06	19.35	20.72	17.65	17.95	18.68	18.97	20.34