

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906559

Luminaire Tested: DFN2DIP-SQ3F0-100D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906559
REPORT IS A COMBINATION OF REPORTS P901394 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D040US835-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12460.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 128.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73
1	103	98	95	91	97	93	90	87	83	81	78	74	72	70	65	64	63
2	94	87	81	76	88	82	77	72	74	69	66	66	63	60	58	56	54
3	86	77	70	64	81	73	66	61	66	60	56	59	55	51	52	49	47
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41
5	73	62	53	48	69	59	51	46	53	47	42	48	43	39	43	39	36
6	68	56	47	42	64	53	46	40	48	42	38	43	39	35	39	35	32
7	63	50	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24
10	51	39	32	27	48	37	31	26	34	29	25	31	27	23	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4736	4736	4736
5°	4740	4657	4689
10°	4690	4563	4535
15°	4623	4409	4297
20°	4534	4198	4007
25°	4444	3962	3726
30°	4323	3721	3371
35°	4205	3462	3058
40°	4084	3194	2701
45°	3944	2897	2377
50°	3799	2597	2060
55°	3648	2278	1756
60°	3472	1944	1444
65°	3270	1606	1298
70°	3024	1289	1173
75°	2716	1130	1063
80°	2269	938	917
85°	1539	611	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3944 cd/sqm

TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	3.1
10°-20°	1063.3	8.5
20°-30°	1492.9	12.0
30°-40°	1627.4	13.1
40°-50°	1495.7	12.0
50°-60°	1174.7	9.4
60°-70°	764.6	6.1
70°-80°	393.6	3.2
80°-90°	102.9	0.8
90°-100°	44.5	0.4
100°-110°	165.9	1.3
110°-120°	440.1	3.5
120°-130°	729.9	5.9
130°-140°	775.4	6.2
140°-150°	720.6	5.8
150°-160°	579.4	4.6
160°-170°	373.3	3.0
170°-180°	128.5	1.0
0°-30°	2943.6	23.6
0°-40°	4571.0	36.7
0°-60°	7241.3	58.1
0°-90°	8502.4	68.2
90°-120°	650.5	5.2
90°-150°	2876.4	23.1
90°-180°	3958.0	31.8
0°-180°	12460.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	1	12	20	24	26	12
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P906559

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.07	15.08	14.86	15.88	16.87	10.03	11.04	10.82	11.84	12.83
	3H	15.76	16.66	16.56	17.47	18.49	11.23	12.13	12.03	12.94	13.96
	4H	16.37	17.22	17.19	18.04	19.07	11.68	12.53	12.50	13.35	14.38
	6H	16.80	17.58	17.63	18.41	19.45	12.00	12.79	12.84	13.62	14.66
	8H	16.93	17.67	17.77	18.52	19.56	12.10	12.84	12.94	13.69	14.73
	12H	16.99	17.70	17.84	18.54	19.61	12.14	12.85	12.99	13.70	14.76
4H	2H	14.11	14.96	14.93	15.78	16.81	10.65	11.49	11.47	12.32	13.35
	3H	15.95	16.65	16.78	17.51	18.55	12.00	12.71	12.84	13.57	14.61
	4H	16.64	17.28	17.49	18.14	19.21	12.55	13.19	13.40	14.05	15.12
	6H	17.16	17.71	18.03	18.60	19.67	12.98	13.53	13.84	14.41	15.48
	8H	17.34	17.85	18.21	18.73	19.82	13.10	13.62	13.97	14.49	15.58
	12H	17.44	17.90	18.33	18.80	19.89	13.17	13.64	14.06	14.53	15.62
8H	4H	16.62	17.14	17.49	18.01	19.10	12.84	13.36	13.71	14.23	15.32
	6H	17.19	17.61	18.09	18.53	19.62	13.36	13.78	14.26	14.70	15.79
	8H	17.40	17.78	18.31	18.69	19.80	13.55	13.92	14.45	14.84	15.94
	12H	17.55	17.88	18.45	18.78	19.94	13.67	14.00	14.58	14.90	16.06
12H	4H	16.58	17.04	17.47	17.94	19.03	12.86	13.32	13.74	14.21	15.31
	6H	17.16	17.54	18.07	18.45	19.56	13.41	13.79	14.31	14.70	15.80
	8H	17.39	17.72	18.30	18.62	19.78	13.62	13.95	14.53	14.86	16.01