

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903665

Luminaire Tested: DFN2DIP-SQ3F0-050D080US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903665
REPORT IS A COMBINATION OF REPORTS P901455 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D080US830-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12130.5 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 102.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903665
CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P903665

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38				38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2101	2101	2101
5°	2103	2070	2085
10°	2085	2041	2056
15°	2053	2006	2011
20°	2010	1958	1966
25°	1967	1901	1913
30°	1914	1848	1846
35°	1864	1785	1775
40°	1802	1721	1707
45°	1741	1658	1638
50°	1673	1591	1558
55°	1602	1514	1484
60°	1522	1422	1400
65°	1434	1327	1300
70°	1323	1211	1193
75°	1169	1072	1093
80°	982	894	903
85°	691	592	591

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1745 cd/sqm



TEST NUMBER: P903665

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.6	1.4
10°-20°	485.6	4.0
20°-30°	713.7	5.9
30°-40°	828.9	6.8
40°-50°	827.8	6.8
50°-60°	721.8	6.0
60°-70°	533.6	4.4
70°-80°	301.9	2.5
80°-90°	84.2	0.7
90°-100°	83.9	0.7
100°-110°	312.8	2.6
110°-120°	829.6	6.8
120°-130°	1376.0	11.3
130°-140°	1461.6	12.0
140°-150°	1358.4	11.2
150°-160°	1092.1	9.0
160°-170°	703.7	5.8
170°-180°	242.2	2.0
0°-30°	1371.9	11.3
0°-40°	2200.7	18.1
0°-60°	3750.4	30.9
0°-90°	4670.1	38.5
90°-120°	1226.4	10.1
90°-150°	5422.4	44.7
90°-180°	7460.0	61.5
0°-180°	12130.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1834	1834	1834	1834	1834	
5°	1834	1827	1807	1821	1818	174
15°	1746	1735	1712	1719	1710	492
25°	1580	1566	1536	1539	1536	727
35°	1363	1346	1317	1307	1298	851
45°	1109	1097	1070	1051	1044	856
55°	839	829	808	786	778	750
65°	566	555	538	522	513	560
75°	296	293	284	273	277	316
85°	72	70	69	63	62	81
90°	2	22	37	46	50	11
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P903665

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.7	1833.7	1833.7	1833.7	1833.7
2.5°	1844.4	1835.6	1816.2	1833.7	1830.4
5°	1833.7	1826.8	1807.3	1821.4	1818.1
7.5°	1821.4	1810.9	1791.5	1805.7	1802.1
10°	1802.1	1789.8	1768.7	1782.6	1777.4
12.5°	1775.6	1765.1	1744.0	1752.8	1749.2
15°	1745.6	1735.1	1712.1	1719.3	1710.4
17.5°	1708.5	1698.1	1675.1	1683.9	1675.1
20°	1668.0	1657.6	1632.9	1638.0	1631.2
22.5°	1627.6	1611.7	1588.7	1588.7	1585.1
25°	1579.9	1565.8	1535.9	1539.3	1535.9
27.5°	1526.9	1514.6	1491.8	1486.5	1477.7
30°	1474.1	1460.0	1433.6	1428.3	1421.3
32.5°	1417.7	1407.2	1378.9	1368.3	1361.2
35°	1363.0	1345.5	1317.2	1306.6	1297.8
37.5°	1301.3	1285.4	1257.2	1244.8	1236.0
40°	1237.9	1223.7	1195.4	1179.7	1172.6
42.5°	1176.2	1162.0	1133.9	1116.1	1105.6
45°	1109.2	1096.8	1070.3	1051.0	1043.9
47.5°	1043.9	1031.5	1003.3	983.8	973.4
50°	975.1	966.3	941.6	916.9	908.0
52.5°	908.0	895.7	872.9	853.5	841.1
55°	839.4	828.8	807.6	786.5	777.7
57.5°	770.5	761.8	738.8	717.7	710.5
60°	701.7	694.8	670.1	650.6	645.5
62.5°	634.8	622.5	604.8	587.2	580.1
65°	566.1	555.4	537.8	522.0	513.1
67.5°	495.6	486.6	470.9	458.5	451.4
70°	430.3	423.2	407.3	394.9	388.0
72.5°	363.4	356.2	347.4	335.1	329.8
75°	296.1	292.8	283.8	273.3	276.9
77.5°	236.3	229.1	225.6	220.4	215.2
80°	176.4	174.6	171.0	165.8	162.2
82.5°	119.9	119.9	118.2	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.8	28.3	24.7	19.4	17.6
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P903665

CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8



TEST NUMBER: P903665
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D080US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.65	9.42	9.70	10.47	11.90	8.21	8.97	9.26	10.03	11.45
	3H	10.30	10.99	11.36	12.05	13.50	9.81	10.50	10.87	11.56	13.00
	4H	10.88	11.53	11.95	12.60	14.05	10.39	11.04	11.46	12.10	13.55
	6H	11.27	11.87	12.35	12.94	14.40	10.77	11.37	11.85	12.44	13.90
	8H	11.37	11.94	12.46	13.03	14.49	10.87	11.44	11.95	12.53	13.98
	12H	11.41	11.96	12.50	13.04	14.52	10.91	11.45	12.00	12.53	14.01
4H	2H	9.10	9.75	10.17	10.81	12.27	8.74	9.39	9.82	10.46	11.91
	3H	10.95	11.49	12.03	12.58	14.05	10.54	11.08	11.63	12.18	13.64
	4H	11.65	12.15	12.75	13.24	14.72	11.23	11.73	12.32	12.81	14.30
	6H	12.16	12.59	13.26	13.69	15.17	11.73	12.16	12.83	13.26	14.74
	8H	12.31	12.70	13.40	13.80	15.30	11.87	12.27	12.97	13.37	14.86
	12H	12.37	12.73	13.49	13.84	15.35	11.92	12.28	13.04	13.40	14.90
8H	4H	11.84	12.24	12.94	13.34	14.83	11.46	11.86	12.56	12.96	14.46
	6H	12.46	12.79	13.58	13.93	15.42	12.08	12.41	13.20	13.55	15.04
	8H	12.68	12.97	13.80	14.09	15.60	12.28	12.57	13.41	13.70	15.21
	12H	12.80	13.06	13.93	14.17	15.72	12.39	12.64	13.52	13.76	15.31
12H	4H	11.82	12.18	12.94	13.29	14.79	11.45	11.81	12.57	12.92	14.42
	6H	12.49	12.78	13.62	13.90	15.41	12.12	12.41	13.24	13.53	15.04
	8H	12.72	12.98	13.85	14.09	15.64	12.34	12.60	13.47	13.71	15.26