

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906576

Luminaire Tested: DFN2DIP-SQ3F0-100D090US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906576
REPORT IS A COMBINATION OF REPORTS P899963 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D090US835-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17865.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 167
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4458	4458	4458
5°	4463	4393	4424
10°	4424	4331	4363
15°	4356	4257	4268
20°	4265	4155	4171
25°	4175	4034	4059
30°	4062	3920	3916
35°	3955	3787	3766
40°	3824	3653	3623
45°	3693	3518	3476
50°	3550	3376	3306
55°	3400	3212	3150
60°	3230	3017	2970
65°	3044	2816	2759
70°	2807	2569	2531
75°	2480	2274	2319
80°	2084	1897	1917
85°	1467	1258	1254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3693 cd/sqm

TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	2.0
10°-20°	1030.4	5.8
20°-30°	1514.3	8.5
30°-40°	1758.8	9.8
40°-50°	1756.6	9.8
50°-60°	1531.7	8.6
60°-70°	1132.3	6.3
70°-80°	640.6	3.6
80°-90°	177.2	1.0
90°-100°	176.1	1.0
100°-110°	559.6	3.1
110°-120°	957.7	5.4
120°-130°	1259.5	7.1
130°-140°	1413.8	7.9
140°-150°	1386.4	7.8
150°-160°	1163.0	6.5
160°-170°	771.2	4.3
170°-180°	269.6	1.5
0°-30°	2911.0	16.3
0°-40°	4669.7	26.1
0°-60°	7958.0	44.5
0°-90°	9908.1	55.5
90°-120°	1693.5	9.5
90°-150°	5753.1	32.2
90°-180°	7957.0	44.5
0°-180°	17865.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	3	31	84	79	82	17
95°	125	149	154	154	149	139
105°	517	523	529	533	533	545
115°	961	975	970	968	961	951
125°	1398	1419	1412	1405	1402	1249
135°	1808	1835	1840	1837	1830	1398
145°	2195	2212	2226	2228	2219	1372
155°	2510	2517	2525	2537	2529	1155
165°	2730	2728	2728	2745	2733	770
175°	2841	2834	2829	2846	2832	270
180°	2846	2846	2846	2846	2846	

TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	2.6	30.9	84.1	78.9	81.5
92.5°	53.2	72.1	74.7	77.2	77.2
95°	125.3	149.3	153.6	153.6	149.3
97.5°	208.5	230.8	240.3	240.3	240.3
100°	304.6	324.4	331.2	331.2	328.7
102.5°	405.9	420.5	429.9	432.5	429.9
105°	516.6	523.4	528.6	532.9	532.9
107.5°	626.4	636.7	636.7	638.4	626.4
110°	732.8	746.6	746.6	746.6	739.7

TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	847.8	862.4	859.8	853.0	847.8
115°	961.1	974.8	970.5	968.0	961.1
117.5°	1073.5	1092.4	1080.4	1073.5	1066.6
120°	1186.8	1205.6	1186.8	1186.8	1179.0
122.5°	1289.7	1313.8	1301.8	1294.9	1289.7
125°	1397.9	1419.3	1412.5	1404.7	1402.2
127.5°	1503.4	1530.0	1520.6	1510.3	1503.4
130°	1602.1	1633.0	1628.7	1623.5	1614.1
132.5°	1712.8	1736.8	1738.5	1726.5	1719.7
135°	1808.0	1834.6	1839.8	1837.2	1830.4
137.5°	1914.4	1935.9	1940.2	1938.5	1928.2
140°	2008.0	2029.4	2041.4	2041.4	2032.0
142.5°	2104.1	2125.5	2132.4	2135.0	2125.5
145°	2195.1	2212.2	2225.9	2228.5	2219.1
147.5°	2276.6	2298.0	2308.3	2312.6	2303.2
150°	2360.7	2375.3	2384.7	2392.4	2384.7
152.5°	2435.3	2449.9	2461.9	2471.4	2461.9
155°	2510.0	2516.8	2524.6	2536.6	2528.9
157.5°	2574.3	2579.5	2583.8	2600.9	2588.9
160°	2631.8	2637.0	2639.6	2654.1	2643.8
162.5°	2685.0	2685.0	2687.6	2703.9	2691.9
165°	2730.5	2727.9	2727.9	2745.1	2733.1
167.5°	2771.7	2764.0	2764.0	2781.1	2769.1
170°	2802.6	2795.7	2793.2	2810.3	2795.7
172.5°	2824.0	2817.2	2814.6	2831.8	2817.2
175°	2841.2	2834.3	2829.2	2846.4	2831.8
177.5°	2850.6	2843.8	2838.6	2853.2	2838.6
180°	2846.4	2846.4	2846.4	2846.4	2846.4

TEST NUMBER: P906576

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.92	13.83	13.83	14.76	15.95	12.48	13.39	13.38	14.32	15.51
	3H	14.58	15.40	15.50	16.34	17.55	14.09	14.91	15.01	15.85	17.06
	4H	15.17	15.94	16.10	16.88	18.11	14.67	15.45	15.61	16.39	17.61
	6H	15.57	16.28	16.51	17.23	18.47	15.07	15.78	16.01	16.73	17.97
	8H	15.67	16.35	16.62	17.32	18.55	15.17	15.85	16.12	16.81	18.05
	12H	15.72	16.37	16.68	17.32	18.59	15.21	15.86	16.17	16.82	18.08
4H	2H	13.38	14.16	14.32	15.10	16.32	13.03	13.80	13.97	14.75	15.97
	3H	15.25	15.90	16.20	16.87	18.11	14.84	15.49	15.79	16.46	17.70
	4H	15.96	16.55	16.92	17.52	18.78	15.54	16.13	16.50	17.09	18.36
	6H	16.47	16.98	17.45	17.97	19.24	16.04	16.55	17.02	17.54	18.80
	8H	16.62	17.10	17.60	18.08	19.36	16.19	16.66	17.16	17.65	18.92
	12H	16.70	17.13	17.69	18.13	19.41	16.25	16.68	17.24	17.68	18.96
8H	4H	16.16	16.63	17.13	17.62	18.89	15.78	16.26	16.76	17.24	18.52
	6H	16.78	17.18	17.79	18.20	19.48	16.40	16.79	17.40	17.82	19.10
	8H	17.00	17.35	18.01	18.36	19.66	16.61	16.96	17.62	17.97	19.26
	12H	17.13	17.44	18.15	18.45	19.79	16.72	17.03	17.74	18.04	19.38
12H	4H	16.14	16.57	17.14	17.57	18.86	15.78	16.21	16.77	17.21	18.49
	6H	16.81	17.16	17.82	18.17	19.47	16.44	16.79	17.45	17.80	19.10
	8H	17.05	17.36	18.07	18.37	19.71	16.67	16.98	17.69	17.99	19.33

END OF REPORT