

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906584

Luminaire Tested: DFN2DIP-SQ3F0-100D110US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906584
REPORT IS A COMBINATION OF REPORTS P899999 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D110US835-FLLFL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19635.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906584
CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P906584

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57	50
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	42
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	42	63	53	45	40	45	39	35	38	34	30	31	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4458	4458	4458
5°	4463	4393	4424
10°	4424	4331	4363
15°	4356	4257	4268
20°	4265	4155	4171
25°	4175	4034	4059
30°	4062	3920	3916
35°	3955	3787	3766
40°	3824	3653	3623
45°	3693	3518	3476
50°	3550	3376	3306
55°	3400	3212	3150
60°	3230	3017	2970
65°	3044	2816	2759
70°	2807	2569	2531
75°	2480	2274	2319
80°	2084	1897	1917
85°	1467	1258	1254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3693 cd/sqm



TEST NUMBER: P906584

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	1.9
10°-20°	1030.4	5.2
20°-30°	1514.3	7.7
30°-40°	1758.8	9.0
40°-50°	1756.6	8.9
50°-60°	1531.7	7.8
60°-70°	1132.3	5.8
70°-80°	640.6	3.3
80°-90°	179.0	0.9
90°-100°	215.3	1.1
100°-110°	684.0	3.5
110°-120°	1170.5	6.0
120°-130°	1539.4	7.8
130°-140°	1727.9	8.8
140°-150°	1694.4	8.6
150°-160°	1421.4	7.2
160°-170°	942.6	4.8
170°-180°	329.5	1.7
0°-30°	2911.0	14.8
0°-40°	4669.7	23.8
0°-60°	7958.0	40.5
0°-90°	9909.9	50.5
90°-120°	2069.8	10.5
90°-150°	7031.6	35.8
90°-180°	9725.0	49.5
0°-180°	19635.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	3	38	103	96	100	19
95°	153	182	188	188	182	170
105°	631	640	646	651	651	666
115°	1175	1191	1186	1183	1175	1162
125°	1708	1735	1726	1717	1714	1527
135°	2210	2242	2249	2246	2237	1708
145°	2683	2704	2721	2724	2712	1676
155°	3068	3076	3086	3100	3091	1412
165°	3337	3334	3334	3355	3340	941
175°	3473	3464	3458	3479	3461	330
180°	3479	3479	3479	3479	3479	



TEST NUMBER: P906584

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	3.1	37.8	102.8	96.5	99.6
92.5°	65.0	88.1	91.2	94.4	94.4
95°	153.1	182.5	187.7	187.7	182.5
97.5°	254.9	282.1	293.7	293.7	293.7
100°	372.3	396.4	404.8	404.8	401.7
102.5°	496.1	513.9	525.5	528.6	525.5
105°	631.4	639.8	646.1	651.3	651.3
107.5°	765.6	778.2	778.2	780.3	765.6
110°	895.7	912.5	912.5	912.5	904.1



TEST NUMBER: P906584

CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1036.2	1054.0	1050.9	1042.5	1036.2
115°	1174.7	1191.4	1186.2	1183.1	1174.7
117.5°	1312.1	1335.1	1320.4	1312.1	1303.7
120°	1450.5	1473.6	1450.5	1450.5	1441.1
122.5°	1576.4	1605.7	1591.0	1582.6	1576.4
125°	1708.5	1734.7	1726.3	1716.9	1713.7
127.5°	1837.5	1870.0	1858.5	1845.9	1837.5
130°	1958.1	1995.9	1990.6	1984.3	1972.8
132.5°	2093.4	2122.8	2124.9	2110.2	2101.8
135°	2209.8	2242.3	2248.6	2245.5	2237.1
137.5°	2339.9	2366.1	2371.3	2369.2	2356.7
140°	2454.2	2480.4	2495.1	2495.1	2483.6
142.5°	2571.7	2597.9	2606.3	2609.4	2597.9
145°	2682.8	2703.8	2720.6	2723.7	2712.2
147.5°	2782.5	2808.7	2821.3	2826.5	2815.0
150°	2885.3	2903.1	2914.6	2924.1	2914.6
152.5°	2976.5	2994.3	3009.0	3020.6	3009.0
155°	3067.8	3076.1	3085.6	3100.3	3090.8
157.5°	3146.4	3152.7	3157.9	3178.9	3164.2
160°	3216.7	3223.0	3226.1	3244.0	3231.4
162.5°	3281.7	3281.7	3284.9	3304.8	3290.1
165°	3337.3	3334.1	3334.1	3355.1	3340.4
167.5°	3387.6	3378.2	3378.2	3399.2	3384.5
170°	3425.4	3417.0	3413.9	3434.8	3417.0
172.5°	3451.6	3443.2	3440.1	3461.1	3443.2
175°	3472.6	3464.2	3457.9	3478.9	3461.1
177.5°	3484.1	3475.7	3469.4	3487.3	3469.4
180°	3478.9	3478.9	3478.9	3478.9	3478.9



TEST NUMBER: P906584
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D110US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.47	13.34	13.43	14.31	15.57	12.03	12.89	12.98	13.86	15.13
	3H	14.13	14.91	15.09	15.88	17.17	13.64	14.42	14.60	15.39	16.68
	4H	14.71	15.45	15.69	16.43	17.73	14.22	14.96	15.20	15.94	17.23
	6H	15.11	15.79	16.10	16.78	18.08	14.61	15.29	15.60	16.28	17.58
	8H	15.21	15.86	16.21	16.86	18.17	14.71	15.36	15.71	16.36	17.67
	12H	15.26	15.87	16.26	16.87	18.20	14.75	15.37	15.75	16.36	17.69
4H	2H	12.93	13.67	13.92	14.65	15.94	12.58	13.31	13.56	14.29	15.59
	3H	14.79	15.41	15.79	16.42	17.73	14.38	15.00	15.38	16.01	17.32
	4H	15.50	16.06	16.50	17.07	18.40	15.08	15.64	16.08	16.64	17.98
	6H	16.01	16.50	17.03	17.52	18.85	15.58	16.06	16.59	17.09	18.42
	8H	16.16	16.61	17.18	17.63	18.98	15.72	16.18	16.74	17.20	18.54
	12H	16.23	16.64	17.27	17.68	19.03	15.78	16.19	16.82	17.23	18.58
8H	4H	15.70	16.15	16.71	17.17	18.51	15.32	15.77	16.33	16.79	18.14
	6H	16.32	16.69	17.36	17.76	19.10	15.94	16.31	16.98	17.37	18.72
	8H	16.54	16.87	17.59	17.92	19.28	16.15	16.47	17.19	17.52	18.88
	12H	16.67	16.96	17.72	18.00	19.40	16.26	16.55	17.31	17.59	18.99
12H	4H	15.68	16.09	16.71	17.12	18.47	15.31	15.72	16.35	16.76	18.11
	6H	16.35	16.68	17.40	17.73	19.09	15.98	16.31	17.02	17.35	18.72
	8H	16.59	16.88	17.64	17.92	19.32	16.21	16.50	17.26	17.54	18.94