

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909130

Luminaire Tested: DFN2DIP-SQ3F0-050D100US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P909130  
REPORT IS A COMBINATION OF REPORTS P899972 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-050D100US840-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13229.3 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 119.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909130  
CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P909130

CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29	24				24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21				21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18				18
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19	16				16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	14				14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13				13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11				11
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10				10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2391	2391	2391
5°	2393	2352	2368
10°	2368	2304	2290
15°	2334	2226	2170
20°	2290	2120	2023
25°	2244	2001	1881
30°	2183	1879	1702
35°	2123	1748	1544
40°	2062	1612	1364
45°	1992	1463	1200
50°	1918	1312	1040
55°	1842	1150	887
60°	1753	982	729
65°	1651	811	656
70°	1527	651	592
75°	1371	571	537
80°	1146	474	463
85°	778	309	344

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 3213 cd/sqm



TEST NUMBER: P909130

CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.6	1.5
10°-20°	536.9	4.1
20°-30°	753.8	5.7
30°-40°	821.7	6.2
40°-50°	755.2	5.7
50°-60°	593.1	4.5
60°-70°	386.1	2.9
70°-80°	198.7	1.5
80°-90°	59.8	0.5
90°-100°	197.6	1.5
100°-110°	627.9	4.7
110°-120°	1074.6	8.1
120°-130°	1413.3	10.7
130°-140°	1586.4	12.0
140°-150°	1555.6	11.8
150°-160°	1304.9	9.9
160°-170°	865.4	6.5
170°-180°	302.5	2.3
0°-30°	1486.3	11.2
0°-40°	2308.0	17.4
0°-60°	3656.4	27.6
0°-90°	4301.0	32.5
90°-120°	1900.2	14.4
90°-150°	6455.4	48.8
90°-180°	8928.0	67.5
0°-180°	13229.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	3	35	94	89	92	13
95°	141	168	172	172	168	156
105°	580	587	593	598	598	612
115°	1078	1094	1089	1086	1078	1067
125°	1568	1593	1585	1576	1573	1402
135°	2029	2059	2064	2062	2054	1568
145°	2463	2482	2498	2500	2490	1539
155°	2816	2824	2833	2846	2838	1296
165°	3064	3061	3061	3080	3067	864
175°	3188	3180	3175	3194	3177	303
180°	3194	3194	3194	3194	3194	



TEST NUMBER: P909130

CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	2.9	34.6	94.3	88.6	91.5
92.5°	59.7	80.9	83.8	86.6	86.6
95°	140.6	167.5	172.4	172.4	167.5
97.5°	234.0	259.0	269.6	269.6	269.6
100°	341.8	364.0	371.6	371.6	368.8
102.5°	455.4	471.8	482.4	485.2	482.4
105°	579.7	587.3	593.1	597.9	597.9
107.5°	702.9	714.5	714.5	716.4	702.9
110°	822.3	837.7	837.7	837.7	830.0



TEST NUMBER: P909130

CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	951.3	967.7	964.8	957.0	951.3
115°	1078.4	1093.8	1089.0	1086.1	1078.4
117.5°	1204.6	1225.8	1212.2	1204.6	1196.8
120°	1331.6	1352.8	1331.6	1331.6	1323.0
122.5°	1447.1	1474.1	1460.7	1453.0	1447.1
125°	1568.5	1592.6	1584.9	1576.2	1573.4
127.5°	1687.0	1716.8	1706.2	1694.7	1687.0
130°	1797.7	1832.3	1827.6	1821.7	1811.2
132.5°	1921.9	1948.8	1950.8	1937.3	1929.6
135°	2028.7	2058.6	2064.4	2061.5	2053.8
137.5°	2148.2	2172.2	2177.1	2175.1	2163.5
140°	2253.1	2277.1	2290.7	2290.7	2280.1
142.5°	2361.0	2385.0	2392.7	2395.6	2385.0
145°	2463.0	2482.2	2497.7	2500.5	2489.9
147.5°	2554.5	2578.6	2590.1	2595.0	2584.3
150°	2648.9	2665.2	2675.8	2684.4	2675.8
152.5°	2732.6	2749.0	2762.5	2773.1	2762.5
155°	2816.4	2824.1	2832.8	2846.2	2837.5
157.5°	2888.6	2894.4	2899.2	2918.4	2905.0
160°	2953.1	2958.9	2961.7	2978.1	2966.6
162.5°	3012.8	3012.8	3015.7	3033.9	3020.5
165°	3063.8	3060.9	3060.9	3080.2	3066.8
167.5°	3110.1	3101.4	3101.4	3120.7	3107.2
170°	3144.7	3137.0	3134.1	3153.4	3137.0
172.5°	3168.8	3161.1	3158.2	3177.4	3161.1
175°	3188.0	3180.4	3174.6	3193.8	3177.4
177.5°	3198.6	3191.0	3185.1	3201.5	3185.1
180°	3193.8	3193.8	3193.8	3193.8	3193.8



TEST NUMBER: P909130  
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D100US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.24	8.95	9.34	10.04	11.54	4.20	4.91	5.30	6.00	7.50
	3H	9.90	10.53	11.01	11.64	13.16	5.37	6.00	6.48	7.11	8.63
	4H	10.50	11.10	11.62	12.20	13.73	5.81	6.41	6.93	7.51	9.04
	6H	10.92	11.47	12.04	12.57	14.11	6.12	6.67	7.25	7.78	9.31
	8H	11.04	11.56	12.17	12.68	14.21	6.21	6.73	7.34	7.85	9.38
	12H	11.09	11.59	12.23	12.70	14.26	6.24	6.74	7.38	7.85	9.41
4H	2H	8.24	8.84	9.37	9.94	11.47	4.78	5.38	5.90	6.48	8.01
	3H	10.05	10.55	11.18	11.68	13.22	6.11	6.61	7.24	7.74	9.27
	4H	10.74	11.19	11.87	12.31	13.87	6.65	7.10	7.78	8.22	9.78
	6H	11.24	11.63	12.38	12.77	14.32	7.05	7.44	8.19	8.59	10.14
	8H	11.41	11.78	12.55	12.91	14.48	7.18	7.54	8.32	8.67	10.24
	12H	11.50	11.83	12.65	12.97	14.54	7.23	7.56	8.39	8.71	10.28
8H	4H	10.69	11.06	11.83	12.19	13.76	6.92	7.28	8.06	8.41	9.98
	6H	11.25	11.55	12.41	12.73	14.29	7.42	7.72	8.58	8.90	10.46
	8H	11.46	11.73	12.63	12.88	14.46	7.61	7.87	8.77	9.02	10.61
	12H	11.59	11.82	12.76	12.98	14.59	7.71	7.95	8.88	9.10	10.71
12H	4H	10.64	10.97	11.80	12.12	13.69	6.91	7.24	8.07	8.39	9.96
	6H	11.23	11.49	12.39	12.64	14.23	7.47	7.73	8.63	8.89	10.47
	8H	11.44	11.67	12.61	12.82	14.44	7.67	7.90	8.84	9.05	10.67