

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909146

Luminaire Tested: DFN2DIP-SQ3F0-060D050US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909146
REPORT IS A COMBINATION OF REPORTS P899884 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D050US840-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9619.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 90.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909146
CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P909146

CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	48	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	43	40	38	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	38	36	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2869	2869	2869
5°	2872	2822	2841
10°	2842	2765	2748
15°	2801	2671	2604
20°	2747	2544	2428
25°	2692	2401	2258
30°	2619	2255	2042
35°	2548	2098	1853
40°	2475	1935	1637
45°	2390	1755	1440
50°	2302	1574	1248
55°	2210	1380	1064
60°	2104	1178	875
65°	1981	973	787
70°	1832	781	711
75°	1646	685	644
80°	1375	568	556
85°	933	370	412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2390 cd/sqm



TEST NUMBER: P909146

CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.4
10°-20°	644.3	6.7
20°-30°	904.6	9.4
30°-40°	986.1	10.3
40°-50°	906.3	9.4
50°-60°	711.7	7.4
60°-70°	463.3	4.8
70°-80°	238.5	2.5
80°-90°	65.4	0.7
90°-100°	98.8	1.0
100°-110°	314.0	3.3
110°-120°	537.3	5.6
120°-130°	706.6	7.3
130°-140°	793.2	8.2
140°-150°	777.8	8.1
150°-160°	652.5	6.8
160°-170°	432.7	4.5
170°-180°	151.2	1.6
0°-30°	1783.6	18.5
0°-40°	2769.6	28.8
0°-60°	4387.7	45.6
0°-90°	5154.9	53.6
90°-120°	950.1	9.9
90°-150°	3227.7	33.6
90°-180°	4464.0	46.4
0°-180°	9619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	17	47	44	46	9
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P909146

CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P909146

CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P909146
 CATALOG NUMBER: DFN2DIP-SQ3F0-060D050US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.10	11.96	12.04	12.91	14.13	7.06	7.92	8.00	8.87	10.09
	3H	12.78	13.55	13.72	14.50	15.75	8.25	9.02	9.19	9.97	11.22
	4H	13.39	14.11	14.34	15.07	16.33	8.70	9.42	9.65	10.38	11.64
	6H	13.81	14.47	14.77	15.44	16.71	9.01	9.68	9.98	10.65	11.91
	8H	13.93	14.57	14.91	15.55	16.81	9.10	9.74	10.08	10.72	11.98
	12H	13.99	14.60	14.97	15.57	16.86	9.14	9.75	10.12	10.72	12.01
4H	2H	11.12	11.85	12.09	12.81	14.06	7.66	8.39	8.63	9.35	10.60
	3H	12.95	13.55	13.92	14.54	15.81	9.01	9.61	9.98	10.60	11.87
	4H	13.64	14.19	14.62	15.17	16.47	9.55	10.10	10.53	11.08	12.38
	6H	14.15	14.63	15.15	15.63	16.92	9.96	10.44	10.96	11.44	12.74
	8H	14.33	14.77	15.32	15.77	17.07	10.09	10.53	11.09	11.53	12.84
	12H	14.42	14.82	15.43	15.83	17.14	10.15	10.55	11.17	11.57	12.88
8H	4H	13.61	14.05	14.60	15.05	16.36	9.83	10.27	10.83	11.27	12.58
	6H	14.17	14.54	15.19	15.58	16.88	10.34	10.71	11.36	11.75	13.05
	8H	14.38	14.71	15.41	15.73	17.06	10.53	10.85	11.56	11.88	13.20
	12H	14.52	14.80	15.55	15.83	17.19	10.64	10.93	11.67	11.95	13.31
12H	4H	13.56	13.96	14.58	14.98	16.29	9.84	10.23	10.85	11.25	12.56
	6H	14.14	14.47	15.17	15.50	16.82	10.39	10.71	11.42	11.74	13.06
	8H	14.36	14.65	15.39	15.67	17.04	10.60	10.88	11.63	11.90	13.27