

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909194

Luminaire Tested: DFN2DIP-SQ3F0-070D080US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909194
REPORT IS A COMBINATION OF REPORTS P899940 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D080US840-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13158.5 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909194
CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P909194

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15	15	15	15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3348	3348	3348
5°	3351	3292	3314
10°	3316	3225	3206
15°	3268	3117	3038
20°	3205	2968	2832
25°	3141	2801	2634
30°	3056	2630	2383
35°	2972	2447	2162
40°	2887	2258	1909
45°	2788	2048	1680
50°	2686	1836	1457
55°	2579	1610	1242
60°	2455	1374	1021
65°	2311	1135	918
70°	2138	912	829
75°	1920	799	752
80°	1604	663	648
85°	1088	432	481

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2788 cd/sqm



TEST NUMBER: P909194

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	2.1
10°-20°	751.7	5.7
20°-30°	1055.3	8.0
30°-40°	1150.4	8.7
40°-50°	1057.3	8.0
50°-60°	830.4	6.3
60°-70°	540.5	4.1
70°-80°	278.2	2.1
80°-90°	78.3	0.6
90°-100°	158.1	1.2
100°-110°	502.4	3.8
110°-120°	859.7	6.5
120°-130°	1130.6	8.6
130°-140°	1269.1	9.6
140°-150°	1244.5	9.5
150°-160°	1043.9	7.9
160°-170°	692.3	5.3
170°-180°	242.0	1.8
0°-30°	2080.9	15.8
0°-40°	3231.2	24.6
0°-60°	5118.9	38.9
0°-90°	6015.9	45.7
90°-120°	1520.1	11.6
90°-150°	5164.3	39.2
90°-180°	7143.0	54.3
0°-180°	13158.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2922	2908	2874	2898	2890	277
15°	2779	2750	2660	2610	2583	783
25°	2522	2438	2263	2155	2115	1160
35°	2173	2038	1806	1639	1581	1360
45°	1777	1600	1322	1134	1071	1372
55°	1351	1145	859	701	651	1207
65°	912	698	460	370	362	904
75°	486	301	212	193	190	515
85°	114	58	50	50	50	130
90°	2	28	76	71	73	13
95°	112	134	138	138	134	125
105°	464	470	474	478	478	489
115°	863	875	871	869	863	853
125°	1255	1274	1268	1261	1259	1121
135°	1623	1647	1652	1649	1643	1254
145°	1970	1986	1998	2000	1992	1231
155°	2253	2259	2266	2277	2270	1037
165°	2451	2449	2449	2464	2453	691
175°	2550	2544	2540	2555	2542	242
180°	2555	2555	2555	2555	2555	



TEST NUMBER: P909194

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2921.6	2921.6	2921.6	2921.6	2921.6
2.5°	2934.8	2921.6	2892.5	2919.1	2913.8
5°	2921.6	2908.4	2874.0	2897.8	2889.9
7.5°	2897.8	2882.1	2845.1	2855.4	2842.3
10°	2866.1	2847.6	2794.8	2786.7	2771.0
12.5°	2826.5	2802.7	2731.2	2715.4	2686.2
15°	2778.8	2749.7	2659.9	2609.7	2583.3
17.5°	2723.3	2681.0	2569.9	2511.7	2469.4
20°	2659.9	2606.9	2474.8	2408.8	2350.5
22.5°	2591.2	2530.3	2376.8	2287.0	2247.6
25°	2522.4	2437.7	2263.2	2155.0	2115.2
27.5°	2440.5	2350.5	2157.5	2033.3	1972.4
30°	2353.3	2252.6	2041.0	1906.4	1834.9
32.5°	2268.6	2146.9	1930.3	1771.5	1705.3
35°	2173.4	2038.5	1806.0	1639.4	1581.0
37.5°	2080.9	1935.3	1689.6	1506.9	1441.1
40°	1983.0	1824.5	1567.8	1380.2	1311.4
42.5°	1882.6	1713.4	1446.3	1250.5	1184.7
45°	1776.9	1599.5	1322.1	1134.2	1070.8
47.5°	1676.4	1488.7	1203.2	1015.2	957.2
50°	1565.3	1377.7	1086.7	904.1	848.9
52.5°	1456.7	1258.4	975.6	801.1	750.9
55°	1351.0	1144.8	859.2	700.7	650.6
57.5°	1242.7	1031.2	756.3	608.1	565.8
60°	1131.7	920.1	647.7	513.1	470.7
62.5°	1023.3	811.8	555.1	428.4	407.3
65°	912.2	697.9	460.1	370.3	362.1
67.5°	806.5	592.2	370.3	325.1	317.3
70°	695.4	489.2	306.6	280.2	269.5
72.5°	589.7	393.8	256.4	235.4	230.0
75°	486.5	301.2	211.5	193.0	190.5
77.5°	383.4	214.0	166.6	155.9	150.7
80°	288.1	153.4	126.8	116.4	116.4
82.5°	200.9	103.2	87.3	81.9	81.9
85°	113.6	58.1	50.2	50.2	50.2
87.5°	42.3	21.0	21.0	18.5	18.5
90°	2.3	27.8	75.5	70.9	73.2
92.5°	47.8	64.7	67.1	69.3	69.3
95°	112.5	134.0	137.8	137.8	134.0
97.5°	187.2	207.2	215.7	215.7	215.7
100°	273.5	291.1	297.3	297.3	295.0
102.5°	364.4	377.5	385.9	388.2	385.9
105°	463.7	469.9	474.5	478.4	478.4
107.5°	562.3	571.6	571.6	573.1	562.3
110°	657.8	670.1	670.1	670.1	664.0



TEST NUMBER: P909194

CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	761.0	774.2	771.8	765.7	761.0
115°	862.7	875.0	871.2	868.9	862.7
117.5°	963.6	980.6	969.8	963.6	957.5
120°	1065.3	1082.3	1065.3	1065.3	1058.3
122.5°	1157.7	1179.3	1168.5	1162.4	1157.7
125°	1254.8	1274.0	1267.9	1260.9	1258.7
127.5°	1349.6	1373.4	1364.9	1355.7	1349.6
130°	1438.1	1465.8	1462.0	1457.4	1449.0
132.5°	1537.5	1559.0	1560.6	1549.8	1543.7
135°	1623.0	1646.9	1651.5	1649.2	1643.1
137.5°	1718.5	1737.8	1741.6	1740.1	1730.8
140°	1802.5	1821.7	1832.5	1832.5	1824.0
142.5°	1888.8	1908.0	1914.2	1916.5	1908.0
145°	1970.4	1985.8	1998.1	2000.4	1992.0
147.5°	2043.6	2062.9	2072.0	2076.0	2067.5
150°	2119.1	2132.1	2140.6	2147.6	2140.6
152.5°	2186.1	2199.2	2210.0	2218.5	2210.0
155°	2253.1	2259.3	2266.2	2276.9	2270.1
157.5°	2310.9	2315.5	2319.4	2334.7	2324.0
160°	2362.5	2367.1	2369.4	2382.5	2373.3
162.5°	2410.2	2410.2	2412.6	2427.2	2416.4
165°	2451.0	2448.7	2448.7	2464.2	2453.4
167.5°	2488.0	2481.1	2481.1	2496.5	2485.7
170°	2515.8	2509.6	2507.3	2522.7	2509.6
172.5°	2535.1	2528.9	2526.6	2541.9	2528.9
175°	2550.4	2544.3	2539.6	2555.1	2541.9
177.5°	2558.9	2552.7	2548.1	2561.2	2548.1
180°	2555.1	2555.1	2555.1	2555.1	2555.1



TEST NUMBER: P909194
 CATALOG NUMBER: DFN2DIP-SQ3F0-070D080US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.90	11.69	11.89	12.70	14.03	6.86	7.65	7.85	8.66	9.99
	3H	12.57	13.28	13.58	14.29	15.65	8.04	8.75	9.05	9.76	11.12
	4H	13.17	13.84	14.19	14.86	16.22	8.48	9.15	9.50	10.17	11.53
	6H	13.59	14.21	14.62	15.23	16.60	8.79	9.41	9.83	10.44	11.81
	8H	13.71	14.30	14.75	15.34	16.71	8.88	9.47	9.92	10.51	11.88
	12H	13.77	14.33	14.81	15.36	16.75	8.92	9.48	9.96	10.51	11.91
4H	2H	10.91	11.58	11.94	12.60	13.96	7.44	8.12	8.47	9.14	10.50
	3H	12.73	13.29	13.77	14.34	15.71	8.78	9.34	9.82	10.39	11.77
	4H	13.42	13.93	14.46	14.97	16.36	9.33	9.84	10.37	10.88	12.27
	6H	13.92	14.36	14.98	15.43	16.82	9.74	10.18	10.79	11.24	12.63
	8H	14.10	14.51	15.15	15.56	16.97	9.86	10.27	10.91	11.33	12.73
	12H	14.19	14.56	15.26	15.63	17.04	9.92	10.29	10.99	11.36	12.77
8H	4H	13.38	13.79	14.43	14.84	16.25	9.60	10.01	10.65	11.07	12.47
	6H	13.94	14.28	15.02	15.37	16.78	10.11	10.45	11.19	11.54	12.95
	8H	14.15	14.45	15.24	15.53	16.95	10.29	10.59	11.38	11.67	13.10
	12H	14.29	14.55	15.37	15.62	17.09	10.41	10.67	11.49	11.74	13.21
12H	4H	13.33	13.70	14.40	14.77	16.18	9.60	9.97	10.67	11.04	12.46
	6H	13.91	14.21	15.00	15.29	16.72	10.16	10.45	11.24	11.53	12.96
	8H	14.13	14.39	15.22	15.47	16.93	10.36	10.62	11.45	11.70	13.16