

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909252

Luminaire Tested: DFN2DIP-SQ3F0-090D050US840-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P909252  
REPORT IS A COMBINATION OF REPORTS P899889 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-090D050US840-FLLFLL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13466.6 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 124.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909252  
CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P909252

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	61	56	56	56	56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47	47	47	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40	40	40	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	37	34	34	34	34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30	30	30	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26	26	26	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23	23	23	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	30	26	23	21	21	21	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19	19	19	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17	17	17	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4052	4052	4052
5°	4056	3993	4021
10°	4021	3936	3965
15°	3959	3869	3879
20°	3876	3776	3791
25°	3794	3666	3689
30°	3692	3563	3559
35°	3595	3442	3423
40°	3476	3320	3292
45°	3357	3197	3159
50°	3227	3068	3005
55°	3090	2919	2863
60°	2935	2742	2700
65°	2767	2559	2508
70°	2551	2335	2301
75°	2254	2067	2107
80°	1894	1724	1742
85°	1334	1143	1140

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3357 cd/sqm



TEST NUMBER: P909252

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.9	2.5
10°-20°	936.5	7.0
20°-30°	1376.3	10.2
30°-40°	1598.5	11.9
40°-50°	1596.5	11.9
50°-60°	1392.1	10.3
60°-70°	1029.1	7.6
70°-80°	582.2	4.3
80°-90°	158.2	1.2
90°-100°	98.8	0.7
100°-110°	314.0	2.3
110°-120°	537.3	4.0
120°-130°	706.6	5.2
130°-140°	793.2	5.9
140°-150°	777.8	5.8
150°-160°	652.5	4.8
160°-170°	432.7	3.2
170°-180°	151.2	1.1
0°-30°	2645.7	19.6
0°-40°	4244.2	31.5
0°-60°	7232.9	53.7
0°-90°	9002.5	66.9
90°-120°	950.1	7.1
90°-150°	3227.7	24.0
90°-180°	4464.0	33.1
0°-180°	13466.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3536	3536	3536	3536	3536	
5°	3536	3523	3486	3513	3506	336
15°	3367	3346	3302	3316	3299	948
25°	3047	3020	2962	2969	2962	1402
35°	2629	2595	2540	2520	2503	1642
45°	2139	2115	2064	2027	2013	1651
55°	1619	1598	1558	1517	1500	1447
65°	1092	1071	1037	1007	990	1079
75°	571	565	547	527	534	610
85°	139	136	133	122	119	155
90°	1	17	47	44	46	13
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P909252

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3536.4	3536.4	3536.4	3536.4	3536.4
2.5°	3557.0	3540.1	3502.6	3536.4	3530.0
5°	3536.4	3523.1	3485.7	3512.7	3506.2
7.5°	3512.7	3492.5	3455.0	3482.4	3475.6
10°	3475.6	3451.7	3410.9	3438.0	3427.9
12.5°	3424.3	3404.1	3363.4	3380.2	3373.5
15°	3366.6	3346.4	3302.0	3315.7	3298.7
17.5°	3295.1	3274.9	3230.6	3247.5	3230.6
20°	3216.8	3196.6	3149.0	3159.1	3145.7
22.5°	3138.9	3108.3	3063.8	3063.8	3057.0
25°	3046.9	3019.8	2962.1	2968.6	2962.1
27.5°	2944.8	2920.9	2877.0	2866.9	2849.9
30°	2843.1	2815.6	2764.7	2754.6	2741.0
32.5°	2734.1	2713.9	2659.4	2638.9	2625.1
35°	2628.8	2594.8	2540.3	2519.8	2502.9
37.5°	2509.7	2479.0	2424.5	2400.8	2383.8
40°	2387.3	2360.0	2305.4	2275.1	2261.5
42.5°	2268.3	2240.9	2186.8	2152.5	2132.3
45°	2139.1	2115.4	2064.1	2026.9	2013.3
47.5°	2013.3	1989.4	1934.9	1897.4	1877.2
50°	1880.5	1863.5	1815.8	1768.3	1751.3
52.5°	1751.3	1727.5	1683.4	1646.0	1622.1
55°	1618.9	1598.3	1557.5	1516.8	1499.9
57.5°	1486.1	1469.2	1424.8	1384.0	1370.3
60°	1353.3	1340.0	1292.3	1254.9	1244.8
62.5°	1224.2	1200.3	1166.4	1132.6	1118.8
65°	1091.8	1071.2	1037.2	1006.6	989.7
67.5°	955.7	938.5	908.1	884.3	870.6
70°	829.8	816.1	785.5	761.6	748.3
72.5°	700.6	686.9	669.9	646.2	636.1
75°	571.2	564.6	547.3	527.1	534.0
77.5°	455.7	442.0	435.2	425.1	415.0
80°	340.2	336.6	329.7	319.6	312.9
82.5°	231.3	231.3	228.0	214.3	214.3
85°	139.3	136.0	132.8	122.3	119.1
87.5°	61.3	54.4	47.7	37.6	33.9
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P909252

CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P909252  
 CATALOG NUMBER: DFN2DIP-SQ3F0-090D050US840-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.52	14.56	14.32	15.38	16.39	13.08	14.12	13.88	14.94	15.94
	3H	15.19	16.12	16.00	16.95	17.99	14.70	15.63	15.51	16.46	17.50
	4H	15.79	16.66	16.61	17.50	18.55	15.29	16.17	16.12	17.01	18.06
	6H	16.19	17.00	17.03	17.85	18.91	15.69	16.50	16.53	17.35	18.41
	8H	16.30	17.07	17.15	17.94	19.00	15.80	16.57	16.65	17.43	18.50
	12H	16.35	17.09	17.21	17.95	19.03	15.84	16.58	16.70	17.44	18.52
4H	2H	14.00	14.88	14.83	15.72	16.77	13.65	14.53	14.48	15.36	16.41
	3H	15.88	16.61	16.72	17.48	18.55	15.47	16.20	16.31	17.08	18.14
	4H	16.60	17.26	17.45	18.13	19.22	16.17	16.84	17.03	17.71	18.80
	6H	17.12	17.70	17.99	18.59	19.68	16.68	17.26	17.56	18.16	19.25
	8H	17.27	17.81	18.14	18.70	19.80	16.83	17.37	17.71	18.26	19.37
	12H	17.35	17.83	18.24	18.74	19.85	16.90	17.39	17.79	18.29	19.41
8H	4H	16.80	17.34	17.68	18.23	19.34	16.43	16.97	17.30	17.85	18.96
	6H	17.43	17.88	18.34	18.81	19.92	17.05	17.50	17.95	18.43	19.54
	8H	17.65	18.05	18.57	18.97	20.10	17.26	17.66	18.17	18.58	19.71
	12H	17.79	18.14	18.71	19.05	20.23	17.38	17.73	18.30	18.64	19.82
12H	4H	16.80	17.28	17.69	18.19	19.30	16.43	16.91	17.32	17.82	18.93
	6H	17.46	17.86	18.38	18.78	19.91	17.09	17.49	18.01	18.41	19.54
	8H	17.71	18.06	18.63	18.97	20.15	17.33	17.68	18.25	18.59	19.77