

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903841

Luminaire Tested: DFN2DIP-SQ3F0-100D070US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903841
REPORT IS A COMBINATION OF REPORTS P901447 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D070US830-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15863.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 151
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54
2	91	83	77	72	85	78	72	68	68	64	60	59	55	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4202	4202	4202
5°	4206	4141	4170
10°	4170	4082	4112
15°	4106	4012	4023
20°	4020	3916	3931
25°	3935	3802	3825
30°	3829	3695	3691
35°	3728	3570	3549
40°	3604	3443	3414
45°	3481	3316	3276
50°	3346	3182	3116
55°	3205	3027	2969
60°	3044	2844	2800
65°	2869	2654	2601
70°	2646	2422	2386
75°	2338	2144	2185
80°	1964	1789	1806
85°	1383	1185	1183

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3481 cd/sqm

TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	2.2
10°-20°	971.2	6.1
20°-30°	1427.3	9.0
30°-40°	1657.7	10.5
40°-50°	1655.7	10.4
50°-60°	1443.7	9.1
60°-70°	1067.2	6.7
70°-80°	603.8	3.8
80°-90°	163.3	1.0
90°-100°	73.4	0.5
100°-110°	273.7	1.7
110°-120°	725.9	4.6
120°-130°	1204.0	7.6
130°-140°	1278.9	8.1
140°-150°	1188.6	7.5
150°-160°	955.6	6.0
160°-170°	615.8	3.9
170°-180°	211.9	1.3
0°-30°	2743.7	17.3
0°-40°	4401.4	27.7
0°-60°	7500.8	47.3
0°-90°	9335.1	58.8
90°-120°	1073.0	6.8
90°-150°	4744.6	29.9
90°-180°	6528.0	41.2
0°-180°	15863.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3668	3668	3668	3668	3668	
5°	3668	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2596	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	2	19	32	40	44	15
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	

TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3667.5	3667.5	3667.5	3667.5	3667.5
2.5°	3688.8	3671.2	3632.3	3667.5	3660.7
5°	3667.5	3653.7	3614.7	3642.8	3636.0
7.5°	3642.8	3621.8	3582.9	3611.4	3604.3
10°	3604.3	3579.6	3537.3	3565.4	3554.9
12.5°	3551.1	3530.2	3487.9	3505.5	3498.3
15°	3491.3	3470.3	3424.3	3438.5	3421.0
17.5°	3417.2	3396.3	3350.2	3367.8	3350.2
20°	3335.9	3315.0	3265.6	3276.1	3262.2
22.5°	3255.2	3223.4	3177.3	3177.3	3170.2
25°	3159.8	3131.7	3071.8	3078.5	3071.8
27.5°	3053.8	3029.1	2983.5	2973.1	2955.4
30°	2948.4	2919.9	2867.1	2856.7	2842.4
32.5°	2835.4	2814.4	2757.9	2736.6	2722.3
35°	2726.1	2691.0	2634.4	2613.1	2595.5
37.5°	2602.6	2570.8	2514.3	2489.6	2472.0
40°	2475.8	2447.3	2390.9	2359.5	2345.2
42.5°	2352.3	2323.8	2267.8	2232.2	2211.3
45°	2218.4	2193.7	2140.5	2102.0	2087.8
47.5°	2087.8	2063.1	2006.6	1967.7	1946.7
50°	1950.1	1932.5	1883.1	1833.7	1816.2
52.5°	1816.2	1791.5	1745.8	1706.9	1682.2
55°	1678.9	1657.6	1615.2	1572.9	1555.4
57.5°	1541.2	1523.5	1477.5	1435.3	1421.1
60°	1403.4	1389.6	1340.2	1301.3	1290.8
62.5°	1269.5	1244.8	1209.7	1174.5	1160.3
65°	1132.2	1110.9	1075.7	1043.9	1026.3
67.5°	991.2	973.2	941.8	917.1	902.9
70°	860.5	846.3	814.5	789.9	776.0
72.5°	726.6	712.4	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.7	553.7
77.5°	472.6	458.4	451.2	440.7	430.3
80°	352.8	349.1	342.0	331.5	324.4
82.5°	239.9	239.9	236.5	222.3	222.3
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2

TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7

TEST NUMBER: P903841

CATALOG NUMBER: DFN2DIP-SQ3F0-100D070US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.00	13.95	13.88	14.85	15.99	12.56	13.51	13.44	14.41	15.54
	3H	14.67	15.52	15.56	16.42	17.59	14.18	15.03	15.07	15.93	17.10
	4H	15.26	16.06	16.16	16.97	18.15	14.76	15.56	15.67	16.48	17.65
	6H	15.66	16.40	16.57	17.32	18.50	15.16	15.90	16.07	16.82	18.00
	8H	15.76	16.47	16.69	17.40	18.59	15.26	15.97	16.18	16.90	18.09
	12H	15.81	16.48	16.74	17.41	18.63	15.30	15.97	16.23	16.90	18.12
4H	2H	13.47	14.28	14.38	15.19	16.36	13.12	13.92	14.03	14.83	16.01
	3H	15.34	16.01	16.26	16.96	18.14	14.93	15.60	15.85	16.55	17.74
	4H	16.05	16.67	16.99	17.61	18.82	15.63	16.24	16.56	17.18	18.40
	6H	16.57	17.10	17.52	18.06	19.28	16.14	16.67	17.08	17.63	18.84
	8H	16.72	17.21	17.67	18.17	19.40	16.28	16.78	17.23	17.73	18.96
	12H	16.79	17.24	17.76	18.21	19.45	16.35	16.79	17.31	17.77	19.00
8H	4H	16.25	16.75	17.20	17.70	18.93	15.88	16.37	16.82	17.33	18.56
	6H	16.88	17.29	17.86	18.29	19.52	16.50	16.91	17.47	17.91	19.13
	8H	17.10	17.46	18.08	18.45	19.70	16.71	17.07	17.69	18.06	19.30
	12H	17.23	17.55	18.22	18.53	19.83	16.82	17.14	17.81	18.12	19.41
12H	4H	16.24	16.69	17.21	17.66	18.90	15.87	16.32	16.84	17.29	18.53
	6H	16.91	17.27	17.89	18.26	19.51	16.54	16.90	17.52	17.89	19.13
	8H	17.15	17.47	18.14	18.45	19.75	16.77	17.09	17.76	18.07	19.37

END OF REPORT