

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909372

Luminaire Tested: DFN2DIP-SQ3F0-120D080US840-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P909372  
REPORT IS A COMBINATION OF REPORTS P899949 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-120D080US840-FLLFLL  
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19147.0 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 186.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9957  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909372  
CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P909372

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	47	44	41	37
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5403	5403	5403
5°	5408	5324	5362
10°	5361	5249	5287
15°	5279	5159	5172
20°	5168	5035	5054
25°	5059	4888	4918
30°	4923	4751	4746
35°	4793	4589	4564
40°	4634	4426	4390
45°	4476	4263	4212
50°	4302	4091	4006
55°	4120	3892	3817
60°	3914	3656	3600
65°	3689	3412	3344
70°	3402	3114	3067
75°	3005	2756	2810
80°	2526	2300	2322
85°	1778	1523	1521

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4476 cd/sqm



TEST NUMBER: P909372

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.8	2.3
10°-20°	1248.7	6.5
20°-30°	1835.1	9.6
30°-40°	2131.4	11.1
40°-50°	2128.7	11.1
50°-60°	1856.2	9.7
60°-70°	1372.1	7.2
70°-80°	776.3	4.1
80°-90°	212.2	1.1
90°-100°	158.1	0.8
100°-110°	502.4	2.6
110°-120°	859.7	4.5
120°-130°	1130.6	5.9
130°-140°	1269.1	6.6
140°-150°	1244.5	6.5
150°-160°	1043.9	5.5
160°-170°	692.3	3.6
170°-180°	242.0	1.3
0°-30°	3527.6	18.4
0°-40°	5659.0	29.6
0°-60°	9643.8	50.4
0°-90°	12004.4	62.7
90°-120°	1520.1	7.9
90°-150°	5164.3	27.0
90°-180°	7143.0	37.3
0°-180°	19147.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4715	4715	4715	4715	4715	
5°	4715	4698	4648	4684	4675	448
15°	4489	4462	4403	4421	4398	1264
25°	4062	4026	3950	3958	3950	1869
35°	3505	3460	3387	3360	3337	2189
45°	2852	2820	2752	2703	2684	2201
55°	2158	2131	2077	2022	2000	1930
65°	1456	1428	1383	1342	1320	1439
75°	762	753	730	703	712	813
85°	186	181	177	163	159	207
90°	2	28	76	71	73	18
95°	112	134	138	138	134	125
105°	464	470	474	478	478	489
115°	863	875	871	869	863	853
125°	1255	1274	1268	1261	1259	1121
135°	1623	1647	1652	1649	1643	1254
145°	1970	1986	1998	2000	1992	1231
155°	2253	2259	2266	2277	2270	1037
165°	2451	2449	2449	2464	2453	691
175°	2550	2544	2540	2555	2542	242
180°	2555	2555	2555	2555	2555	



TEST NUMBER: P909372

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4715.4	4715.4	4715.4	4715.4	4715.4
2.5°	4742.7	4720.1	4670.1	4715.4	4706.7
5°	4715.4	4697.5	4647.5	4683.6	4674.9
7.5°	4683.6	4656.6	4606.6	4643.2	4634.1
10°	4634.1	4602.3	4547.9	4584.0	4570.6
12.5°	4565.7	4538.7	4484.4	4507.0	4497.8
15°	4488.8	4461.8	4402.6	4420.9	4398.3
17.5°	4393.5	4366.6	4307.4	4330.0	4307.4
20°	4289.1	4262.1	4198.7	4212.1	4194.4
22.5°	4185.2	4144.3	4085.1	4085.1	4076.0
25°	4062.5	4026.4	3949.5	3958.2	3949.5
27.5°	3926.4	3894.6	3836.0	3822.4	3799.9
30°	3790.7	3754.2	3686.3	3672.9	3654.6
32.5°	3645.4	3618.6	3545.8	3518.5	3500.2
35°	3504.9	3459.8	3387.1	3359.7	3337.1
37.5°	3346.2	3305.4	3232.7	3201.0	3178.3
40°	3183.2	3146.6	3073.9	3033.5	3015.3
42.5°	3024.4	2987.9	2915.7	2870.0	2843.1
45°	2852.2	2820.5	2752.1	2702.6	2684.3
47.5°	2684.3	2652.5	2579.9	2529.9	2503.0
50°	2507.3	2484.7	2421.2	2357.6	2335.0
52.5°	2335.0	2303.3	2244.6	2194.5	2162.8
55°	2158.5	2131.1	2076.7	2022.4	1999.7
57.5°	1981.5	1958.8	1899.7	1845.3	1827.0
60°	1804.4	1786.7	1723.1	1673.1	1659.6
62.5°	1632.2	1600.4	1555.3	1510.1	1491.8
65°	1455.7	1428.3	1383.0	1342.1	1319.6
67.5°	1274.3	1251.2	1210.8	1179.1	1160.8
70°	1106.4	1088.1	1047.2	1015.5	997.7
72.5°	934.2	915.9	893.3	861.6	848.1
75°	761.5	752.9	729.7	702.9	712.0
77.5°	607.5	589.3	580.2	566.6	553.2
80°	453.6	448.8	439.7	426.3	417.1
82.5°	308.3	308.3	304.1	285.8	285.8
85°	185.7	181.4	177.0	163.1	158.8
87.5°	81.8	72.6	63.5	50.0	45.2
90°	2.3	27.8	75.5	70.9	73.2
92.5°	47.8	64.7	67.1	69.3	69.3
95°	112.5	134.0	137.8	137.8	134.0
97.5°	187.2	207.2	215.7	215.7	215.7
100°	273.5	291.1	297.3	297.3	295.0
102.5°	364.4	377.5	385.9	388.2	385.9
105°	463.7	469.9	474.5	478.4	478.4
107.5°	562.3	571.6	571.6	573.1	562.3
110°	657.8	670.1	670.1	670.1	664.0



TEST NUMBER: P909372

CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	761.0	774.2	771.8	765.7	761.0
115°	862.7	875.0	871.2	868.9	862.7
117.5°	963.6	980.6	969.8	963.6	957.5
120°	1065.3	1082.3	1065.3	1065.3	1058.3
122.5°	1157.7	1179.3	1168.5	1162.4	1157.7
125°	1254.8	1274.0	1267.9	1260.9	1258.7
127.5°	1349.6	1373.4	1364.9	1355.7	1349.6
130°	1438.1	1465.8	1462.0	1457.4	1449.0
132.5°	1537.5	1559.0	1560.6	1549.8	1543.7
135°	1623.0	1646.9	1651.5	1649.2	1643.1
137.5°	1718.5	1737.8	1741.6	1740.1	1730.8
140°	1802.5	1821.7	1832.5	1832.5	1824.0
142.5°	1888.8	1908.0	1914.2	1916.5	1908.0
145°	1970.4	1985.8	1998.1	2000.4	1992.0
147.5°	2043.6	2062.9	2072.0	2076.0	2067.5
150°	2119.1	2132.1	2140.6	2147.6	2140.6
152.5°	2186.1	2199.2	2210.0	2218.5	2210.0
155°	2253.1	2259.3	2266.2	2276.9	2270.1
157.5°	2310.9	2315.5	2319.4	2334.7	2324.0
160°	2362.5	2367.1	2369.4	2382.5	2373.3
162.5°	2410.2	2410.2	2412.6	2427.2	2416.4
165°	2451.0	2448.7	2448.7	2464.2	2453.4
167.5°	2488.0	2481.1	2481.1	2496.5	2485.7
170°	2515.8	2509.6	2507.3	2522.7	2509.6
172.5°	2535.1	2528.9	2526.6	2541.9	2528.9
175°	2550.4	2544.3	2539.6	2555.1	2541.9
177.5°	2558.9	2552.7	2548.1	2561.2	2548.1
180°	2555.1	2555.1	2555.1	2555.1	2555.1



TEST NUMBER: P909372  
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D080US840-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.19	15.18	15.03	16.04	17.12	13.75	14.74	14.59	15.60	16.68
	3H	15.86	16.75	16.71	17.62	18.72	15.37	16.26	16.22	17.13	18.23
	4H	16.45	17.29	17.32	18.17	19.28	15.95	16.79	16.82	17.67	18.79
	6H	16.85	17.63	17.73	18.51	19.64	16.35	17.13	17.23	18.01	19.14
	8H	16.96	17.70	17.85	18.60	19.73	16.46	17.19	17.35	18.10	19.22
	12H	17.01	17.71	17.90	18.61	19.76	16.50	17.20	17.40	18.10	19.25
4H	2H	14.67	15.50	15.54	16.38	17.50	14.31	15.15	15.18	16.03	17.14
	3H	16.54	17.24	17.42	18.15	19.28	16.13	16.83	17.01	17.74	18.87
	4H	17.25	17.89	18.15	18.80	19.95	16.83	17.47	17.73	18.37	19.53
	6H	17.77	18.32	18.68	19.25	20.41	17.34	17.89	18.25	18.82	19.98
	8H	17.92	18.44	18.84	19.36	20.53	17.48	18.00	18.40	18.92	20.10
	12H	18.00	18.46	18.93	19.41	20.58	17.55	18.01	18.48	18.96	20.13
8H	4H	17.46	17.97	18.37	18.90	20.07	17.08	17.59	17.99	18.52	19.69
	6H	18.09	18.51	19.03	19.48	20.65	17.70	18.13	18.64	19.10	20.27
	8H	18.30	18.68	19.26	19.64	20.83	17.91	18.29	18.86	19.25	20.44
	12H	18.44	18.77	19.39	19.72	20.96	18.03	18.36	18.98	19.31	20.55
12H	4H	17.45	17.91	18.38	18.85	20.03	17.08	17.54	18.01	18.49	19.66
	6H	18.12	18.49	19.07	19.45	20.64	17.74	18.12	18.69	19.08	20.27
	8H	18.36	18.69	19.31	19.64	20.88	17.98	18.31	18.93	19.26	20.50