

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903897

Luminaire Tested: DFN2DIP-SQ3F0-110D120US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903897
REPORT IS A COMBINATION OF REPORTS P901539 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D120US830-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21461.6 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 206
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4623	4623	4623
5°	4627	4555	4587
10°	4586	4491	4524
15°	4516	4414	4425
20°	4422	4308	4324
25°	4328	4182	4208
30°	4212	4064	4060
35°	4101	3926	3904
40°	3965	3787	3756
45°	3829	3647	3604
50°	3681	3500	3428
55°	3525	3330	3266
60°	3349	3128	3080
65°	3156	2919	2861
70°	2910	2664	2624
75°	2571	2358	2404
80°	2161	1967	1987
85°	1522	1304	1300

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3829 cd/sqm

TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	1.8
10°-20°	1068.3	5.0
20°-30°	1570.0	7.3
30°-40°	1823.5	8.5
40°-50°	1821.2	8.5
50°-60°	1588.0	7.4
60°-70°	1173.9	5.5
70°-80°	664.2	3.1
80°-90°	182.0	0.8
90°-100°	125.9	0.6
100°-110°	469.2	2.2
110°-120°	1244.4	5.8
120°-130°	2064.0	9.6
130°-140°	2192.4	10.2
140°-150°	2037.6	9.5
150°-160°	1638.2	7.6
160°-170°	1055.6	4.9
170°-180°	363.3	1.7
0°-30°	3018.1	14.1
0°-40°	4841.6	22.6
0°-60°	8250.9	38.4
0°-90°	10271.0	47.9
90°-120°	1839.5	8.6
90°-150°	8133.6	37.9
90°-180°	11191.0	52.1
0°-180°	21461.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3767	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1873
45°	2440	2413	2355	2312	2297	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	696
85°	159	155	152	140	136	177
90°	3	33	55	69	74	20
95°	179	88	108	122	119	212
105°	840	923	169	199	210	897
115°	1588	1635	1704	425	227	1563
125°	2245	2282	2334	2353	2362	2003
135°	2779	2823	2848	2876	2870	2146
145°	3224	3221	3267	3287	3273	2016
155°	3549	3524	3558	3574	3552	1635
165°	3740	3723	3732	3751	3732	1057
175°	3825	3806	3812	3831	3803	364
180°	3817	3817	3817	3817	3817	

TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.3	4034.3	4034.3	4034.3	4034.3
2.5°	4057.6	4038.3	3995.5	4034.3	4026.8
5°	4034.3	4019.0	3976.2	4007.0	3999.7
7.5°	4007.0	3984.0	3941.2	3972.5	3964.7
10°	3964.7	3937.5	3891.0	3921.8	3910.3
12.5°	3906.3	3883.2	3836.7	3856.0	3848.2
15°	3840.4	3817.3	3766.7	3782.3	3763.0
17.5°	3758.9	3735.9	3685.2	3704.6	3685.2
20°	3669.6	3646.5	3592.2	3603.7	3588.5
22.5°	3580.7	3545.7	3495.0	3495.0	3487.2
25°	3475.7	3444.9	3379.0	3386.5	3379.0
27.5°	3359.2	3332.1	3281.8	3270.3	3251.0
30°	3243.2	3211.9	3153.8	3142.3	3126.7
32.5°	3118.9	3095.9	3033.7	3010.2	2994.6
35°	2998.7	2960.1	2897.8	2874.4	2855.1
37.5°	2862.9	2827.9	2765.8	2738.6	2719.2
40°	2723.4	2692.1	2630.0	2595.4	2579.7
42.5°	2587.6	2556.3	2494.5	2455.4	2432.4
45°	2440.2	2413.0	2354.6	2312.2	2296.6
47.5°	2296.6	2269.5	2207.2	2164.5	2141.4
50°	2145.1	2125.8	2071.4	2017.1	1997.8
52.5°	1997.8	1970.6	1920.4	1877.5	1850.4
55°	1846.7	1823.3	1776.8	1730.2	1710.9
57.5°	1695.3	1675.9	1625.3	1578.8	1563.1
60°	1543.8	1528.6	1474.2	1431.4	1419.9
62.5°	1396.5	1369.3	1330.6	1291.9	1276.3
65°	1245.4	1221.9	1183.3	1148.3	1129.0
67.5°	1090.2	1070.5	1035.9	1008.8	993.2
70°	946.6	930.9	896.0	868.8	853.6
72.5°	799.3	783.6	764.3	737.2	725.6
75°	651.5	644.1	624.3	601.3	609.2
77.5°	519.8	504.2	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	2.6	33.1	55.1	69.2	74.5
92.5°	69.2	58.1	66.3	71.8	74.5
95°	179.4	88.2	107.5	121.7	118.8
97.5°	323.1	96.8	140.7	149.2	151.8
100°	489.0	110.6	157.4	179.4	185.0
102.5°	671.1	665.8	163.0	193.2	201.7
105°	839.6	922.7	168.6	198.8	209.9
107.5°	1035.8	1104.7	174.2	204.3	215.5
110°	1223.7	1281.5	483.4	207.3	218.1

TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1400.5	1450.0	1403.2	212.5	221.0
115°	1588.1	1635.0	1704.2	425.4	226.7
117.5°	1751.1	1806.3	1853.5	1458.2	734.7
120°	1933.5	1974.8	2024.7	2057.9	1684.9
122.5°	2088.0	2132.3	2187.7	2204.1	2207.1
125°	2245.4	2281.5	2334.0	2353.3	2361.5
127.5°	2389.1	2427.8	2469.5	2497.0	2499.6
130°	2524.5	2568.8	2599.0	2629.5	2626.9
132.5°	2662.6	2698.7	2728.8	2753.8	2751.2
135°	2778.7	2823.0	2847.6	2875.5	2869.9
137.5°	2900.1	2933.2	2961.1	2988.6	2980.4
140°	3018.9	3041.1	3071.3	3096.3	3082.5
142.5°	3118.5	3137.9	3173.6	3195.6	3181.8
145°	3223.5	3220.6	3267.4	3286.8	3273.0
147.5°	3314.4	3306.2	3353.1	3366.9	3356.0
150°	3402.9	3383.5	3427.8	3444.2	3430.5
152.5°	3477.3	3455.4	3496.7	3513.4	3494.1
155°	3549.1	3524.5	3557.7	3574.1	3552.2
157.5°	3607.2	3585.2	3610.2	3629.5	3607.2
160°	3657.1	3640.4	3657.1	3673.5	3654.1
162.5°	3701.1	3684.7	3698.4	3717.8	3692.9
165°	3739.7	3723.3	3731.5	3750.9	3731.5
167.5°	3770.3	3753.5	3762.1	3781.4	3756.5
170°	3795.1	3778.5	3784.0	3803.3	3778.5
172.5°	3811.5	3795.1	3800.8	3820.1	3795.1
175°	3825.3	3806.0	3811.5	3831.0	3803.3
177.5°	3831.0	3811.5	3814.6	3833.9	3809.0
180°	3817.2	3817.2	3817.2	3817.2	3817.2

TEST NUMBER: P903897

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.36	13.20	13.33	14.19	15.49	11.91	12.75	12.89	13.74	15.04
	3H	14.01	14.76	15.00	15.76	17.09	13.52	14.27	14.51	15.27	16.60
	4H	14.59	15.31	15.59	16.31	17.64	14.10	14.81	15.10	15.82	17.15
	6H	14.99	15.65	16.00	16.65	18.00	14.49	15.15	15.50	16.15	17.50
	8H	15.09	15.72	16.11	16.74	18.08	14.59	15.22	15.61	16.24	17.58
	12H	15.14	15.73	16.16	16.75	18.12	14.63	15.22	15.65	16.24	17.61
4H	2H	12.81	13.53	13.82	14.53	15.86	12.46	13.17	13.46	14.17	15.50
	3H	14.67	15.27	15.68	16.30	17.64	14.26	14.86	15.28	15.89	17.23
	4H	15.38	15.92	16.40	16.95	18.32	14.95	15.50	15.98	16.52	17.89
	6H	15.89	16.36	16.92	17.40	18.77	15.46	15.93	16.49	16.97	18.34
	8H	16.04	16.47	17.07	17.51	18.89	15.60	16.04	16.63	17.08	18.46
	12H	16.11	16.50	17.16	17.56	18.94	15.66	16.05	16.71	17.11	18.49
8H	4H	15.57	16.01	16.60	17.05	18.43	15.19	15.63	16.23	16.67	18.05
	6H	16.19	16.56	17.25	17.64	19.01	15.81	16.17	16.87	17.25	18.63
	8H	16.41	16.73	17.48	17.80	19.19	16.02	16.34	17.08	17.40	18.80
	12H	16.54	16.82	17.61	17.88	19.32	16.13	16.41	17.20	17.47	18.91
12H	4H	15.55	15.95	16.61	17.00	18.39	15.18	15.58	16.24	16.64	18.02
	6H	16.22	16.54	17.29	17.61	19.00	15.85	16.17	16.91	17.23	18.63
	8H	16.46	16.74	17.53	17.80	19.24	16.08	16.36	17.15	17.42	18.86

END OF REPORT