

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903898

Luminaire Tested: DFN2DIP-SQ3F0-110D120US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903898
REPORT IS A COMBINATION OF REPORTS P900020 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D120US830-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18822.6 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 206
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4910	4910	4910
5°	4915	4829	4861
10°	4863	4731	4701
15°	4793	4571	4455
20°	4701	4353	4154
25°	4607	4108	3863
30°	4482	3858	3495
35°	4359	3589	3171
40°	4234	3311	2800
45°	4089	3004	2464
50°	3939	2693	2136
55°	3782	2362	1821
60°	3600	2016	1497
65°	3390	1665	1346
70°	3136	1337	1216
75°	2815	1172	1103
80°	2353	973	951
85°	1595	633	705

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4089 cd/sqm

TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.1
10°-20°	1102.5	5.9
20°-30°	1547.8	8.2
30°-40°	1687.2	9.0
40°-50°	1550.8	8.2
50°-60°	1217.9	6.5
60°-70°	792.7	4.2
70°-80°	408.1	2.2
80°-90°	114.3	0.6
90°-100°	221.3	1.2
100°-110°	703.3	3.7
110°-120°	1203.6	6.4
120°-130°	1582.9	8.4
130°-140°	1776.7	9.4
140°-150°	1742.3	9.3
150°-160°	1461.5	7.8
160°-170°	969.3	5.1
170°-180°	338.8	1.8
0°-30°	3051.9	16.2
0°-40°	4739.1	25.2
0°-60°	7507.8	39.9
0°-90°	8822.9	46.9
90°-120°	2128.2	11.3
90°-150°	7230.1	38.4
90°-180°	10000.0	53.1
0°-180°	18822.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4239	406
15°	4076	4033	3901	3828	3789	1148
25°	3700	3575	3319	3161	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2013
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	3	39	106	99	102	19
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2801	2789	1724
155°	3154	3163	3173	3188	3178	1452
165°	3432	3428	3428	3450	3435	968
175°	3571	3562	3556	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4285.1	4285.1	4285.1	4285.1	4285.1
2.5°	4304.4	4285.1	4242.3	4281.4	4273.6
5°	4285.1	4265.8	4215.1	4250.1	4238.6
7.5°	4250.1	4227.0	4172.7	4188.0	4168.6
10°	4203.6	4176.4	4099.1	4087.1	4064.1
12.5°	4145.6	4110.6	4005.7	3982.6	3939.8
15°	4075.6	4032.9	3901.2	3827.6	3788.8
17.5°	3994.2	3932.1	3769.1	3683.9	3621.8
20°	3901.2	3823.4	3629.6	3532.9	3447.3
22.5°	3800.4	3711.1	3486.1	3354.4	3296.4
25°	3699.6	3575.3	3319.4	3160.6	3102.2
27.5°	3579.5	3447.3	3164.3	2982.0	2892.8
30°	3451.5	3303.8	2993.6	2796.1	2691.1
32.5°	3327.3	3148.7	2831.0	2598.2	2501.1
35°	3187.8	2989.8	2648.8	2404.4	2318.8
37.5°	3052.0	2838.5	2478.0	2210.2	2113.6
40°	2908.4	2676.0	2299.5	2024.2	1923.4
42.5°	2761.1	2513.0	2121.4	1834.2	1737.5
45°	2606.0	2346.0	1939.1	1663.4	1570.5
47.5°	2458.7	2183.5	1764.6	1488.9	1403.8
50°	2295.8	2020.5	1593.9	1326.1	1245.0
52.5°	2136.6	1845.7	1431.0	1175.1	1101.4
55°	1981.4	1679.0	1260.2	1027.7	954.1
57.5°	1822.7	1512.4	1109.2	892.0	829.8
60°	1659.7	1349.5	950.0	752.5	690.4
62.5°	1500.9	1190.7	814.3	628.3	597.4
65°	1337.9	1023.6	674.8	543.1	531.1
67.5°	1182.9	868.6	543.1	476.8	465.3
70°	1019.9	717.6	449.7	411.0	395.4
72.5°	864.8	577.7	376.1	345.2	337.3
75°	713.4	441.9	310.2	283.0	279.4
77.5°	562.4	314.0	244.4	228.8	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	3.2	38.8	105.7	99.2	102.5
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.9	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.3	543.6	540.3
105°	649.2	657.8	664.3	669.7	669.7
107.5°	787.2	800.2	800.2	802.3	787.2
110°	921.0	938.2	938.2	938.2	929.6

TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1072.0	1065.4
115°	1207.8	1225.1	1219.6	1216.4	1207.8
117.5°	1349.1	1372.8	1357.7	1349.1	1340.5
120°	1491.5	1515.1	1491.5	1491.5	1481.8
122.5°	1620.9	1651.1	1636.0	1627.3	1620.9
125°	1756.7	1783.7	1775.1	1765.4	1762.1
127.5°	1889.4	1922.8	1910.9	1898.0	1889.4
130°	2013.4	2052.2	2046.8	2040.3	2028.4
132.5°	2152.5	2182.7	2184.8	2169.7	2161.2
135°	2272.2	2305.6	2312.2	2308.9	2300.3
137.5°	2405.9	2432.9	2438.3	2436.1	2423.2
140°	2523.5	2550.4	2565.5	2565.5	2553.6
142.5°	2644.3	2671.3	2679.8	2683.0	2671.3
145°	2758.5	2780.1	2797.4	2800.7	2788.8
147.5°	2861.0	2887.9	2901.0	2906.3	2894.5
150°	2966.7	2985.0	2996.9	3006.6	2996.9
152.5°	3060.5	3078.8	3094.0	3105.9	3094.0
155°	3154.3	3163.0	3172.7	3187.8	3178.1
157.5°	3235.3	3241.7	3247.1	3268.6	3253.6
160°	3307.5	3314.0	3317.2	3335.6	3322.6
162.5°	3374.3	3374.3	3377.6	3398.1	3383.0
165°	3431.5	3428.3	3428.3	3449.8	3434.7
167.5°	3483.3	3473.6	3473.6	3495.1	3480.1
170°	3522.1	3513.4	3510.2	3531.8	3513.4
172.5°	3549.0	3540.4	3537.2	3558.8	3540.4
175°	3570.6	3562.0	3555.6	3577.0	3558.8
177.5°	3582.5	3573.8	3567.3	3585.7	3567.3
180°	3577.0	3577.0	3577.0	3577.0	3577.0

TEST NUMBER: P903898

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.34	13.15	13.33	14.14	15.46	8.30	9.11	9.29	10.10	11.42
	3H	14.01	14.73	15.01	15.74	17.08	9.48	10.20	10.48	11.21	12.55
	4H	14.62	15.30	15.63	16.31	17.65	9.93	10.61	10.94	11.62	12.96
	6H	15.03	15.66	16.06	16.67	18.03	10.24	10.87	11.26	11.88	13.24
	8H	15.16	15.75	16.19	16.78	18.14	10.33	10.92	11.36	11.95	13.31
	12H	15.22	15.78	16.25	16.81	18.19	10.37	10.93	11.40	11.96	13.34
4H	2H	12.35	13.03	13.37	14.04	15.39	8.89	9.57	9.91	10.58	11.93
	3H	14.18	14.74	15.20	15.78	17.14	10.23	10.80	11.26	11.84	13.20
	4H	14.86	15.38	15.90	16.41	17.79	10.77	11.29	11.81	12.32	13.70
	6H	15.37	15.82	16.42	16.87	18.25	11.18	11.63	12.23	12.68	14.06
	8H	15.54	15.96	16.59	17.01	18.40	11.31	11.72	12.36	12.77	14.16
	12H	15.64	16.01	16.70	17.07	18.47	11.37	11.74	12.43	12.80	14.20
8H	4H	14.83	15.24	15.87	16.29	17.68	11.05	11.46	12.09	12.51	13.90
	6H	15.39	15.73	16.46	16.82	18.21	11.56	11.90	12.63	12.99	14.38
	8H	15.60	15.90	16.68	16.97	18.38	11.74	12.04	12.82	13.12	14.53
	12H	15.73	16.00	16.81	17.07	18.52	11.86	12.12	12.94	13.19	14.64
12H	4H	14.78	15.15	15.84	16.21	17.61	11.05	11.43	12.12	12.49	13.89
	6H	15.36	15.66	16.44	16.74	18.15	11.61	11.91	12.68	12.98	14.39
	8H	15.58	15.84	16.66	16.91	18.36	11.81	12.07	12.89	13.14	14.59