

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911854

Luminaire Tested: DFN2DIP-SQ3F0-050D090US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911854
REPORT IS A COMBINATION OF REPORTS P899954 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D090US850-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13546.5 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	16	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2626	2626	2626
5°	2628	2583	2600
10°	2601	2530	2514
15°	2563	2445	2383
20°	2514	2328	2222
25°	2464	2197	2066
30°	2397	2063	1869
35°	2331	1919	1696
40°	2265	1771	1498
45°	2187	1606	1318
50°	2107	1440	1142
55°	2023	1263	974
60°	1925	1078	801
65°	1813	890	720
70°	1677	715	650
75°	1506	627	590
80°	1258	520	508
85°	854	339	377

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3175 cd/sqm

TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	1.6
10°-20°	589.6	4.4
20°-30°	827.8	6.1
30°-40°	902.4	6.7
40°-50°	829.4	6.1
50°-60°	651.3	4.8
60°-70°	424.0	3.1
70°-80°	218.2	1.6
80°-90°	64.7	0.5
90°-100°	195.3	1.4
100°-110°	620.6	4.6
110°-120°	1062.1	7.8
120°-130°	1396.8	10.3
130°-140°	1567.9	11.6
140°-150°	1537.5	11.3
150°-160°	1289.7	9.5
160°-170°	855.3	6.3
170°-180°	299.0	2.2
0°-30°	1632.2	12.0
0°-40°	2534.6	18.7
0°-60°	4015.3	29.6
0°-90°	4722.2	34.9
90°-120°	1878.1	13.9
90°-150°	6380.2	47.1
90°-180°	8824.0	65.1
0°-180°	13546.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	3	34	93	88	90	13
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	

TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3

TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7



TEST NUMBER: P911854

CATALOG NUMBER: DFN2DIP-SQ3F0-050D090US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.86	9.58	9.94	10.66	12.13	4.82	5.54	5.90	6.62	8.09
	3H	10.52	11.17	11.62	12.26	13.75	6.00	6.64	7.09	7.73	9.22
	4H	11.13	11.74	12.23	12.82	14.32	6.44	7.05	7.54	8.13	9.63
	6H	11.54	12.10	12.65	13.19	14.70	6.74	7.31	7.86	8.40	9.91
	8H	11.66	12.19	12.77	13.30	14.80	6.83	7.36	7.94	8.47	9.97
	12H	11.72	12.22	12.83	13.32	14.85	6.87	7.37	7.98	8.47	10.00
4H	2H	8.86	9.47	9.97	10.56	12.06	5.40	6.01	6.51	7.10	8.60
	3H	10.68	11.18	11.79	12.30	13.81	6.73	7.24	7.85	8.36	9.87
	4H	11.36	11.83	12.48	12.93	14.46	7.27	7.74	8.39	8.84	10.37
	6H	11.87	12.26	12.99	13.39	14.92	7.68	8.08	8.80	9.21	10.73
	8H	12.04	12.41	13.16	13.53	15.07	7.80	8.17	8.93	9.29	10.83
	12H	12.12	12.46	13.27	13.59	15.14	7.86	8.19	9.00	9.33	10.87
8H	4H	11.32	11.69	12.44	12.81	14.35	7.54	7.91	8.67	9.03	10.57
	6H	11.88	12.18	13.02	13.35	14.88	8.05	8.35	9.19	9.52	11.05
	8H	12.09	12.36	13.24	13.50	15.06	8.23	8.50	9.38	9.64	11.20
	12H	12.22	12.46	13.38	13.59	15.19	8.34	8.58	9.50	9.72	11.31
12H	4H	11.27	11.60	12.41	12.74	14.28	7.54	7.88	8.68	9.01	10.55
	6H	11.85	12.12	13.00	13.26	14.82	8.09	8.36	9.25	9.50	11.06
	8H	12.06	12.30	13.22	13.44	15.03	8.29	8.53	9.45	9.67	11.26