

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906445

Luminaire Tested: DFN2DIP-SQ3F0-060D120US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906445
REPORT IS A COMBINATION OF REPORTS P901529 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-060D120US835-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17820.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 147.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2675	2675	2675
5°	2678	2636	2655
10°	2654	2599	2618
15°	2613	2554	2561
20°	2559	2493	2502
25°	2505	2420	2435
30°	2437	2352	2350
35°	2373	2272	2259
40°	2294	2192	2173
45°	2216	2111	2085
50°	2130	2026	1984
55°	2040	1927	1890
60°	1938	1811	1782
65°	1826	1689	1655
70°	1684	1542	1519
75°	1488	1365	1391
80°	1251	1139	1150
85°	880	754	753

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2774 cd/sqm

TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	1.2
10°-20°	618.3	3.5
20°-30°	908.6	5.1
30°-40°	1055.3	5.9
40°-50°	1054.0	5.9
50°-60°	919.0	5.2
60°-70°	679.4	3.8
70°-80°	384.4	2.2
80°-90°	108.6	0.6
90°-100°	133.5	0.7
100°-110°	497.8	2.8
110°-120°	1320.3	7.4
120°-130°	2189.8	12.3
130°-140°	2326.1	13.1
140°-150°	2161.8	12.1
150°-160°	1738.1	9.8
160°-170°	1119.9	6.3
170°-180°	385.5	2.2
0°-30°	1746.6	9.8
0°-40°	2801.8	15.7
0°-60°	4774.8	26.8
0°-90°	5947.1	33.4
90°-120°	1951.7	11.0
90°-150°	8629.4	48.4
90°-180°	11873.0	66.6
0°-180°	17820.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	103
90°	3	35	58	73	79	16
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	

TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4

TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9

TEST NUMBER: P906445

CATALOG NUMBER: DFN2DIP-SQ3F0-060D120US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.88	9.61	9.97	10.70	12.19	8.44	9.17	9.53	10.26	11.75
	3H	10.53	11.18	11.63	12.28	13.79	10.04	10.69	11.14	11.79	13.30
	4H	11.11	11.73	12.22	12.82	14.34	10.61	11.23	11.72	12.33	13.84
	6H	11.50	12.07	12.61	13.17	14.69	11.00	11.57	12.11	12.67	14.19
	8H	11.60	12.14	12.72	13.25	14.77	11.09	11.64	12.21	12.75	14.27
	12H	11.64	12.15	12.76	13.26	14.81	11.13	11.65	12.25	12.75	14.30
4H	2H	9.33	9.95	10.44	11.04	12.56	8.97	9.59	10.08	10.69	12.20
	3H	11.17	11.69	12.29	12.81	14.34	10.77	11.28	11.89	12.41	13.93
	4H	11.88	12.35	13.00	13.47	15.01	11.45	11.93	12.58	13.04	14.59
	6H	12.38	12.79	13.51	13.92	15.46	11.95	12.36	13.08	13.49	15.03
	8H	12.53	12.91	13.66	14.03	15.59	12.09	12.47	13.22	13.60	15.15
	12H	12.59	12.93	13.74	14.07	15.63	12.14	12.49	13.29	13.63	15.19
8H	4H	12.06	12.44	13.19	13.57	15.12	11.68	12.06	12.81	13.19	14.75
	6H	12.68	12.99	13.83	14.16	15.71	12.30	12.61	13.45	13.78	15.33
	8H	12.90	13.17	14.05	14.32	15.89	12.50	12.78	13.66	13.93	15.50
	12H	13.02	13.26	14.18	14.40	16.01	12.61	12.85	13.77	13.99	15.60
12H	4H	12.04	12.38	13.19	13.52	15.08	11.67	12.01	12.82	13.15	14.71
	6H	12.71	12.98	13.86	14.13	15.70	12.33	12.61	13.49	13.76	15.33
	8H	12.94	13.18	14.10	14.33	15.93	12.56	12.80	13.72	13.94	15.55