

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911914

Luminaire Tested: DFN2DIP-SQ3F0-070D060US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P911914  
REPORT IS A COMBINATION OF REPORTS P899904 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-070D060US850-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12487.3 lumens  
Efficiency: N/A  
Efficacy: 112.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 110.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLLFLL

### Luminous Intensity Polar Plot



TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
| 0   | 108 | 108 | 108 | 108 | 100 | 100 | 100 | 100 | 85 | 85 | 85 | 71 | 71 | 71 | 59 | 59 | 59 |
| 1   | 99  | 95  | 91  | 88  | 92  | 88  | 85  | 82  | 75 | 73 | 71 | 64 | 62 | 60 | 53 | 52 | 51 |
| 2   | 91  | 83  | 77  | 72  | 84  | 78  | 72  | 68  | 67 | 63 | 59 | 56 | 54 | 51 | 47 | 45 | 43 |
| 3   | 83  | 74  | 67  | 61  | 77  | 69  | 62  | 57  | 59 | 54 | 51 | 50 | 47 | 44 | 42 | 40 | 38 |
| 4   | 76  | 66  | 58  | 52  | 70  | 61  | 54  | 49  | 53 | 48 | 44 | 45 | 41 | 38 | 38 | 35 | 33 |
| 5   | 70  | 59  | 51  | 45  | 65  | 55  | 48  | 43  | 48 | 42 | 38 | 41 | 37 | 33 | 34 | 31 | 29 |
| 6   | 65  | 53  | 45  | 39  | 60  | 50  | 42  | 37  | 43 | 38 | 33 | 37 | 33 | 30 | 31 | 28 | 26 |
| 7   | 60  | 48  | 40  | 35  | 56  | 45  | 38  | 33  | 39 | 34 | 30 | 34 | 30 | 26 | 29 | 26 | 23 |
| 8   | 56  | 44  | 36  | 31  | 52  | 41  | 34  | 29  | 36 | 30 | 27 | 31 | 27 | 24 | 27 | 23 | 21 |
| 9   | 52  | 40  | 33  | 28  | 48  | 38  | 31  | 26  | 33 | 28 | 24 | 29 | 24 | 21 | 25 | 21 | 19 |
| 10  | 49  | 37  | 30  | 25  | 45  | 35  | 28  | 24  | 31 | 25 | 22 | 27 | 22 | 19 | 23 | 20 | 17 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 3676 | 3676 | 3676 |
| 5°  | 3680 | 3615 | 3640 |
| 10° | 3641 | 3542 | 3520 |
| 15° | 3588 | 3423 | 3336 |
| 20° | 3520 | 3259 | 3110 |
| 25° | 3450 | 3076 | 2893 |
| 30° | 3356 | 2889 | 2617 |
| 35° | 3264 | 2687 | 2374 |
| 40° | 3170 | 2479 | 2097 |
| 45° | 3062 | 2249 | 1845 |
| 50° | 2950 | 2016 | 1600 |
| 55° | 2832 | 1768 | 1364 |
| 60° | 2695 | 1509 | 1121 |
| 65° | 2538 | 1247 | 1008 |
| 70° | 2348 | 1001 | 910  |
| 75° | 2108 | 877  | 826  |
| 80° | 1762 | 729  | 712  |
| 85° | 1195 | 474  | 528  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3062 cd/sqm

TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLLFLL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 300.7   | 2.4       |
| 10°-20°   | 825.5   | 6.6       |
| 20°-30°   | 1158.9  | 9.3       |
| 30°-40°   | 1263.3  | 10.1      |
| 40°-50°   | 1161.1  | 9.3       |
| 50°-60°   | 911.9   | 7.3       |
| 60°-70°   | 593.5   | 4.8       |
| 70°-80°   | 305.5   | 2.4       |
| 80°-90°   | 84.0    | 0.7       |
| 90°-100°  | 130.2   | 1.0       |
| 100°-110° | 413.7   | 3.3       |
| 110°-120° | 708.0   | 5.7       |
| 120°-130° | 931.2   | 7.5       |
| 130°-140° | 1045.3  | 8.4       |
| 140°-150° | 1025.0  | 8.2       |
| 150°-160° | 859.8   | 6.9       |
| 160°-170° | 570.2   | 4.6       |
| 170°-180° | 199.3   | 1.6       |
| 0°-30°    | 2285.1  | 18.3      |
| 0°-40°    | 3548.4  | 28.4      |
| 0°-60°    | 5621.4  | 45.0      |
| 0°-90°    | 6604.5  | 52.9      |
| 90°-120°  | 1252.0  | 10.0      |
| 90°-150°  | 4253.5  | 34.1      |
| 90°-180°  | 5883.0  | 47.1      |
| 0°-180°   | 12487.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 3208 | 3208  | 3208 | 3208  | 3208 |      |
| 5°   | 3208 | 3194  | 3156 | 3182  | 3174 | 304  |
| 15°  | 3052 | 3020  | 2921 | 2866  | 2837 | 860  |
| 25°  | 2770 | 2677  | 2485 | 2366  | 2323 | 1274 |
| 35°  | 2387 | 2239  | 1983 | 1800  | 1736 | 1494 |
| 45°  | 1951 | 1756  | 1452 | 1246  | 1176 | 1507 |
| 55°  | 1484 | 1257  | 944  | 770   | 714  | 1326 |
| 65°  | 1002 | 766   | 505  | 407   | 398  | 993  |
| 75°  | 534  | 331   | 232  | 212   | 209  | 565  |
| 85°  | 125  | 64    | 55   | 55    | 55   | 143  |
| 90°  | 2    | 23    | 62   | 58    | 60   | 12   |
| 95°  | 93   | 110   | 114  | 114   | 110  | 103  |
| 105° | 382  | 387   | 391  | 394   | 394  | 403  |
| 115° | 710  | 721   | 718  | 716   | 710  | 703  |
| 125° | 1034 | 1049  | 1044 | 1039  | 1037 | 924  |
| 135° | 1337 | 1356  | 1360 | 1358  | 1353 | 1033 |
| 145° | 1623 | 1636  | 1646 | 1648  | 1641 | 1014 |
| 155° | 1856 | 1861  | 1866 | 1875  | 1870 | 854  |
| 165° | 2019 | 2017  | 2017 | 2030  | 2021 | 569  |
| 175° | 2101 | 2096  | 2092 | 2104  | 2094 | 200  |
| 180° | 2104 | 2104  | 2104 | 2104  | 2104 |      |

TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLFL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 3208.4 | 3208.4 | 3208.4 | 3208.4 | 3208.4 |
| 2.5°   | 3222.9 | 3208.4 | 3176.4 | 3205.7 | 3199.8 |
| 5°     | 3208.4 | 3193.9 | 3156.1 | 3182.3 | 3173.6 |
| 7.5°   | 3182.3 | 3165.0 | 3124.4 | 3135.7 | 3121.3 |
| 10°    | 3147.5 | 3127.2 | 3069.2 | 3060.3 | 3043.0 |
| 12.5°  | 3104.0 | 3077.8 | 2999.3 | 2982.0 | 2949.9 |
| 15°    | 3051.6 | 3019.6 | 2921.0 | 2865.9 | 2836.9 |
| 17.5°  | 2990.6 | 2944.2 | 2822.2 | 2758.3 | 2711.8 |
| 20°    | 2921.0 | 2862.8 | 2717.7 | 2645.3 | 2581.2 |
| 22.5°  | 2845.6 | 2778.7 | 2610.1 | 2511.6 | 2468.2 |
| 25°    | 2770.1 | 2677.0 | 2485.4 | 2366.5 | 2322.8 |
| 27.5°  | 2680.1 | 2581.2 | 2369.3 | 2232.9 | 2166.0 |
| 30°    | 2584.3 | 2473.7 | 2241.4 | 2093.6 | 2015.1 |
| 32.5°  | 2491.3 | 2357.6 | 2119.7 | 1945.4 | 1872.7 |
| 35°    | 2386.8 | 2238.6 | 1983.3 | 1800.4 | 1736.3 |
| 37.5°  | 2285.2 | 2125.3 | 1855.5 | 1654.8 | 1582.5 |
| 40°    | 2177.6 | 2003.6 | 1721.7 | 1515.7 | 1440.1 |
| 42.5°  | 2067.4 | 1881.6 | 1588.3 | 1373.3 | 1301.0 |
| 45°    | 1951.3 | 1756.5 | 1451.9 | 1245.5 | 1175.9 |
| 47.5°  | 1840.9 | 1634.9 | 1321.3 | 1114.9 | 1051.1 |
| 50°    | 1719.0 | 1512.9 | 1193.4 | 992.9  | 932.2  |
| 52.5°  | 1599.7 | 1381.9 | 1071.4 | 879.8  | 824.7  |
| 55°    | 1483.6 | 1257.2 | 943.5  | 769.5  | 714.4  |
| 57.5°  | 1364.7 | 1132.4 | 830.5  | 667.8  | 621.4  |
| 60°    | 1242.7 | 1010.4 | 711.3  | 563.5  | 516.9  |
| 62.5°  | 1123.7 | 891.5  | 609.6  | 470.4  | 447.3  |
| 65°    | 1001.8 | 766.4  | 505.3  | 406.7  | 397.7  |
| 67.5°  | 885.6  | 650.3  | 406.7  | 357.0  | 348.4  |
| 70°    | 763.7  | 537.2  | 336.7  | 307.7  | 296.0  |
| 72.5°  | 647.5  | 432.5  | 281.6  | 258.5  | 252.6  |
| 75°    | 534.2  | 330.8  | 232.2  | 211.9  | 209.2  |
| 77.5°  | 421.1  | 235.0  | 183.0  | 171.2  | 165.5  |
| 80°    | 316.4  | 168.5  | 139.3  | 127.9  | 127.9  |
| 82.5°  | 220.6  | 113.3  | 95.8   | 89.9   | 89.9   |
| 85°    | 124.8  | 63.8   | 55.1   | 55.1   | 55.1   |
| 87.5°  | 46.5   | 23.1   | 23.1   | 20.3   | 20.3   |
| 90°    | 1.9    | 22.8   | 62.2   | 58.3   | 60.2   |
| 92.5°  | 39.4   | 53.3   | 55.2   | 57.1   | 57.1   |
| 95°    | 92.6   | 110.3  | 113.6  | 113.6  | 110.3  |
| 97.5°  | 154.2  | 170.7  | 177.7  | 177.7  | 177.7  |
| 100°   | 225.2  | 239.8  | 244.9  | 244.9  | 243.0  |
| 102.5° | 300.1  | 310.9  | 317.8  | 319.7  | 317.8  |
| 105°   | 381.9  | 387.0  | 390.8  | 394.0  | 394.0  |
| 107.5° | 463.1  | 470.8  | 470.8  | 472.0  | 463.1  |
| 110°   | 541.9  | 551.9  | 551.9  | 551.9  | 546.8  |

TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLLFLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 626.8  | 637.6  | 635.7  | 630.6  | 626.8  |
| 115°   | 710.5  | 720.7  | 717.5  | 715.6  | 710.5  |
| 117.5° | 793.7  | 807.7  | 798.7  | 793.7  | 788.6  |
| 120°   | 877.4  | 891.4  | 877.4  | 877.4  | 871.7  |
| 122.5° | 953.5  | 971.3  | 962.4  | 957.4  | 953.5  |
| 125°   | 1033.5 | 1049.3 | 1044.2 | 1038.6 | 1036.7 |
| 127.5° | 1111.6 | 1131.2 | 1124.2 | 1116.7 | 1111.6 |
| 130°   | 1184.5 | 1207.4 | 1204.2 | 1200.4 | 1193.4 |
| 132.5° | 1266.4 | 1284.1 | 1285.3 | 1276.5 | 1271.4 |
| 135°   | 1336.8 | 1356.4 | 1360.2 | 1358.3 | 1353.2 |
| 137.5° | 1415.4 | 1431.3 | 1434.5 | 1433.2 | 1425.6 |
| 140°   | 1484.6 | 1500.5 | 1509.3 | 1509.3 | 1502.4 |
| 142.5° | 1555.6 | 1571.5 | 1576.6 | 1578.4 | 1571.5 |
| 145°   | 1622.9 | 1635.6 | 1645.8 | 1647.6 | 1640.7 |
| 147.5° | 1683.1 | 1699.0 | 1706.6 | 1709.7 | 1702.8 |
| 150°   | 1745.3 | 1756.1 | 1763.1 | 1768.7 | 1763.1 |
| 152.5° | 1800.5 | 1811.3 | 1820.2 | 1827.2 | 1820.2 |
| 155°   | 1855.7 | 1860.8 | 1866.4 | 1875.4 | 1869.7 |
| 157.5° | 1903.3 | 1907.1 | 1910.3 | 1923.0 | 1914.1 |
| 160°   | 1945.9 | 1949.6 | 1951.5 | 1962.3 | 1954.7 |
| 162.5° | 1985.1 | 1985.1 | 1987.0 | 1999.1 | 1990.2 |
| 165°   | 2018.7 | 2016.8 | 2016.8 | 2029.6 | 2020.7 |
| 167.5° | 2049.2 | 2043.6 | 2043.6 | 2056.2 | 2047.3 |
| 170°   | 2072.1 | 2067.0 | 2065.1 | 2077.7 | 2067.0 |
| 172.5° | 2087.9 | 2082.8 | 2080.9 | 2093.6 | 2082.8 |
| 175°   | 2100.6 | 2095.6 | 2091.7 | 2104.4 | 2093.6 |
| 177.5° | 2107.5 | 2102.6 | 2098.7 | 2109.4 | 2098.7 |
| 180°   | 2104.4 | 2104.4 | 2104.4 | 2104.4 | 2104.4 |

TEST NUMBER: P911914

CATALOG NUMBER: DFN2DIP-SQ3F0-070D060US850-RLFL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 11.90            | 12.76 | 12.84 | 13.71 | 14.94 | 7.86           | 8.72  | 8.80  | 9.67  | 10.90 |
|                 | 3H   | 13.58            | 14.34 | 14.53 | 15.30 | 16.56 | 9.05           | 9.81  | 10.00 | 10.77 | 12.03 |
|                 | 4H   | 14.18            | 14.90 | 15.15 | 15.87 | 17.13 | 9.49           | 10.21 | 10.46 | 11.18 | 12.44 |
|                 | 6H   | 14.60            | 15.27 | 15.58 | 16.24 | 17.51 | 9.81           | 10.47 | 10.78 | 11.44 | 12.72 |
|                 | 8H   | 14.73            | 15.36 | 15.71 | 16.35 | 17.62 | 9.90           | 10.53 | 10.88 | 11.52 | 12.79 |
|                 | 12H  | 14.79            | 15.39 | 15.77 | 16.37 | 17.67 | 9.94           | 10.54 | 10.93 | 11.52 | 12.82 |
| 4H              | 2H   | 11.92            | 12.64 | 12.89 | 13.61 | 14.87 | 8.46           | 9.18  | 9.43  | 10.14 | 11.41 |
|                 | 3H   | 13.75            | 14.35 | 14.73 | 15.34 | 16.62 | 9.80           | 10.40 | 10.78 | 11.40 | 12.68 |
|                 | 4H   | 14.44            | 14.98 | 15.42 | 15.97 | 17.27 | 10.35          | 10.89 | 11.33 | 11.88 | 13.18 |
|                 | 6H   | 14.95            | 15.42 | 15.95 | 16.43 | 17.73 | 10.76          | 11.23 | 11.76 | 12.24 | 13.54 |
|                 | 8H   | 15.12            | 15.56 | 16.12 | 16.56 | 17.88 | 10.89          | 11.32 | 11.89 | 12.33 | 13.64 |
|                 | 12H  | 15.21            | 15.61 | 16.23 | 16.63 | 17.95 | 10.95          | 11.34 | 11.97 | 12.36 | 13.68 |
| 8H              | 4H   | 14.40            | 14.84 | 15.41 | 15.85 | 17.16 | 10.63          | 11.06 | 11.63 | 12.07 | 13.38 |
|                 | 6H   | 14.97            | 15.33 | 15.99 | 16.37 | 17.69 | 11.14          | 11.50 | 12.16 | 12.55 | 13.86 |
|                 | 8H   | 15.18            | 15.50 | 16.21 | 16.53 | 17.86 | 11.32          | 11.64 | 12.36 | 12.67 | 14.01 |
|                 | 12H  | 15.31            | 15.60 | 16.35 | 16.62 | 18.00 | 11.44          | 11.72 | 12.47 | 12.74 | 14.12 |
| 12H             | 4H   | 14.36            | 14.75 | 15.38 | 15.77 | 17.09 | 10.63          | 11.03 | 11.65 | 12.05 | 13.37 |
|                 | 6H   | 14.94            | 15.26 | 15.97 | 16.29 | 17.62 | 11.18          | 11.50 | 12.22 | 12.54 | 13.87 |
|                 | 8H   | 15.16            | 15.44 | 16.20 | 16.47 | 17.84 | 11.39          | 11.67 | 12.43 | 12.70 | 14.07 |