

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911926

Luminaire Tested: DFN2DIP-SQ3F0-070D090US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911926
REPORT IS A COMBINATION OF REPORTS P899958 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D090US850-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15431.7 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	46	41	44	39	35	36	32	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3676	3676	3676
5°	3680	3615	3640
10°	3641	3542	3520
15°	3588	3423	3336
20°	3520	3259	3110
25°	3450	3076	2893
30°	3356	2889	2617
35°	3264	2687	2374
40°	3170	2479	2097
45°	3062	2249	1845
50°	2950	2016	1600
55°	2832	1768	1364
60°	2695	1509	1121
65°	2538	1247	1008
70°	2348	1001	910
75°	2108	877	826
80°	1762	729	712
85°	1195	474	528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3175 cd/sqm

TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	1.9
10°-20°	825.5	5.3
20°-30°	1158.9	7.5
30°-40°	1263.3	8.2
40°-50°	1161.1	7.5
50°-60°	911.9	5.9
60°-70°	593.5	3.8
70°-80°	305.5	2.0
80°-90°	87.0	0.6
90°-100°	195.3	1.3
100°-110°	620.6	4.0
110°-120°	1062.1	6.9
120°-130°	1396.8	9.1
130°-140°	1567.9	10.2
140°-150°	1537.5	10.0
150°-160°	1289.7	8.4
160°-170°	855.3	5.5
170°-180°	299.0	1.9
0°-30°	2285.1	14.8
0°-40°	3548.4	23.0
0°-60°	5621.4	36.4
0°-90°	6607.5	42.8
90°-120°	1878.1	12.2
90°-150°	6380.2	41.3
90°-180°	8824.0	57.2
0°-180°	15431.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	143
90°	3	34	93	88	90	15
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	

TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3

TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7

TEST NUMBER: P911926

CATALOG NUMBER: DFN2DIP-SQ3F0-070D090US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.92	11.70	11.95	12.73	14.10	6.88	7.66	7.91	8.69	10.06
	3H	12.59	13.29	13.63	14.32	15.71	8.06	8.76	9.10	9.79	11.18
	4H	13.20	13.85	14.24	14.89	16.29	8.51	9.16	9.55	10.20	11.60
	6H	13.61	14.21	14.67	15.26	16.67	8.82	9.42	9.87	10.46	11.88
	8H	13.73	14.31	14.79	15.37	16.77	8.90	9.48	9.96	10.54	11.94
	12H	13.79	14.34	14.86	15.39	16.82	8.94	9.49	10.01	10.54	11.97
4H	2H	10.93	11.59	11.99	12.63	14.03	7.47	8.13	8.52	9.17	10.57
	3H	12.75	13.30	13.81	14.36	15.78	8.81	9.35	9.87	10.42	11.83
	4H	13.44	13.94	14.50	15.00	16.43	9.35	9.85	10.41	10.91	12.34
	6H	13.95	14.38	15.02	15.46	16.89	9.76	10.19	10.83	11.27	12.70
	8H	14.12	14.52	15.19	15.59	17.04	9.88	10.28	10.96	11.36	12.80
	12H	14.21	14.57	15.30	15.66	17.11	9.94	10.30	11.03	11.39	12.84
8H	4H	13.40	13.80	14.48	14.87	16.32	9.62	10.02	10.70	11.10	12.54
	6H	13.96	14.29	15.06	15.40	16.85	10.13	10.46	11.23	11.58	13.02
	8H	14.17	14.46	15.28	15.56	17.02	10.32	10.61	11.42	11.70	13.17
	12H	14.31	14.56	15.41	15.65	17.15	10.43	10.68	11.53	11.77	13.28
12H	4H	13.35	13.71	14.44	14.80	16.25	9.62	9.99	10.72	11.07	12.52
	6H	13.93	14.22	15.04	15.32	16.78	10.18	10.47	11.28	11.57	13.03
	8H	14.15	14.40	15.26	15.50	17.00	10.38	10.64	11.49	11.73	13.23

END OF REPORT