

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906591

Luminaire Tested: DFN2DIP-SQ3F0-100D120US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906591
REPORT IS A COMBINATION OF REPORTS P901538 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D120US835-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20380.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906591
CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906591

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	49	49	49	42
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42	42	42	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	36	36	36	31
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31	31	31	31	27
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	27	27	27	23
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	24	24	24	20
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	21	21	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	19	19	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	17	17	17	15
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	15	15	15	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4736	4736	4736
5°	4740	4657	4689
10°	4690	4563	4535
15°	4623	4409	4297
20°	4534	4198	4007
25°	4444	3962	3726
30°	4323	3721	3371
35°	4205	3462	3058
40°	4084	3194	2701
45°	3944	2897	2377
50°	3799	2597	2060
55°	3648	2278	1756
60°	3472	1944	1444
65°	3270	1606	1298
70°	3024	1289	1173
75°	2716	1130	1063
80°	2269	938	917
85°	1539	611	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3944 cd/sqm



TEST NUMBER: P906591

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	1.9
10°-20°	1063.3	5.2
20°-30°	1492.9	7.3
30°-40°	1627.4	8.0
40°-50°	1495.7	7.3
50°-60°	1174.7	5.8
60°-70°	764.6	3.8
70°-80°	393.6	1.9
80°-90°	107.6	0.5
90°-100°	133.5	0.7
100°-110°	497.8	2.4
110°-120°	1320.3	6.5
120°-130°	2189.8	10.7
130°-140°	2326.1	11.4
140°-150°	2161.8	10.6
150°-160°	1738.1	8.5
160°-170°	1119.9	5.5
170°-180°	385.5	1.9
0°-30°	2943.6	14.4
0°-40°	4571.0	22.4
0°-60°	7241.3	35.5
0°-90°	8507.1	41.7
90°-120°	1951.7	9.6
90°-150°	8629.4	42.3
90°-180°	11873.0	58.3
0°-180°	20380.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	3	35	58	73	79	19
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	



TEST NUMBER: P906591

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4



TEST NUMBER: P906591

CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9



TEST NUMBER: P906591
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D120US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	12.46	12.72	13.49	14.88	7.65	8.42	8.68	9.45	10.84
	3H	13.36	14.05	14.40	15.09	16.50	8.83	9.52	9.87	10.56	11.97
	4H	13.96	14.61	15.02	15.66	17.07	9.27	9.92	10.33	10.97	12.38
	6H	14.38	14.98	15.44	16.03	17.45	9.59	10.18	10.65	11.23	12.66
	8H	14.50	15.07	15.57	16.13	17.56	9.67	10.24	10.74	11.30	12.73
	12H	14.56	15.10	15.63	16.16	17.60	9.71	10.25	10.78	11.31	12.75
4H	2H	11.70	12.35	12.76	13.40	14.81	8.24	8.89	9.30	9.93	11.35
	3H	13.52	14.06	14.59	15.13	16.56	9.58	10.12	10.64	11.19	12.62
	4H	14.21	14.70	15.28	15.76	17.21	10.12	10.61	11.19	11.67	13.12
	6H	14.71	15.14	15.79	16.22	17.67	10.53	10.95	11.61	12.04	13.48
	8H	14.88	15.28	15.97	16.36	17.82	10.65	11.04	11.73	12.12	13.58
	12H	14.97	15.33	16.07	16.42	17.89	10.71	11.07	11.81	12.16	13.62
8H	4H	14.17	14.56	15.25	15.64	17.10	10.39	10.78	11.47	11.86	13.32
	6H	14.73	15.05	15.83	16.17	17.63	10.90	11.22	12.00	12.34	13.80
	8H	14.94	15.23	16.05	16.33	17.80	11.08	11.37	12.19	12.47	13.95
	12H	15.07	15.32	16.19	16.42	17.94	11.19	11.44	12.31	12.54	14.06
12H	4H	14.12	14.47	15.22	15.57	17.03	10.39	10.75	11.49	11.84	13.30
	6H	14.70	14.99	15.81	16.09	17.57	10.94	11.23	12.05	12.33	13.81
	8H	14.91	15.17	16.03	16.27	17.78	11.15	11.40	12.26	12.50	14.01