

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906594

Luminaire Tested: DFN2DIP-SQ3F0-110D040US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906594
REPORT IS A COMBINATION OF REPORTS P899876 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D040US835-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12890.0 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 142.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906594
CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P906594

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73
1	104	99	96	92	98	94	91	88	85	83	80	77	75	73	69	68	66	66	66	66	63
2	95	88	82	77	90	83	78	74	76	71	68	68	65	62	62	59	57	57	57	57	54
3	87	78	70	65	82	74	68	62	67	62	58	61	57	53	55	52	49	49	49	49	46
4	80	69	61	55	76	66	59	54	60	55	50	55	50	47	50	46	43	43	43	43	40
5	74	62	54	48	70	60	52	47	54	48	44	50	45	41	45	41	38	38	38	38	35
6	68	56	48	42	65	54	47	41	49	43	39	45	40	36	41	37	34	34	34	34	31
7	64	51	43	38	60	49	42	37	45	39	34	41	36	32	38	34	30	30	30	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	28	28	28	28	25
9	55	43	35	30	53	41	34	30	38	32	28	35	30	27	33	28	25	25	25	25	23
10	52	40	32	28	49	38	31	27	35	30	26	33	28	24	30	26	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5209	5209	5209
5°	5214	5123	5158
10°	5159	5019	4988
15°	5085	4850	4727
20°	4988	4618	4407
25°	4888	4359	4099
30°	4755	4093	3708
35°	4625	3808	3364
40°	4492	3513	2971
45°	4339	3187	2615
50°	4179	2857	2266
55°	4012	2506	1932
60°	3819	2139	1589
65°	3597	1766	1428
70°	3327	1419	1290
75°	2987	1243	1170
80°	2496	1032	1009
85°	1693	672	748

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4339 cd/sqm



TEST NUMBER: P906594

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	3.3
10°-20°	1169.7	9.1
20°-30°	1642.2	12.7
30°-40°	1790.1	13.9
40°-50°	1645.3	12.8
50°-60°	1292.1	10.0
60°-70°	841.1	6.5
70°-80°	432.9	3.4
80°-90°	114.1	0.9
90°-100°	78.3	0.6
100°-110°	248.7	1.9
110°-120°	425.6	3.3
120°-130°	559.8	4.3
130°-140°	628.3	4.9
140°-150°	616.2	4.8
150°-160°	516.9	4.0
160°-170°	342.8	2.7
170°-180°	119.8	0.9
0°-30°	3238.0	25.1
0°-40°	5028.1	39.0
0°-60°	7965.5	61.8
0°-90°	9353.6	72.6
90°-120°	752.7	5.8
90°-150°	2556.9	19.8
90°-180°	3536.0	27.4
0°-180°	12890.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	1	14	37	35	36	13
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P906594

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8



TEST NUMBER: P906594

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0



TEST NUMBER: P906594
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.74	15.79	15.48	16.55	17.46	10.70	11.75	11.44	12.51	13.42
	3H	16.43	17.37	17.18	18.14	19.08	11.90	12.84	12.65	13.61	14.55
	4H	17.04	17.93	17.82	18.71	19.67	12.35	13.24	13.13	14.02	14.98
	6H	17.47	18.29	18.26	19.08	20.05	12.68	13.50	13.47	14.29	15.25
	8H	17.60	18.38	18.40	19.19	20.16	12.77	13.55	13.57	14.36	15.33
	12H	17.67	18.41	18.47	19.21	20.21	12.82	13.57	13.62	14.36	15.36
4H	2H	14.78	15.67	15.56	16.45	17.40	11.32	12.21	12.10	12.99	13.94
	3H	16.63	17.36	17.42	18.18	19.15	12.68	13.42	13.47	14.23	15.20
	4H	17.32	17.99	18.13	18.81	19.81	13.23	13.90	14.04	14.72	15.72
	6H	17.84	18.42	18.67	19.26	20.27	13.66	14.24	14.48	15.07	16.08
	8H	18.02	18.56	18.85	19.40	20.41	13.79	14.33	14.61	15.16	16.18
	12H	18.12	18.61	18.97	19.46	20.49	13.86	14.34	14.70	15.20	16.22
8H	4H	17.30	17.85	18.13	18.68	19.70	13.53	14.07	14.35	14.90	15.92
	6H	17.87	18.32	18.73	19.20	20.21	14.04	14.49	14.90	15.37	16.38
	8H	18.09	18.48	18.95	19.36	20.39	14.23	14.63	15.10	15.50	16.53
	12H	18.23	18.58	19.10	19.44	20.53	14.35	14.70	15.22	15.57	16.66
12H	4H	17.27	17.75	18.11	18.61	19.63	13.54	14.03	14.39	14.88	15.90
	6H	17.85	18.25	18.71	19.12	20.15	14.09	14.49	14.96	15.36	16.40
	8H	18.08	18.43	18.94	19.29	20.38	14.31	14.66	15.17	15.52	16.61