

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906603

Luminaire Tested: DFN2DIP-SQ3F0-110D060US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906603
REPORT IS A COMBINATION OF REPORTS P901432 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D060US835-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15290.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	60	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	61	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5209	5209	5209
5°	5214	5123	5158
10°	5159	5019	4988
15°	5085	4850	4727
20°	4988	4618	4407
25°	4888	4359	4099
30°	4755	4093	3708
35°	4625	3808	3364
40°	4492	3513	2971
45°	4339	3187	2615
50°	4179	2857	2266
55°	4012	2506	1932
60°	3819	2139	1589
65°	3597	1766	1428
70°	3327	1419	1290
75°	2987	1243	1170
80°	2496	1032	1009
85°	1693	672	748

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4339 cd/sqm

TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.8
10°-20°	1169.7	7.7
20°-30°	1642.2	10.7
30°-40°	1790.1	11.7
40°-50°	1645.3	10.8
50°-60°	1292.1	8.5
60°-70°	841.1	5.5
70°-80°	432.9	2.8
80°-90°	114.1	0.7
90°-100°	66.8	0.4
100°-110°	248.9	1.6
110°-120°	660.2	4.3
120°-130°	1094.9	7.2
130°-140°	1163.0	7.6
140°-150°	1080.9	7.1
150°-160°	869.0	5.7
160°-170°	560.0	3.7
170°-180°	192.7	1.3
0°-30°	3238.0	21.2
0°-40°	5028.1	32.9
0°-60°	7965.5	52.1
0°-90°	9353.6	61.2
90°-120°	975.8	6.4
90°-150°	4314.7	28.2
90°-180°	5936.0	38.8
0°-180°	15290.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	1	18	29	37	40	14
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	

TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7

TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9

TEST NUMBER: P906603

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.83	14.76	14.69	15.64	16.75	9.79	10.72	10.65	11.60	12.71
	3H	15.51	16.34	16.39	17.23	18.36	10.98	11.81	11.86	12.70	13.83
	4H	16.12	16.91	17.01	17.80	18.94	11.43	12.22	12.32	13.11	14.25
	6H	16.54	17.27	17.45	18.17	19.32	11.75	12.48	12.65	13.38	14.53
	8H	16.67	17.36	17.58	18.28	19.43	11.84	12.53	12.75	13.45	14.60
	12H	16.74	17.39	17.65	18.30	19.48	11.89	12.54	12.80	13.45	14.63
4H	2H	13.86	14.65	14.76	15.54	16.68	10.40	11.18	11.29	12.08	13.22
	3H	15.69	16.34	16.60	17.27	18.43	11.75	12.40	12.66	13.33	14.48
	4H	16.39	16.98	17.30	17.90	19.08	12.30	12.89	13.21	13.81	14.99
	6H	16.90	17.41	17.83	18.36	19.54	12.71	13.22	13.64	14.17	15.35
	8H	17.08	17.55	18.01	18.49	19.69	12.84	13.32	13.77	14.26	15.45
	12H	17.17	17.60	18.12	18.56	19.76	12.91	13.34	13.86	14.29	15.50
8H	4H	16.36	16.84	17.29	17.78	18.97	12.58	13.06	13.51	14.00	15.19
	6H	16.92	17.32	17.88	18.30	19.49	13.09	13.49	14.05	14.47	15.67
	8H	17.14	17.49	18.11	18.46	19.67	13.28	13.63	14.25	14.60	15.81
	12H	17.28	17.58	18.25	18.55	19.81	13.40	13.71	14.37	14.67	15.93
12H	4H	16.31	16.74	17.27	17.70	18.90	12.59	13.02	13.54	13.98	15.18
	6H	16.90	17.25	17.87	18.22	19.43	13.14	13.49	14.11	14.46	15.68
	8H	17.12	17.43	18.09	18.39	19.65	13.35	13.66	14.32	14.62	15.89

END OF REPORT