

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912012

Luminaire Tested: DFN2DIP-SQ3F0-100D040US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912012
REPORT IS A COMBINATION OF REPORTS P899873 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D040US850-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14904.9 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 128.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78
1	103	99	95	91	98	94	90	87	85	82	80	77	74	72	69	67	66
2	94	86	80	74	89	82	76	71	74	70	66	67	64	61	61	58	55
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47
4	79	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36
6	67	54	46	40	63	52	44	38	47	41	36	43	38	34	39	35	31
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	36	31	28
8	57	45	37	31	54	43	35	30	39	33	28	36	31	27	33	29	25
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4944	4944	4944
5°	4949	4872	4907
10°	4906	4803	4839
15°	4831	4721	4733
20°	4730	4608	4625
25°	4630	4473	4501
30°	4505	4348	4343
35°	4386	4200	4176
40°	4241	4051	4017
45°	4096	3901	3855
50°	3937	3744	3667
55°	3770	3562	3493
60°	3582	3346	3294
65°	3375	3123	3060
70°	3113	2850	2807
75°	2750	2522	2571
80°	2311	2104	2125
85°	1627	1394	1391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4096 cd/sqm

TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	2.7
10°-20°	1142.7	7.7
20°-30°	1679.4	11.3
30°-40°	1950.5	13.1
40°-50°	1948.1	13.1
50°-60°	1698.7	11.4
60°-70°	1255.7	8.4
70°-80°	710.4	4.8
80°-90°	191.5	1.3
90°-100°	86.8	0.6
100°-110°	275.8	1.9
110°-120°	472.0	3.2
120°-130°	620.8	4.2
130°-140°	696.8	4.7
140°-150°	683.3	4.6
150°-160°	573.2	3.8
160°-170°	380.1	2.6
170°-180°	132.9	0.9
0°-30°	3228.3	21.7
0°-40°	5178.7	34.7
0°-60°	8825.5	59.2
0°-90°	10983.1	73.7
90°-120°	834.7	5.6
90°-150°	2835.6	19.0
90°-180°	3922.0	26.3
0°-180°	14904.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4315	4315	4315	4315	4315	
5°	4315	4299	4253	4286	4278	410
15°	4108	4083	4029	4046	4025	1157
25°	3718	3685	3614	3622	3614	1711
35°	3208	3166	3100	3075	3054	2003
45°	2610	2581	2518	2473	2456	2014
55°	1975	1950	1900	1851	1830	1766
65°	1332	1307	1266	1228	1208	1317
75°	697	689	668	643	652	744
85°	170	166	162	149	145	190
90°	1	15	42	39	40	14
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4315.2	4315.2	4315.2	4315.2	4315.2
2.5°	4340.3	4319.6	4273.8	4315.2	4307.2
5°	4315.2	4298.9	4253.1	4286.2	4278.2
7.5°	4286.2	4261.4	4215.6	4249.1	4240.8
10°	4240.8	4211.8	4162.0	4195.0	4182.7
12.5°	4178.3	4153.6	4103.9	4124.6	4116.2
15°	4107.8	4083.2	4029.0	4045.7	4025.1
17.5°	4020.7	3996.1	3941.8	3962.6	3941.8
20°	3925.1	3900.5	3842.4	3854.7	3838.4
22.5°	3830.0	3792.7	3738.4	3738.4	3730.1
25°	3717.8	3684.8	3614.3	3622.2	3614.3
27.5°	3593.2	3564.1	3510.4	3498.1	3477.4
30°	3469.1	3435.6	3373.5	3361.2	3344.4
32.5°	3336.1	3311.5	3244.9	3219.9	3203.1
35°	3207.6	3166.2	3099.7	3074.6	3053.9
37.5°	3062.3	3024.8	2958.4	2929.3	2908.6
40°	2913.0	2879.5	2813.1	2776.2	2759.4
42.5°	2767.7	2734.2	2668.3	2626.4	2601.8
45°	2610.1	2581.1	2518.5	2473.2	2456.5
47.5°	2456.5	2427.5	2361.0	2315.1	2290.5
50°	2294.5	2273.8	2215.7	2157.6	2136.9
52.5°	2136.9	2107.9	2054.1	2008.4	1979.3
55°	1975.4	1950.3	1900.5	1850.7	1830.1
57.5°	1813.3	1792.6	1738.5	1688.8	1672.0
60°	1651.3	1635.0	1576.9	1531.1	1518.8
62.5°	1493.7	1464.7	1423.3	1381.9	1365.2
65°	1332.1	1307.1	1265.7	1228.2	1207.6
67.5°	1166.2	1145.0	1108.1	1079.1	1062.3
70°	1012.5	995.8	958.4	929.3	913.0
72.5°	854.9	838.2	817.6	788.5	776.1
75°	696.9	689.0	667.8	643.2	651.5
77.5°	556.1	539.3	530.9	518.6	506.3
80°	415.1	410.8	402.3	390.0	381.7
82.5°	282.2	282.2	278.2	261.5	261.5
85°	169.9	166.0	162.0	149.3	145.3
87.5°	74.9	66.4	58.1	45.8	41.4
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P912012

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.74	15.86	15.46	16.61	17.49	14.29	15.42	15.02	16.16	17.05
	3H	16.41	17.42	17.15	18.18	19.10	15.92	16.93	16.66	17.69	18.61
	4H	17.01	17.96	17.76	18.73	19.66	16.52	17.47	17.27	18.23	19.16
	6H	17.42	18.30	18.19	19.07	20.02	16.92	17.80	17.69	18.57	19.52
	8H	17.53	18.37	18.31	19.16	20.11	17.03	17.87	17.81	18.66	19.61
	12H	17.59	18.39	18.37	19.17	20.14	17.08	17.88	17.86	18.66	19.64
4H	2H	15.23	16.18	15.99	16.94	17.87	14.87	15.82	15.63	16.59	17.52
	3H	17.11	17.91	17.88	18.71	19.65	16.70	17.50	17.47	18.30	19.25
	4H	17.83	18.56	18.62	19.35	20.33	17.41	18.13	18.19	18.93	19.91
	6H	18.36	18.98	19.16	19.81	20.79	17.92	18.55	18.73	19.38	20.36
	8H	18.51	19.10	19.32	19.92	20.91	18.07	18.66	18.88	19.48	20.47
	12H	18.59	19.12	19.42	19.96	20.96	18.14	18.67	18.97	19.51	20.51
8H	4H	18.04	18.63	18.85	19.45	20.45	17.67	18.25	18.47	19.07	20.07
	6H	18.68	19.17	19.52	20.03	21.02	18.30	18.78	19.13	19.64	20.64
	8H	18.90	19.33	19.75	20.19	21.20	18.51	18.94	19.36	19.80	20.81
	12H	19.04	19.42	19.89	20.27	21.34	18.63	19.01	19.48	19.86	20.93
12H	4H	18.04	18.57	18.87	19.41	20.41	17.67	18.20	18.50	19.04	20.04
	6H	18.71	19.14	19.56	20.00	21.01	18.34	18.77	19.19	19.63	20.64
	8H	18.96	19.34	19.81	20.19	21.26	18.58	18.96	19.43	19.81	20.88

END OF REPORT